

Racks



PACSystems RX7i Racks set the pace for the latest PLC technology. They are built to support the high-power PACSystems power supplies along with the latest technology in the PACSystems CPUs. The VME64 backplane provides up to four times the bandwidth of existing VME based systems for faster I/O throughput. The VME64 base supports all standard VME modules including I/O and VMIC modules.

	IC698CHS009	IC698CHS017	IC698CHS109	IC698CHS117	IC698CHS217
Product Name	Standard PACSystems 9-slot Wall (Rear) Mount	Standard PACSystems 18-slot Wall (Rear) Mount	Standard PACSystems 9-slot Wall (Panel) Mount	Standard PACSystems 18-slot Wall (Panel) Mount	PACSystems 17-slot Wall (Rear) Mount, Rear I/O Access
Lifecycle Status	Active	Active	Active	Active	Active
Number of Slots	9 Single Width, 5 Double Width (plus one for power supply)	15 Single Width, 8 Double Width (plus one for power supply)	9 Single Width, 5 Double Width (plus one for power supply)	15 Single Width, 8 Double Width (plus one for power supply)	17 Single Width, 8 Double Width (plus one for power supply)
Mounting Location	Rear (Panel)	Rear (Panel)	Front (Rack)	Front (Rack)	Rear (Panel)
Rack Configurations	RX7i CPU and I/O, VME modules	RX7i CPU and I/O, VME modules	RX7i CPU and I/O, VME modules	RX7i CPU and I/O, VME modules	RX7i CPU and I/O, VME modules (with or without rear access connections)
Rack Slot Size	0.8 inch	0.8 inch	0.8 inch	0.8 inch	0.8 inch
Compatible Power Supplies	RX7i Power Supply (IC698)	RX7i Power Supply (IC698)	RX7i Power Supply (IC698)	RX7i Power Supply (IC698)	RX7i Power Supply (IC698)
Dimensions	11.15"H x 12.6"W x 7.25"D (283 x 320 x 184mm)	11.15" x 19.00" x 7.5"	11.15"H x 12.6"W x 7.25"D (283 x 320 x 184mm)	11.15" x 19.00" x 7.5"	11.15"H x 19"W x 8.875"D (8.97"D with rear I/O cover) (283 x 483 x 225mm) (228mm D with rear I/O cover)