SLB SURFACE

SLB SERIES


1' x 4' SURFACE BOX FLUORESCENT FLAT STEEL OR REGRESSED ALUMINIUM FRAME 1 or 2 linear T8/T12


- Shallow 4" deep body.
- Positive cam-action latches door frame on either side.
- Efficiency 56.2% (2 T8).
- Center mounted ballast compartment (2 lamps).
- Snap-on wiring channel cover removed without tools.
- Matte black light seal on both ends to prevent light leaks.




MOUNTING METHODS/FEATURES

DIMENSIONS












12" (305mm)	4" (102mm)
2 1/2"	7/8" (22mm) DIA. K.O.
(64mm)	9 PLACES
3"	-2" (51mm)
(76mm)	DIA. K.O.

48" (1219mm)




FIXTURE TYPE	VOLTS
JOB INFORMATION:	


SLB SERIES 1' X 4'

1' X 4' SLB SURFACE 1' x 4' SURFACE FLUORESCENT


PHOTOMETRY



MODEL NO. SLB12SFSVA232S0



ORDERING INFORMATION Explanation of Catalogue Number Example: SLB1GFSVA232120SO



† % Total Harmonic Distortion

OPTIONS/ACCESSORIES

LENSES/SHIELDING

VB: Pattern 12 lens .125" nominal-Prismatic lens
VY: Pattern 12 lens .130" nominal-Prismatic lens

KA: Pattern 19 lens .156" nominal-Prismatic lens

AP: $1/2 \times 1/2 \times 1/2$ parabolic louver silver acrylic **SA**: $1 \frac{1}{2} \times 1 \frac{1}{2} \times 7/8$ parabolic louver silver acrylic

STEM AND CANOPY SETS: Suspend luminaire 12", 18", 24", 36", or 48" from surface. (Four per luminaire is recommended.) catalogue Number: STKF12 (12"); STKF18 (18"); STKF24 (24"); STKF36 (36"); STKF48 (48")

RADIO INTERFERENCE FILTER: 120, 277 or 347 volt, 50 or 60 Hz. SUFFIX: R.

BALLAST OPTIONS: For other ballast options, consult ballast specification sheet (folio BA-1-02)

SPECIFICATIONS:

PERFORMANCE: In an installation of 2 lamp 32W luminaires in a room cavity ratio of 1, with a reflectance of 80% ceiling, 50% wall, 20% floor, the C.U. shall not be less than .60. To prevent glare the average brightness at 65° shall not exceed 2037 candelas per square meter. To control veiling reflections, luminaire output in the 30°-90° zone shall be not less than 65%.

MATERIALS: Chassis parts are die-formed 20 gauge cold rolled steel.

ELECTRICAL: Thermally protected class "P" ballast C.B.M. approved, non PCB. If K.O. is within 3" of ballast, use wire suitable for at least 90°.

LABELS:



FINISH: White baked polyester powder coat.

We reserve the right to change, materials and finish in any way that will not alter installed appearance or reduce function and performance.



525 EDUCATION RD., CORNWALL, ONTARIO K6H 6C7 TEL.: (613) 938-6221 FAX: (613) 938-0961