



Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately.

CFL Frame-in Kit	Lamp	Base	Voltage	Amps
1101F13U	1-13W QT/TTT	4 Pin (GX24q-1/G24q-1)	120/277V	0,13 / 0,06A
1101F13-347	1-13W QT/TTT	4 Pin (GX24q-1/G24q-1)	347V	0,06A
1101F18U	1-18W QT/TTT	4 Pin (GX24q-2/G24q-2)	120/277V	0,17 / 0,08A
1101F18-347	1-18W QT/TTT	4 Pin (GX24q-2/G24q-2)	347V	0,06A
1101F2642U	1-26W QT/TTT	4 Pin (GX24q-3/G24q-3)	120/277V	0,24/0,11A
	1-32W TTT	4 Pin (GX24q-3)		0,31/0,13A
	1-42W TTT	4 Pin (GX24q-4)		0,38/0,17A
1101F2642-347	1-26W QT/TTT	4 Pin (GX24q-3/G24q-3)	347V	0,09A
	1-32W TTT	4 Pin (GX24q-3)		0,11A
	1-42W TTT	4 Pin (GX24q-4)		0,15A

Features

- 1. Mounting Frame:** .036" (#20ga.) Galvanized Steel. Accommodates all ceilings up to 1-1/2" thick; including existing or inaccessible areas.
- 2. Trim Clips:** "Push In / Twist Out" Stainless Steel clips hold reflector flush to ceiling.
- 3. Junction Box:** 2" x 4" x 3-1/2" (22cu.in.) .032" (#22ga.) galvanized steel. CSA Certified for maximum of 8 (#12ga.) through branch circuit conductors.
- 4. UniFrame™ Mounting System – Grid Ceiling:** Tool free mounting in grid ceilings. .036" (20ga.) Galvanized Steel interlocking slide bars adjust to 24-1/8" long accommodating 24" O.C. Ceiling Grid. Adjustable speed clamps for positive attachment to grid ceiling systems.
- 5. UniFrame™ Mounting System – Wood Joist Ceiling:** Integral nailing tabs, alignment guides, fastener holes and bendable strapping guides for wood joist installation. Galvanized Steel interlocking slide bars adjust from 12-15/16" to 24-1/8" long to accommo spacing, with or without strapping. Suitable for Steel Ceiling construction using standard 1/2" EMT, (See Instruction Sheet).
- 6. Ballast:** 120V, 277V, 347V UL Listed Electronic Ballast, end of lamp life protection, class "P" thermally protected, class "A" sound rating. Minimum starting temperature is 0°F.
- 7. Socket:** Four-pin base, molded thermoplastic socket, prewired with No. 18 AWM leads to ballast.
- 8. Socket Housing:** .036" (#20ga.) Galvanized Steel housing attaches to reflector trim by spring clip for precise optic alignment.

Markinas

cULus listed, suitable for damp locations.

Accessories

1967A: Extra Thick Ceiling Adapter (2" thick).

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	