



EnduraLED 17W 2700K 120V PAR38 Dimmable

Product family description

The Philips EnduraLED™ PAR indoor reflectors with high brightness LEDs are suited for track and recessed lighting. Energy saving, long life LED PAR lamps install into existing fixtures, can lower cost with reduced wattage and re-lamping frequency.

Features

- Soft white light.
- Ideal for overhead track fixtures.
- High brightness indoor flood lamps.
- Application performance close to 45W Halogen PAR.
- Offers 15 year rated average life, if operated 8 hours per day, 7 days per week.
- Smooth dimming to 10% of full light levels (Designed for "Leading Edge" TRIAC dimming systems)
- 16Watt Par38 in Soft White, Warm White, and Cool White versions.

Benefits

- Philips is the global leader in light and a leader in LED technology.
- Philips knows LED light and stands behind the EnduraLED products with a warranty.
- Philips' commitment to innovation and quality provides the confidence of partnering with an industry leader.

Application

- Perfect for track and recessed lighting.


Product data	
Product Number	410175
Full product name	EnduraLED 17W 2700K 120V PAR38 Dimmable
Ordering Code	410175
Pack type	
Pieces per Sku	1
Skus/Case	6
Pack UPC	046677410179

PHILIPS

Product data	
EAN2US	
Case Bar Code	50046677410174
Successor Product number	
Additional Information	Dimmable
Bulb	PAR38 [PAR38 mm]
Average Lifetime	45000 hr
Pack UPC	046677410179
Case Bar Code	50046677410174
Ordering Code	17PAR38/END/2700 DIMM/22D
Wattage	17W
Dimmable	Yes
Color Code	WW
Color Designation (text)	Warm White
Correlated Color Temperature	2700 K
Luminous Flux	880 Lm
Luminous Intensity	3500 cd
Color Temperature	2700K [CCT 2700K]
Product Number	410175



EnduraLED E26 PAR38



EnduraLED E26/E27 PAR38



©2009 Koninklijke Philips Electronics N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Document order number : 0000 000 00000