

50-100 Amps

Functions

All timing and sensing functions originate in the generator controller.

Utility voltage drop-out.....	<60%
Timer to generator start	10 second factory set, adjustable between 2-1500 seconds by a qualified dealer*
Engine warm up delay	5 seconds
Standby voltage sensor	60% for 5 seconds
Utility voltage pickup.....	>80%
Re-transfer time delay	15 seconds
Engine cool-down timer	60 seconds
Exerciser	12 minutes every 7 days

The transfer switch can be operated manually without power applied.

*When used in conjunction with units utilizing Evolution™ controls

Specifications

Model	RTG10EZA1	RTG12EZA1	RTG14EZA1	RTG16EZA1
Voltage	120/240, 1Ø	120/240, 1Ø	120/240, 1Ø	120/240, 1Ø
Amps	50	50	100	100
Circuits, 50A, 240V	—	—	—	1
40A, 240V	—	1	1	1
30A, 240V	1	1	—	—
20A, 240V	1	—	1	1
20A, 120V	3	3	6	5
15A, 120V	3	5	4	5
Phase	1			
Rated AC Frequency	60 Hz			
Enclosure Material	Steel			
Enclosure Type	NEMA 1			
Withstand Rating (Amps)	10,000			
Lug Range	1/0 - #14			
Load Transition Type	Open Transition			
3Ø Whip Conductor Gauges (Hot, Neutral, Ground, Control)	8, 8, 10, 18		6, 6, 8, 18	

Features

- Electrically operated, mechanically-held contacts for fast, positive connections.
- Rated for all classes of load, 100% equipment rated, both inductive and resistive.
- 2 pole, 250 VAC contactors.
- 30 millisecond transfer time.
- Dual coil (100A) and single coil (50A) designs.
- Main contacts are silver plated or silver alloy to resist welding and sticking.
- NEMA 1 (indoor rated) enclosure is standard.
- 5 Year Limited Warranty.

Dimensions and Wire Ranges

Mechanical Dimensions							
Amps	Height			Width			Depth
	H1	H2	H3	W1	W2	W3	
50*	18.5 in.	22.5 in.	22 in.	10.5 in.	15.4 in.	14.4 in.	3.8 in.
	470mm	571.8mm	558.8mm	266.7	392mm	366mm	97.5mm
100	23.5 in.	26.4 in.	N/A	8.3 in.	12.6 in.	N/A	6.3 in.
	597mm	671.7mm	N/A	211mm	320.7mm	N/A	159.6mm

*Note: The 50 Amp switch is flush mountable. H1 and W1 refer to mounting hole spacing. H2 and W2 are cover dimensions. H3 and W3 (not shown in diagram) are the enclosure dimensions without cover.

Wire Ranges			
Amps	Conductor Lug	Neutral Lug	Ground Lug
50	1/0 - #14	2/0 - #14	2/0 - #14
100	2/0 - #14	2/0 - #14	2/0 - #14

