



Electrical	<b>Specifications</b>

GOPA-3P32-LW-SC		
Brand Name	OPTANIUM	
Ballast Type	Electronic	
Starting Method	Instant Start	
Lamp Connection	Parallel	
Input Voltage	347	
Input Frequency	50/60 HZ	
Status	Active	

Lamp Type	Num. of	Rated Lamp Watts	Min. Start Temp (°F/C)	Input Current (Amps)	Input Power (ANSI	Ballast Factor	MAX THD	Power Factor	MAX Lamp Current Crest	B.E.F.
	Lamps				Watts)		%		Factor	
* F17T8	2	17	-20/-29	0.09	30	0.87	10	0.97	1.6	2.90
F17T8	3	17	-20/-29	0.12	39	0.81	10	0.98	1.6	2.08
F25T8	2	25	-20/-29	0.12	42	0.85	10	0.98	1.6	2.02
F25T8	3	25	-20/-29	0.16	56	0.77	10	0.99	1.6	1.38
F32T8	2	32	-20/-29	0.16	55	0.86	10	0.98	1.6	1.56
F32T8	3	32	-20/-29	0.21	74	0.77	10	0.99	1.6	1.04
F32T8/ES (25W)	2	25	60/16	0.13	43	0.86	10	0.98	1.6	2.00
F32T8/ES (25W)	3	25	60/16	0.17	58	0.77	10	0.99	1.6	1.33
F32T8/ES (28W)	2	28	60/16	0.13	46	0.77	10	0.98	1.6	1.67
F32T8/ES (28W)	3	28	60/16	0.18	62	0.77	10	0.99	1.6	1.24
F32T8/ES (30W)	2	30	60/16	0.15	50	0.86	10	0.98	1.6	1.72
F32T8/ES (30W)	3	30	60/16	0.19	67	0.77	10	0.99	1.6	1.15
F40T8	2	40	32/00	0.19	65	0.85	10	0.99	1.6	1.31







## **Enclosure Dimensions**

OverAll (L)	Width (W)	Height (H)	Mounting (M)
9.50 "	1.7 "	1.18 "	8.90 "
9 1/2	1 7/10	1 9/50	8 9/10
24.1 cm	4.3 cm	3 cm	22.6 cm





Revised 06/23/09

Data is based upon tests performed by Advance Transformer in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.



## **Electrical Specifications**

GOPA-3P32-LW-SC		
Brand Name	OPTANIUM	
Ballast Type	Electronic	
Starting Method	Instant Start	
Lamp Connection	Parallel	
Input Voltage	347	
Input Frequency	50/60 HZ	
Status	Active	

## Notes:

Section I - Physical Characteristics

- 1.1 Ballast shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable.
- 1.2 Ballast shall be provided with integral leads color-coded per ANSI C82.11.

Section II - Performance

- 2.1 Ballast shall be \_\_\_\_\_ (Instant or Programmed) Start.
- 2.2 Ballast shall provide Independent Lamp Operation (ILO) for Instant Start or Programmed Start Parallel ballasts allowing remaining lamp(s) to maintain full light output when one or more lamps fail.
- 2.3 Ballast shall contain auto restart circuitry in order to restart lamps without resetting power.
- 2.4 Ballast shall operate from 50/60 Hz input source of \_\_\_\_\_ (120V through 277V or 347V) with sustained variations of +/- 10% (voltage and frequency).
- 2.5 Ballast shall be high frequency electronic type and operate lamps at a frequency between 42 kHz and 52 kHz to avoid interference with infrared devices, eliminate visible flicker and avoid Article Surveillance System, such as anti-theft devices.
- 2.6 Ballast shall have a Power Factor greater than 0.98 for primary lamp.
- 2.7 Ballast shall have a minimum ballast factor for primary lamp application as follows: 0.77 for Low Watt, 0.87 for Normal Light Output, and
- 1.18 for High Light for Instant Start ballasts or 0.71 for Low Watt and 0.88 for Normal Light Output for Programmed Start ballasts.
- 2.8 Ballast shall provide for a Lamp Current Crest Factor of 1.7 or less.
- 2.9 Ballast input current shall have Total Harmonic Distortion (THD) of less than 10% when operated at nominal line voltage with primary lamp.
- 2.10 Ballast shall have a Class A sound rating for all 4-foot lamps and smaller.
- 2.11 Ballast shall have a minimum starting temperature of -29C (-20F) on Instant Start ballasts or -18C (0F) on Programmed Start ballasts for standard T8 lamps and 16C (60F) for energy-saving T8 lamps. Consult lamp manufacturer for temperature versus light output characteristics.
- 2.12 Ballast shall tolerate sustained open circuit and short circuit output conditions.
- 2.13 Ballast shall have lamp striation-reduction circuitry.
- 2.14 Programmed Start ballast shall provide lamp EOL protection circuitry.
- 2.15 Maximum distance for Energy Saving Lamps in Remote/Tandem wiring applications shall be 6 feet for Instant Start and Programmed Start models.

Section III - Regulatory

- 3.1 Ballast shall not contain any Polychlorinated Biphenyl (PCB).
- 3.2 Ballast shall be Underwriters Laboratories (UL) listed, Class P and Type 1 Outdoor; and Canadian Standards Association (CSA) certified where applicable.
- 3.3 Ballast shall comply with ANSI C62.41 Category A for Transient protection.
- 3.4 Ballast shall comply with ANSI C82.11 where applicable.
- 3.5 Ballast shall comply with applicable requirements of the Federal Communications Commission (FCC) rules and regulations, Title 47 CFR part 18, for Non-Consumer equipment.
- 3.6 Ballast shall meet NEMA Premium/CEE High Performance T8 Lighting System Specifications.
- 3.7 IOP or GOP ballast shall comply with UL Type CC rating.
- 3.8 Ballast shall comply with NEMA 410 for in-rush current limits.
- 3.9 Ballast shall meet RoHS Compliance Standards

Section IV - Other

- 4.1 Ballast shall be manufactured in an ISO 9001 Qualified factory.
- 4.2 Ballast shall carry a five-year warranty from date of manufacture against defects in material or workmanship, including replacement, for operation at a maximum case temperature of 70C. Ballasts with a "90C" designation in their catalog number shall also carry a three-year warranty at maximum case temperature of 90C.
- 4.3 Manufacturer shall have a twenty-year history of producing electronic ballasts for the North American market.
- 4.4 Energy-saving T8 lamps (25W, 28W or 30W) may experience lamp striations if operated on ballasts not rated for their use.





Revised 06/23/09

Data is based upon tests performed by Advance Transformer in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.