

LCD Console with High-Performance lyriQ, White

HA5010-WH



This 7" LCD Console features a simple graphic user interface that allows control of camera, multi-room audio, intercom, lighting and messaging functions when coupled with the [Integration Module](#) of the Unity Home System. The console mounts in a standard triple gang box and installs easily via Cat 5 wiring with convenient RJ45 connections.

This LCD features additional connections for High-Performance lyriQ that turn it into a volume control when used as part of the Unity Home System.

features & benefits

- Mounts in a standard triple gang box and installs easily via Cat 5 wiring with convenient RJ45 connections.
- 7" LCD screen with a simple push button interface to select desired input.
- Controllable through an On-Q IR remote control.
- Attractive design complements the home and matches other On-Q devices in the Studio design.
- Up to four video feeds available with on-board sequencing of camera images.
- Additional connections for High-Performance lyriQ to turn screen into volume control.
- Integration module required.

specifications

General Info

Color: White

Dimensions

Overall Dimensions U S: 7.00"H x 7.25"W x 3.5"D

Cord Information

Pinning: LCD Out

1. Left Audio (PreGND) Audio Pre-Ground
2. Left Audio Input Audio Signal (line level analog)
3. Right Audio (PreGND) Audio Pre-Ground
4. IR (IR TX) Output IR Command (analog 12V max signal)
5. Status (IR RX) Input IR Command (analog 12V max signal)
6. Right Audio Input Audio Signal (line level analog)
7. Ground Power Ground
8. Power (+24VDC) +24Vdc Power Input

lyriQ Out

1. Left Audio (PreGND) Audio Pre-Ground
2. Left Audio Input Audio Signal (line level analog)
3. Right Audio (PreGND) Audio Pre-Ground
4. IR (IR TX) Output IR Command (analog 12V max signal)
5. Status (IR RX) Input IR Command (analog 12V max signal)
6. Right Audio Input Audio Signal (line level analog)
7. Ground Power Ground
8. Power (+24VDC) +24Vdc Power Input

Technical Information

Cat5 Cable Rating: Cat 5e UTP, 4 Pair Solid Conductor (24 AWG)

Frequency Response: 20 - 20,000Hz \pm 1dB with lyriQ Add-On Board

Humidity: Up to 90% RH (non-condensing)

IR Range On Axis: 25ft Max

IR Receive Frequency: 10 kHz – 110 kHz

Operating Temperature Celsius: 0 to 55°C

Output And Line Out Connection: 14-28 AWG Springcon® Terminal Block with lyriQ Add-On Board

Output Impedance: 8 Ohms per channel (1 pair of speakers) with lyriQ Add-On Board

Power Requirements: +24Vdc, +/-1.5Vdc, 0.75 A max; +24Vdc, +0/ -6Vdc, 1500mA max with lyriQ Add-On Board

Q Link Video Ports: RJ-45

Speaker Impedance Load: 6 Ohm max with lyriQ Add-On Board

Storage Temperature: -55 to 75°C