



Compact Fluorescent  
Energy Saver Universal  
and 3-Way Lamps

*Ideal for use in any current  
incandescent application*

ENERGY SAVER



† This lamp is better for the environment because of its reduced mercury content. All Philips ALTO® lamps give you end-of-life options which can simplify and reduce your lamp disposal costs depending on your state and local regulations.

## Energy saver universal lamps

Philips Compact Fluorescent Energy Saving Universal and 3-Way Lamps provide energy savings and reduce operating costs without sacrificing quality of light compared to incandescent equivalents.

### Direct replacement for incandescent bulbs

- Provides warm and inviting soft white light
- Fits into incandescent fixtures and can be used in enclosed fixtures
- Available in 3-Way

### Long life

- Lasts at least 5 years\*

### Energy savings

- Saves up to \$112 over the life of the lamp when you replace a 100W A19 incandescent lamp with a 25W energy saver universal\*\*

\* Based on an average daily usage of 3–4 hours per day, 7 days per week.

\*\* Energy savings based on wattage saved x replacement lamp rated average life (15,000 hours) ÷ 1000 x \$0.10 kWh rate.

**PHILIPS**  
sense and simplicity

# Compact Fluorescent Energy Saver Universal and 3-Way Lamps

## Ordering, Electrical and Technical Data

Product Number	Description	Volts	Nom. Watts	Approx. Incand. Equiv.	Base	Color Temp. (Kelvin)	CRI	Approx. Initial Lumens <sup>1</sup>	MOL (In.)	Diam. (In.)	Rated Avg. Life (Hrs.) <sup>2</sup>	Min. Starting Temp.	Max. Ambient Temp.
<b>UNIVERSAL</b>													
● 14691-0	Universal SLS 14 ALTO	120	14	60W	Med.	2700	82	860	4 1/16	2.3	12,000	-32°F/0°C	104°F/40°C
● 13077-3	Universal SLS 20 ALTO	120	20	75W	Med.	2700	82	1200	5 5/8	2.3	15,000	-32°F/0°C	104°F/40°C
● 13574-9	Universal SLS 25 ALTO	120	25	100W	Med.	2700	82	1750	6 3/8	2.3	15,000	-32°F/0°C	104°F/40°C
<b>3-WAY</b>													
● 14042-6	3-Way EL/TW	120	34/26/18	150/100/50W	Med.	2700	82	2025/1400/750	6 3/8	2.3	7000	-32°F/0°C	104°F/40°C
<b>TABLE</b>													
● 37082-5	Universal SLS 34 ALTO	120	34	120W	Med.	2700	82	2100	6 3/8	2.6	7000	-32°F/0°C	104°F/40°C

## Shipping Data

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	SKU Dimensions (W x D x H)(In.)	Case Dimensions (W x D x H)(In.)	Pallet Dimensions (W x D x H)(In.)
<b>UNIVERSAL</b>											
14691-0	14691-7	14691-2	6	2.00	0.118	2016	336	6	2.2 x 2.2 x 5.3	4.8 x 7.1 x 6.0	38.5 x 42.4 x 42.0
13077-3	13077-0	13077-5	6	1.98	0.133	2016	336	6	2.2 x 2.2 x 6.0	5.0 x 7.0 x 6.8	38.5 x 49.4 x 40.5
13574-9	13574-4	13574-9	6	1.98	0.143	2016	336	6	2.2 x 2.2 x 6.5	4.8 x 7.1 x 7.3	38.5 x 49.4 x 43.5
<b>3-WAY</b>											
14042-6	14042-7	14042-2	6	1.98	0.143	2016	336	6	2.2 x 2.2 x 6.5	4.8 x 7.1 x 7.3	38.5 x 49.4 x 43.5
<b>TABLE</b>											
37082-5	37082-4	37082-9	6	2.00	0.140	2100	210	10	2.2 x 2.2 x 6.5	4.8 x 7.1 x 7.3	36.3 x 49.4 x 48.1

1) Approximate initial lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life under standard laboratory conditions. Use in recessed cans or enclosed fixtures could result in reduced lamp life.

2) Average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Use in recessed cans or enclosed fixtures could result in reduced lamp life.

● Amalgam Technology provides stable light output from -32°F to 104°F.

● This lamp is better for the environment because of its reduced mercury content. All Philips ALTO® lamps give you end-of-life options which can simplify and reduce your lamp disposal costs depending on your state and local regulations.

Above specifications subject to change without notice.

**WARNINGS AND CAUTIONS:** Do not use with dimmers. Some electronic timer and photo sensor switches contain dimming circuitry, so before using such a switch, check with its manufacturer to ensure compatibility with electronic CFL bulbs. Do not use with emergency exit fixtures or lights. Outdoor use requires a weather-protected fixture. Turn off power before changing bulb. This device complies with Part 18 of the FCC Rules.

Reliable operating temperature range -32F/-0C to 104F/40C.

**Note:** This product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.

Bulb Type	Table/Floor Lamp	Outdoor Postlight	Wall Sconce	Surface Mount	Reading Lamp	Border Lights	Recessed Fixture	Open Hanging	Vanity Strip	Ceiling Fan
Decorative Twister	●		●		●			●		
Universal	●	●	●	●	●	●	●	●		
3-Way	●									
Reflector Flood							●	●		
Dimmable Reflector Flood							●	●		
Candle		●	●		●					●
Vanity & Decor Globe								●	●	●
Soft White Plus	●	●	●		●	●		●		●
Outdoor		●				●				
Bug-A-Way		●								
Circline	●									
Genie	●	●	●	●	●	●	●	●	●	●



© 2008 Philips Lighting Company. All rights reserved.  
 Printed in USA 1/08  
 P-3754-D  
[www.philips.com](http://www.philips.com)

Philips Lighting Company  
 200 Franklin Square Drive  
 P.O. Box 6800  
 Somerset, NJ 08875-6800  
 1-800-555-0050  
 A Division of Philips Electronics North America Corporation

Philips Lighting  
 281 Hillmount Road  
 Markham, Ontario  
 Canada L6C 2S3  
 1-800-555-0050  
 A Division of Philips Electronics Ltd.