

INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.) ⁽⁹³⁾	Approx. MBCP* Lumens	
120	BR40	Med.	22541-7	▲ X ✓ (87)	I20BR/FL60	120	24	Reflector Flood	C, CC-6	6½		2000	1300	
		Med.	22532-6	▲ X ✓ (87)	I20BR/FL60	130	24	Reflector Flood	C, CC-6	6½		2000	1300	
		Med.	20199-6	▲ ✓ (87)	I20BR/FL60/TG 24/1	130	24	TuffGuard Coated Reflector Flood	C, CC-6	6½		2000	1300	
		Med.	20200-2	▲ ✓ (87)	I20BR/FL60/TG CDA 24/1	120	24	TuffGuard Coated Reflector Flood	C, CC-6	6½		2000	1300	
		Med.	22544-1	▲ X (87)	I20BR/SP20	120-130	24	Reflector Spot	C, CC-6	6½		2000	1300	
		Med.	16779-1	▲ X (87)	I20BR/FL60/LL 8/1	120	8	Long Life Reflector Flood	C, CC-6	6½		2500	1000	1285
		Med.	16781-7	▲ X (87)	I20BR/SP20/LL 8/1	120	8	Long Life Reflector Spot	C, CC-6	6½		2500	4600	1225
		Med.	16715-5	▲ (87)	I20BR/Agro 6/1	120	6	Agro-Lite Plant Light	C, CC-6	6½		2000		
		Med.	14012-9	X (87)	I20BR/FL 12/1 PRO	130	12	ProPack Reflector	C, CC-6	6½		2000		1300
		ER40	Med.	13928-7	▲ X \$	I20ER40	120-130	24	Elliptical Reflector	C, CC-6	7¾		2000	1190
125	BR40	Med.	15930-1	▲ (27,87,89)	I25BR40/1/TG 4/1	120	4	TuffGuard Coated Clear Reflector Infrared	C, C-9	6½		5000		
135	A21	Med.	28175-8	▲ \$	I50A-I35A/EW	120-130	60	Frost Econ-o-watt Ratings @ 120V=127W	C, CC-8			5%	750 1280	2490 2169
		Med.	15002-9	▲ \$	I50A-I35A/99/EW	120-130	60	Frost Econ-o-watt Ratings @ 120V=119W	C, CC-8			5%	1000 1700	2300 2000
		Med.	37616-0	(12)	K135A21/TS/EW	120-125	120	Clear Krypton Econ-o-watt Traffic Signal	C, C-11V	3	4¼	8000	1750	
	A25	Med.	26836-7	X \$ □	I35A25/35	130	60	Frost Econ-o-watt Industrial Svc. Ratings @ 120V=119W	C, C-9			6½%	3500 9987	1865 1423
150	A21	Med.	27003-3	▲ ✓	I50A	120	48	Frost	C, C-9			5%	750	2700
		Med.	27069-4	▲ ✓	I50A	130	48	Frost Ratings @ 120V=133W	C, CC-8			5%	750 2120	2700 2050
		Med.	37417-3	▲ ✓ X (82)	I50A/99	120-130	60	Frost Extended Service Ratings @ 120V=141W	C, C-9			5%	2500 4250	2200 1930
		Med.	37418-1	▲ (82)	I50A/CL	120-130	60	Clear Ratings @ 120V=141W	C, CC-8	3¾		5%	750 1275	2700 2300
		Med.	14969-0	▲ (66)	I50A21/RS/TF	120-130	60	High-Temp. Coating	C, RC-9			5%	1000	
		Med.	15009-4	▲	I50A/CL/LL 12/1 TP	120	12	Clear Long Life	C, CC-8			5%	1500	2000
		Med.	16866-6	▲	I50A/WL 12/1	120	12	Soft White Long Life	C, CC-8			5%	2000	2310
		Med.	27578-4	▲	I50A21/RS/BR	120-130	60	Frost Rough & Vibration Service Ratings @ 120V=141W	C, RC-9			5%	1000 1700	2205 1915
		Med.	27586-7	▲	I50A21/CL/RS/VS	120-130	60	Clear Rough & Vibration Service Ratings @ 120V=141W	C, RC-9	3¾		5%	1000 1700	2200 1915
		Med.	27588-3	▲	I50A/35/RS/BR	120-130	60	Frost Industrial Rough Service Ratings @ 120V=141W	C, RC-9	3¾		5½%	3500 5900	1640 1425
		Med.	15931-9	▲	I50A/35RS/BR/TG	120-130	60	Frost Industrial Rough Service Ratings @ 120V=141W	C, RC-9	3¾		5½%	3500 5900	1640 1425

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
150	A23	Med. LHT	28170-9	(18) X	I50A23/LHT	120-130	60	Frost	C, CC-8		6%	750		2700
	A23	Med.	28172-5	▲	I50A23	120-130	60	Frost	C, CC-8	4%	6%	750		2700
			37419-9	▲	I50A23/CL	120-130	60	Clear Ratings @120V=141W	C, CC-8	4%	6%	750 1275		2700 2300
	A25	Med.	37421-5	□	I50A25/35	120-130	60	Frost Industrial Service Ratings @120V=141W	C, C-9		6%	3500 5975		1715 1500
			14961-7	□ (14,66)	I50A25/35/TF	120	60	Frost Silicone Coated Industrial Svc.	C, C-9		6%	3500		
	BR40	Med.	22725-6	▲ (87)	I50BR/AGRO 6/1	120	6	Agro-Lite Plant Light	C, CC-6		6½%	2000		
	BR38	Med.	38568-2		I50BR38/5FL	130	12	Flood Anti-Vibration	C, C-11V		5½%	5000		
			20203-6		I50BR38/FL/TG 6/1	130	6	TuffGuard Coated Lamp	C, CC-6		5½%	2000		1650
	PS25	Med.	28173-3	▲	I50	120-130	60	Frost Ratings @120V=141W	C, C-9		6%	750 1280		2460 2143
			28174-1	▲	I50PS25/99	120-130	60	Frost Extended Service Ratings @120V=141W	C, C-9		6%	2500 4250		1950 1690
			14983-1	▲ (66)	I50PS25/TF	120	60	Frost Silicone Coated	C, C-9		6%	1000		
			24684-3	▲	I50PS25/99CL	250	60	Clear Extended Service	C, CC-9		6%	2500		1840
	175	PAR38	Med. Skt.	14551-6	(27,89)	I75PAR38/HEAT/CL	120	12	Clear Infrared	C, C-9		5%	5000	
			36403-4	(27,89)	IR175PAR	120	15	Clear Infrared	C, C-9		5%	5000		
			20838-9	(27,89)	IR175PAR	120	12	Clear Infrared	C, C-9		5%	5000		

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP* Lumens
-------	------	------	----------------	--------------------	---------------	-------	------------	-------------	----------------	-----------	-----------	----------------------------	----------------------

INCANDESCENT LAMPS (BY WATTAGE) CONTINUED

200	A21	Med.	16867-4	▲	200A/WL 6/I	120	6	Soft White Long Life	C, CC-2V		5%	1500	3100
	A23	Med.	16798-0	▲	200A/CL/LL 6/I	120	6	Clear Long Life	C, CC-8		6%	1500	3665
			36289-7	▲	200A	120	60	Frost	C, CC-8		6%	750	3800
			36291-3	▲	200A	130	60	Frost	C, CC-2V		6%	750	3600
								Ratings @120V=176W				2120	2700
			37427-2	▲	200A/CL	120-130	60	Clear	C, CC-2V	4%	6%	750	3600
								Ratings @120V=187W				1275	3130
			28176-6	▲	200A/99	120-130	60	Frost Extended Service	C, CC-2V		6%	2500	3250
								Ratings @120V=187W				4250	2830
			20204-4	▲	200A/99/TG 60/I	120-130	60	TuffGuard Coated Lamp Frost	C, CC-8		6%	2500	3500
			32383-2	▲	200A/99/CL	130	60	Clear	C, CC-8		6%	2500	3100
	A25	Med.	39813-1	□	200A25/35	130	60	Frost Industrial Service	C, C-9		6½%	3500	2690
								Ratings @120V=177W				9987	2052
	PAR56	Mog. End Prong	28956-1	(9,59,90)	200PAR56/MFL	120	8	PAR Med. Flood	C, CC-13		5	2000	
	PS25	Med.	34974-6	▲	200/IF	250	60	Frost	C, CC-9		6½%	1000	2900
			34976-1	▲	200	277	60	Clear—Mine	C, CC-9	5¼	6½%	1000	2540
	PS30	Med.	14301-6	▲	200	120-130	60	Clear	C, C-9		8%	750	3250
								Ratings @120V=177W				2120	2470
			14299-1	▲	200/IF	120-130	12	Clear	C, C-9		8%	750	3200
								Ratings @120V=177W				2120	2430
		14298-3	▲ (66)	200/TF	120	60	Frost Silicone Coated	C, C-9		8%	750	2980	
		14297-5	▲	200/99IF	120-130	60	Frost	C, C-9		8%	750	2600	
							Ratings @120V=177W				2140	1975	
		14304-0	▲	200PS30/23	120-130	60	Frost	C, C-9		8%	1000	2800	
							Ratings @120V=177W				2830	2130	
		14303-2	▲	200PS30/24	120-130	60	Clear Rough Service	C, C-9		8%	1000	2900	
							Ratings @120V=177W				2830	2205	
		14305-7	▲ (66)	200PS30/RS/TF	120-130	60	Frost Rough Service Silicone Coated	C, C-9		8%	1000	2715	
											2830	2065	
		20472-7	▲ (66)	200PS30/RS/TG	120-130	60	TuffGuard Frost Rough Service	C, C-9		8%	1000		
		14302-4	▲	200PS30/RS	250	60	Clear Rough Service	C, C-9		8%	1000	2600	
		14300-8		200/35/TF	120	60	Frost Silicone Coated Industrial Svc.	C, C-9		8%	3500	2570	
PS30	Mog.	14296-7		200PS30/12	130	60	Clear	C, C-9	6%	8%	750	3250	
							Ratings @120V=177W				2140	2785	

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
250	BR40	Med.	38932-0	▲ (27, 87)	250BR40/I 4/I	120	4	Clear Reflector Infrared	C, C-9		6½	5000		
			20205-1	▲ (27, 87)	250BR40/I/TG 4/I	120	4	TuffGuard Coated Clr. Ref. Infrared	C, C-9		6½	5000		
			14011-1	▲ (27, 87)	250BR40/I 12/I PRO	130	12	ProPack Clear Reflector Infrared	C, C-9		6½	5000	1600	
	PAR38	Med. Skt.	37432-2	□ (53, 82)	K250PAR38/FL	120-130	12	PAR Floodlight (Krypton)	C, CC-6		5½	4000	5000	3100
			37433-0	□ (53, 82)	K250PAR38/SP	120-130	12	PAR Spotlight (Krypton)	C, CC-6		5½	4000		3100
	R40	Med.	38933-8	▲ \$(27,87,89)	250R40/HR 4/I	120	4	Red Bowl Heat Ray	C, C-9		6%	5000		
15932-7			▲ \$(27,87,89)	250R40/HR/TG 4/I	120	4	TuffGuard Ctd. Red Bowl Heat Ray	C, C-9		6%	5000			
300	BR40	Med.	14343-8	▲ \$ (87)	300BR/FL	120-130	24	Reflector Flood	C, CC-11		6½	2000		2480
			PAR56	Mog. End Prong	23382-5		300PAR56/MFL	120	8	PAR Med. Flood	C, CC-13		5	2000
	23405-4	(9, 55)			300PAR56/MFL	130	8	PAR Med. Flood	C, CC-13		5	2000		
	23388-2	(9, 55)			300PAR56/WFL	120	8	PAR Wide Flood	C, CC-13		5	2000		
	23410-4	(9, 55)			300PAR56/WFL	130	8	PAR Wide Flood	C, CC-13		5	2000		
	23378-3	(9, 46, 55)			300PAR56/NSP	120	8	PAR Narrow Spotlight	C, CC-13		5	2000		
	PS25	Med.	28177-4	▲	300M/IF	120-130	60	Frost	C, CC-8		6½	750		6230
												1280		5471
			38941-1	▲	300M/IF	120	6	Frost	C, CC-8		6½	750		6300
			20206-9	▲	300M/99IF/TG	120/130	60	TuffGuard Frost Coated Lamp	C, CC-8		6½	2500		5060
			13391-8	▲	300M	120-130	12	Clear	C, CC-8	5¼	6½	750		6280
												2120		4625
			35008-2	▲	300M/99IF	120	60	Frost Extended Service	C, CC-8		6½	2500		4044
			35009-0	▲	300M/99IF	130	60	Frost Extended Service	C, CC-8		6½	2500		506
												7130		4044
										7134		5300		
									7134		4044			
PS30	Med.	14307-3	▲	300M/PS30IF	120-130	60	Frost	C, C-9		8½	750		5000	
											2120		3800	
		14306-5	▲	300M/PS30	120-130	60	Clear	C, C-9		8½	750		5000	
											2120		3800	
												5000		
												2120	3800	
												5000		
												2120	3800	
												3500	3800	
												9900	2885	

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



BR40
Med.



PAR38
Med. Skt.



R40
Med.



PAR56
Mog. End Prong



PS25
Med.



PS30
Med.

INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP* Lumens
-------	------	------	----------------	--------------------	---------------	-------	------------	-------------	----------------	-----------	-----------	----------------------------	----------------------

INCANDESCENT LAMPS (BY WATTAGE) CONTINUED

300	PS35	Mog.	14320-6		300/RSIF	120	24	Frost Rough Service	C, C-9			9%	1000	5150	
			14309-9		300/99IF	120-130	24	Frost Extended Service Ratings @120V=265W	C, C-9				9%	1000	4500
														2830	3420
			14321-4		300/99	120-130	24	Clear Extended Service Ratings @120V=265W	C, C-9				9%	2500	4600
														7134	3495
			14316-4		300/IF	120-130	12	Frost Ratings @120V=265W	C, C-9				9%	1000	4,600
														2854	3495
			14314-9		300	120-130	24	Clear Ratings @120V=265W	C, C-9	7		9%	1000	4600	
												2854	3495		
			14317-2		300	277	24	Clear	C, C-9	7		9%	1000	4000	
			20474-3		300/IF/TG	120-130	12	TuffGuard Coated Lamp	C, C-9			9%	1000		
	R40	Med.	14432-9	■▲ (31,37,51,53)	300R/FL/I	12	24	Reflector Flood Frost—Swimming Pool	C, C-2V			6%	2000	2960	
			14429-5	■▲ (31,37,51,53)	300R/FL/I	120-130	24	Reflector Flood—Swimming Pool	C, CC-1 I			6%	2000	2480	
	R40	Mog.	14433-7	▲ (31,37,51,53)	300R/3FL	120-130	24	Reflector Flood	CC-1 I			7%	2000	3600	
375	BR40	Med. Skt.	14342-0	(19,31,37,87)	375BR40	120	24	Reflector Infrared Lt. Frost Industrial	C, C-7A			7%	5000		
	R40	Med. Skt.	14574-8	(19,31,37,87)	375R40/I	120	24	Clear Reflector Infrared Industrial	C, C-7A			7%	5000		

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



PS35
Mog.



R40
Med.



R40
Mog.



BR40
Med. Skt.



R40
Med. Skt.

INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
400	G30	Med.	14461-8	(12, 22)	400G/FL	120-130	60	Clear Floodlight	C, C-7A	3	5½	800		6645
500	PAR64	Ext. Mog. End Prong	23417-9	(9, 55)	500PAR64/MFL	120	8	PAR Med. Flood	C, CC-13		6	2000		
			23416-1		500PAR64/NSP	120	8	PAR Narrow Spot	C, CC-13		6	2000		
	PS35	Mog.	14407-1		500	120-130	24	Clear Ratings @120V=442W	C, C-9	7	9%	1000 2830		8900 6755
			14313-1		500/IF	120-130	24	Frost Ratings @120V=442W	C, C-9		9%	1000 2830		8700 6600
			14319-8		500/99	120-130	24	Clear Extended Service Ratings @120V=442W	C, C-9	7	9%	2500 7134		8100 6145
			14318-0		500/99IF	120-130	24	Frost Extended Service Ratings @120V=442W	C, C-9		9%	2500 7134		8000 6080
	PS40	Mog.	14327-1		500	277	24	Clear	C, C-9		9%	1000		7000
	R40	Med.	14430-3	■▲X (31, 37,51,53,12)	500R/3FL/2S	130	24	Swimming Pool Ratings @120V=442W	C, C-7A		6%	2000 5707		6120 4669
R40	Mog.	14434-5	▲ (51, 53)	500R/3FL	120-130	24	Frost Reflector Flood	CC-11		7½	2000		5000	
		14435-2	▲ (51, 53)	500R/3FL	250	24	Frost Reflector Flood Special Svc.	C, C-7A		7½	2000		4700	

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.) ⁽⁹³⁾	Approx. MBCP* [†]	Lumens
INCANDESCENT LAMPS (BY WATTAGE) CONTINUED														
620	PS40	Mog. Pf.	14323-0		620PS40P	120	24	Code Beacon	C, C-7A	5 1/16	10 1/16	3000		9000
LAMPS LISTED BY LUMENS														
1950L	P25	Med. +	14572-2		1950L/P25/TS	120	60	Traffic Signal	C, C-9	3	4 1/4	8000		1950
SPECIAL LIGHTING														
Night Light Plug In			25139-7	(94)	BCPNL 4C7 12/1	120	12	Night Light Plug In	B, C-7A		2 1/8	3000		16
STREET LIGHTING LAMPS, SERIES														
6.6A	PS35	Mog.	14311-5		2500/66R	22.8	24	Clear Extended Service	C, C-2V	7	9 3/8	3000		
			14310-7		4M/66R	34	24	Clear Extended Service	C, C-2V	7	9 3/8	3000		

For the most current product information, go to the e-catalog on www.philips.com
 Incandescent symbols and footnotes located on page 149



INCANDESCENT LAMPS

Decoratives

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens	
3	CA10	Cand.	16698-2	▲	BC3CA10C/CL/LL 6/1	120	6	Clear Long Life Flicker Flame	B, C-7A		4 ¹ / ₁₆	2000			
15	BA9	Cand.	16696-6	▲	BC15BA9C/CL/LL 6/4	120	24	Clear Long Life Bent Tip	B, CC-2V, C-7A		3 ¹ / ₁₆	2000		110	
			16811-2	▲	BC15BA9C/CL/LL 6/2	120	12	Clear Long Life Bent Tip	B, CC-2V, C-7A		4 ¹ / ₁₆	2000		110	
	F10	Cand.	16830-2	▲	BC15F10C/CL/LL 6/2	120	12	Clear Long Life Flame	B, C-7A		3 ¹ / ₁₆	2000		95	
			16831-0	▲	BC15F10C/A/LL 6/2	120	12	Amber Long Life Flame	B, C-7A		3 ¹ / ₁₆	2000		85	
25	BA9	Cand.	16719-7	▲	BC25BA9C/CL/LL 6/4	120	24	Clear Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		150	
			16806-2	▲	BC25BA9C/CL/LL 6/2	120	12	Clear Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		150	
			16810-4	▲	BC25BA9C/F/LL 6/2	120	12	Frost Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		145	
			13823-0	▲	BC25BA9C/CL 6/1 TP	120	6	Clear Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000			
	BA9 ¹ / ₂	Med.	16819-5	▲	BC25BA9 ¹ / ₂ /CL/LL 6/2	120	12	Clear Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		150	
	B10 ¹ / ₂	Cand.	16824-5	▲	BC25B10 ¹ / ₂ /C/CL/LL 6/2	120	12	Clear Long Life Blunt Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		150	
	B13	Med.	16827-8	▲	BC25B13/CL/LL 6/2	120	12	Clear Long Life Blunt Tip	C, C-7A		4 ¹ / ₁₆	2000		150	
	CA8	Cand.	13568-1	▲	BC25CA8C/CL/LL 6/2	120	12	Clear Petite Long Life Bent Tip	C, CC-2V		3 ¹ / ₁₆	2000		220	
	F10	Cand.	16832-8	▲	BC25F10C/CL/LL 6/2	120	12	Clear Long Life Flame	B, C-7A		3 ¹ / ₁₆	2000		105	
	F15	Med.	16833-6	▲	BC25F15/CL/LL 6/2	120	12	Clear Long Life Flame	B, C-9		4 ¹ / ₁₆	2000		150	
			16839-3	▲	BC25F15/IR/LL 6/2	120	12	Iridescent Long Life Flame	C, C-9		4 ¹ / ₁₆	2000		150	
			16841-9	▲	BC25F15/A/LL 6/2	120	12	Amber Long Life Flame	B, C-9		4 ¹ / ₁₆	2000		130	
			16845-0	▲	BC25G16 ¹ / ₂ /C/CL/LL 6/2	120	12	Clear Long Life Globe	B, C-7A		3	2000		200	
	G16 ¹ / ₂	Cand.	16847-6	▲	BC25G16 ¹ / ₂ /CW/LL 6/2	120	12	White Long Life Globe	B, C-7A		3	2000		165	
			Med.	13535-0	▲	BC25G16 ¹ / ₂ /CL/LL 6/2	120	12	Clear Long Life Globe	C, CC-2V		2 ³ / ₁₆	2000		180
				13534-3	▲	BC25G16 ¹ / ₂ /W/LL 6/2	120	12	White Long Life Globe	C, CC-2V		2 ³ / ₁₆	2000		160
40	BA9	Cand.	16720-5	▲	BC40BA9C/CL/LL 6/4	120	24	Clear Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		300	
			16807-0	▲	BC40BA9C/CL/LL 6/2	120	12	Clear Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		300	
			16809-6	▲	BC40BA9C/F/LL 6/2	120	12	Frost Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		295	
		BA9 ¹ / ₂	Med.	16760-1	▲	BC40BA9 ¹ / ₂ /CL/LL 6/4	120	24	Clear Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		300
	16820-3			▲	BC40BA9 ¹ / ₂ /CL/LL	120	12	Clear Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		300	
	16821-1			▲	BC40BA9 ¹ / ₂ /F/	120	12	Frost Long Life Bent Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		295	
		B10 ¹ / ₂	Cand.	16825-2	▲	BC40B10 ¹ / ₂ /C/CL/LL 6/2	120	12	Clear Long Life Blunt Tip	C, CC-2V		4 ¹ / ₁₆	2000		300
	14125-9			▲	BC40B10 ¹ / ₂ /C/N/LL 6/2	120	12	Natural Light Blunt Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		270	
	B13	Med.	16828-6	▲	BC40B13/CL/LL 6/2	120	12	Clear Long Life Blunt Tip	C, C-7A		4 ¹ / ₁₆	2000		300	
				14127-5	▲	BC40B13/N/LL 6/2	120	12	Natural Light Blunt Tip	C, CC-2V, C-7A		4 ¹ / ₁₆	2000		270

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



CA10
Cand.



BA9
Cand.



F10
Cand.



BA9¹/₂
Med.



B10¹/₂
Cand.



B13
Med.



CA8
Cand.



F15
Med.



G16¹/₂
Cand.



G16¹/₂
Med.

INCANDESCENT LAMPS

Decoratives

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP* Lumens
40	F15	Med.	16835-1	▲	BC40F15/CL/LL 6/2	120	12	Clear Long Life Flame	C, C-9		4½	2000	385
			16837-7	▲	BC40F15/IR/LL 6/2	120	12	Iridescent Long Life Flame	C, C-9		4½	2000	370
			16838-5	▲	BC40F15/W/LL 6/2	120	12	White Long Life Flame	C, C-9		4½	2000	300
	G16½	Cand.	16846-8	▲	BC40G16½/C/LL 6/2	120	12	Clear Long Life Globe	C, CC-2V, C-7A		3	2000	300
			16848-4	▲	BC40G16½/C/W/LL 6/2	120	12	White Long Life Globe	C, CC-2V, C-7A		3	2000	245
			14129-1	▲	BC40G16½/C/N/LL 6/2	120	12	Natural Light Globe	C, CC-2V, C-7A		3	2000	270
	G16½	Med.	13537-6	▲	BC40G16½/CL/LL 6/2	120	12	Clear Long Life Globe	C, CC-2V, C-7A		2¾	2000	300
			13536-8	▲	BC40G16½/W/LL 6/2	120	12	White Long Life Globe	C, CC-2V, C-7A		2¾	2000	270
			14876-7	▲	BC40G16½/IR/LL 6/2TP	120	12	Iridescent Long Life Globe	C, CC-2V, C-7A		2¾	2000	270
60	BA9	Cand.	16808-8	▲	BC60BA9C/CL/ 6/2	120	12	Clear Long Life Bent Tip	C, CC-2V, C-7A		4⅞	2000	550
			16721-3	▲	BC60BA9C/CL/LL 6/4	120	24	Clear Long Life Bent Tip	C, CC-2V, C-7A		4⅞	2000	550
			16805-4	▲	BC60BA9C/F/LL 6/2	120	12	Frost Long Life Bent Tip	C, CC-2V, C-7A		4⅞	2000	545
	BA9½	Med.	16822-9	▲	BC60BA9½/CL/LL 6/2	120	12	Clear Long Life Bent Tip	C, CC-2V, C-7A		4⅞	2000	550
			16823-7	▲	BC60BA9½/F/LL 6/2	120	12	Frost Long Life Bent Tip	C, CC-2V, C-7A		4⅞	2000	545
	B10½	Cand.	16826-0	▲	BC60B10½/C/CL/LL 6/2	120	12	Clear Long Life Blunt Tip	C, CC-2V		4⅞	2000	550
	B13	Med.	16829-4	▲	BC60B13/CL/LL 6/2	120	12	Clear Long Life Blunt Tip	C, C-7A		4⅞	2000	550
			14006-1		60B13/CL PRO	130	25	ProPack Clear Blunt Tip	C, C-7A		4⅞	2000	550
	F15	Med.	16842-7	▲	BC60F15/CL/LL 6/2	120	12	Clear Long Life Flame	C, C-9		4½	2000	630
			20471-9	▲	60F15/CL/TG 24/1	120	24	TuffGuard Coated Flame	C, C-9		4½	2000	
	G16½	Cand.	16699-0	▲	BC60G16½/C/LL 6/2	120	12	Clear Long Life Globe	C, CC-2V		3	2000	540
			16700-7	▲	BC60G16½/C/W/LL 6/2	120	12	White Long Life Globe	C, CC-2V		3	2000	450
G16½	Med.	13538-4	▲	BC60G16½/CL/LL 6/2	120	12	Clear Long Life Globe	C, CC-2V		2¾	2000	540	
		13530-1	▲	BC60G16½/W/LL 6/2	120	12	White Long Life Globe	C, CC-2V		2¾	2000	420	
100	F20	Med.	16844-3	▲	100F20/POSTLT/CL/LL 6/1	120	6	Clear Long Life PostLight	C, C-9		5⅞	4000	1250

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



INCANDESCENT LAMPS

Decoratives

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
25	B10½	Cand.	14000-4		25B10-½/C/CL PRO	130	25	ProPack Clear Blunt Tip	C, C-7A, CC-2V	4⅞		2000		150
	BA9	Cand.	14003-8		25BA9C/CL PRO	130	25	ProPack Clear Bent Tip	C, C-7A, CC-2V	4⅞		2000		150
			31090-4	▲	25BA9C	120	25	Clear Bent Tip	C, C-7A, CC-2V	4⅞		4000		135
	G16½	Cand.	31133-2	▲	25G16-½/C/4M	120	25	Clear Globe	C, C-7A		3	4000		170
			14013-7		25G16-½/C/CL PRO	130	25	ProPack Clear Globe	C, C-7A		3	2000		200
40	BA9	Cand.	31093-8	▲	40BA9C/4M	120	25	Clear Bent Tip	C, C-7A, CC-2V	4⅞		4000		270
			14004-6		40BA9C/CL PRO	130	25	ProPack Clear Bent Tip	C, C-7A, CC-2V	4⅞		2000		300
	BA9½	Med.	14070-7		40BA9-½/CL PRO	130	25	ProPack Clear Bent Tip	C, C-7A, CC-2V	4⅞		2000		300
			B10½	Cand.	31115-9	▲	40B10-½/C/4M	120	25	Clear Blunt Tip	C, C-7A	4⅞		4000
	14001-2				40B10-½/C/CL PRO	130	25	ProPack Clear Blunt Tip	C, C-7A, CC-2V	4⅞		2000		300
	G16½	Cand.	31134-0	▲	40G16-½/C/4M	120	25	Clear Globe	C, C-7A, CC-2V		3	4000		250
			14068-1		40G16-½/C/CL PRO	130	25	ProPack Clear Globe	C, C-7A		3	2000		300
	60	BA9	Cand.	31095-3	▲	60BA9C/4M	120	25	Clear Bent Tip	C, C-7A, CC-2V	4⅞		4000	
14005-3					60BA9C/CL PRO	120	25	ProPack Clear Bent Tip	C, C-7A, CC-2V	4⅞		2000		550
BA9½		Med.	31099-5	▲	60BA9-½/4M	120	25	Clear Bent Tip	C, C-7A	4⅞		4000		530
			B10½	Cand.	31116-7	▲	60B10-½/C/4M	120	25	Clear Blunt Tip	C, C-7A	4⅞		4000
14002-0					60B10-½/C/CL PRO	130	25	ProPack Clear Blunt Tip	C, C-7A	4⅞		2000		550

DECORATIVES, ALL OTHERS

25	G25	Med.	16887-2	▲	25G25/CL/LL 12/1	120	12	Clear Long Life Globe	C, CC-6	4⅞		2000		235
			16748-6	▲	25G25/W/LL 12/1	120	12	White Long Life Globe	C, CC-6	4⅞		2000		210
			16901-1	▲	25G25/CL/LL 4/3	120	12	Clear Long Life Globe	C, CC-6	4⅞		2000		235
			16902-9	▲	25G25/W/LL 4/3	120	12	White Long Life Globe	C, CC-6	4⅞		2000		210
			14014-5		25G25/CL PRO	130	12	ProPack Clear Globe	C, CC-6	4⅞		2000		200
40	G25	Med.	16702-3	▲	40G25/CT	120	6	Clear Chrome-Top Long Life Globe	C, C-9	4⅞		2000		200
			16747-8	▲	40G25/CL/LL 12/1	120	12	Clear Long Life Globe	C, CC-6	4⅞		2000		460
			25001-9	▲	40G25/W 120V 12/1	120	12	White Globe	C, CC-6	4⅞		1500		370
			16746-0	▲	40G25/W/LL 12/1	120	12	White Long Life Globe	C, CC-6	4⅞		2000		415
			16903-7	▲	40G25/CL/LL 4/3	120	12	Clear Long Life Globe	C, CC-6	4⅞		2000		460
			16904-5	▲	40G25/W/LL 4/3	120	12	White Long Life Globe	C, CC-6	4⅞		2000		415
			13563-3	▲	40G25/NTL 6/1	120	12	Natural Light Globe	C, CC-6	4⅞		1500		320
			14016-0		40G25/W PRO	130	12	ProPack White Globe	C, CC-6	4⅞		2000		420
			14015-2		40G25/CL PRO	130	12	ProPack Clear Globe	C, CC-6	4⅞		2000		455
	G40	Med.	16857-5	▲	40G40/CL/LL 6/1	120	6	Clear Long Life Globe	C, C-9	6⅞		3000		372
16858-3			▲	40G40/W/LL 6/1	120	6	White Long Life Globe	C, C-9	6⅞		3000		335	

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



B10½
Cand.



BA9
Cand.



G16½
Cand.



BA9½
Med.



G25
Med.



G40
Med.

INCANDESCENT LAMPS

Decoratives

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated		Approx. MBCP* Lumens
												Avg. Life (Hrs.)(93)		
DECORATIVES, ALL OTHERS CONTINUED														
60	G25	Med.	16896-2 ▲		60G25/CL/LL 12/1	120	12	Clear Long Life Globe	C, CC-6		4 ⁵ / ₁₆	2000		775
			16749-4 ▲		60G25/W/LL 12/1	120	12	White Long Life Globe	C, CC-6		4 ⁵ / ₁₆	2000		700
			16899-6 ▲		60G25/CL/LL 4/3	120	12	Clear Long Life Globe	C, CC-6		4 ⁵ / ₁₆	2000		775
			16900-3 ▲		60G25/W/LL 4/3	120	12	White Long Life Globe	C, CC-6		4 ⁵ / ₁₆	2000		700
			14018-6 ▲		60G25/W PRO	130	12	ProPack White Globe	C, CC-6		4 ⁵ / ₁₆	2000		715
	14017-8		60G25/CL PRO	130	12	ProPack Clear Globe	C, CC-6		4 ⁵ / ₁₆	2000		780		
	G30	Med.	16849-2 ▲		60G30/W/LL 6/1	120	6	White Long Life Globe	C, C-9		5 ¹ / ₂	3000		580
	G40	Med.	16851-8 ▲		60G40/W/LL 6/1	120	6	White Long Life Globe	C, C-9		6 ⁵ / ₁₆	3000		595
			16852-6 ▲		60G40/CL/LL 6/1	120	6	Clear Long Life Globe	C, C-9		6 ⁵ / ₁₆	3000		665
			14077-2		60G40/W 6/1 PRO	130	6	ProPack White Globe	C, C-9		6 ⁵ / ₁₆	1500		570
14078-0				60G40/CL 6/1 PRO	130	6	ProPack Clear Globe	C, C-9		6 ⁵ / ₁₆	1500		610	
100	G25	Med.	13423-9 ▲		100G25/W/LL 12/1	120	12	White Long Life Globe	C, CC-6		4 ⁵ / ₁₆	2000		1180
	G30	Med.	16850-0 ▲		100G30/W/LL 6/1	120	6	White Long Life Globe	C, C-9		5 ¹ / ₂	3000		945
	G40	Med.	16853-4 ▲		100G40/W/LL 6/1	120	6	White Long Life Globe	C, C-9		6 ⁵ / ₁₆	3000		985
			16859-1 ▲		100G40/CL/LL 6/1	120	6	Clear Long Life Globe	C, C-9		6 ⁵ / ₁₆	3000		1100

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



INCANDESCENT LAMPS

Tuffguard

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Description	Volts	Pkg. Qty.‡	Rated Avg. Life (Hrs.)(93)	Availability
25	A19	Med.	20178-0	▲	25A1F/TG 130V 24/2	130	24/2	2500	Made to Order
	T10	Med.	20179-8	▲	25T10/TG 120/130V 24/1	120	24	1000	Made to Order
30	R20	Med.	20181-4	▲ (87)	30R20/TG 120V 12/1	120		2000	Made to Order
40	A15	Med.	20182-2	▲	40A15/TG 120/130V 120/1	120	120	1000	Made to Order
	A19	Med.	20183-0	▲	40A/CL/TG 120/130V 48/1	120	48	1500	Made to Order
	T10	Med.	20184-8	▲	40T10/TG 120/130V 24/1	120	24	1000	Stocked
50	R20	Med.	20187-1	✕ ▲ (87)	50R20/TG 120V 12/1	120	12	2000	Made to Order
60	A19	Med.	20188-9		60A19/35/TG 120V 48/1	120	48	3500	Made to Order
			15925-1		60A/35/TG 130V 48/1	120	48	3500	Made to Order
65	BR30	Med.	20190-5	▲ (87)	65BR30/FL55/TG 120V 12/1	120	12	2000	Made to Order
	BR30	Med.	20191-3	▲ (87)	65BR30/FL55/TG 130V 12/1	130	12	2000	Made to Order
75	A19	Med.	20195-4	▲	75A/TG 120V 48/1	120	48	750	Made to Order
			15933-5	▲	75A/TG 130V 48/1	120	48	750	Stocked
	A21	Med.	20018-8	▲	75A/RH/TG 120/130V 12/1	120	12	1000	Stocked
100	A19	Med.	15934-3	▲	100A/TG 130V 48/1	130	48	750	Stocked
	A21	Med.	15927-7		100A/RS/VS/BR/TG 120/130V 60/1	120	60	1000	Stocked
	BR38	Med.	15923-6	(37, 51, 53)	100PAR/1/CL/TG 130V 12/1	130	12	2000	Stocked
	A21	Med.	20197-0	▲	100A21/TG 120/130V 120/1	120	120	750	Made to Order
120	BR40	Med.	20198-8	▲	100A21/99/TG 120/130V 60/1	120	60	2500	Made to Order
			20199-6	✕ ▲ (87)	120BR/FL60/TG 130V 24/1	130	24	2000	Stocked
125	BR40	Med.	20200-2	✕ ▲ (87)	120BR/FL60/TG 120V 24/1	120	24	2000	Made to Order
			15930-1	✕ (27, 87, 89)	125BR40/1/TG 120V 4/1	120	4	5000	Stocked
150	A21	Med.	15931-9		150A/35/RS/BR/TG 120/130V 60/1	120	60	3500	Stocked
	BR38	Med.	20203-6	✕ (37, 51, 53)	150BR38/FL/TG 130V 6/1	130	6	2000	Stocked

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149

