


Decorator Devices Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC


Pass & Seymour



Features	
<ul style="list-style-type: none"> Meets 2006 UL requirements. SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red lamp). Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Two back wire holes per terminal. 	<ul style="list-style-type: none"> Ground screw has a back wire clamp for easy installation. 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. Mounting screws are shipped captive in the device and wall plate for easier installation. High-impact-resistant thermoplastic construction. Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws.
Specifications	
<ul style="list-style-type: none"> Supply Voltage: 125VAC, 60 Hz Supply Voltage Range: 102-132VAC Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> Trip Time: 0.025 sec., nominal per UL Standard 20 Amp feed-thru capacity



1595-HGW



2095-HGW


Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
Hospital Grade 15 Amp Duplex GFCI							
1595-HGI	15	125	Ivory	5-15R	•	•	•
1595-HGW	15	125	White	5-15R	•	•	•
1595-HG	15	125	Brown	5-15R	•	•	•
1595-HGGRY	15	125	Gray	5-15R	•	•	•
1595-HGRED	15	125	Red	5-15R	•	•	•
1595-HGLA	15	125	Light Almond	5-15R	•	•	•
Hospital Grade 20 Amp Duplex GFCI							
2095-HGI	20	125	Ivory	5-20R	•	•	•
2095-HGW	20	125	White	5-20R	•	•	•
2095-HG	20	125	Brown	5-20R	•	•	•
2095-HGGRY	20	125	Gray	5-20R	•	•	•
2095-HGRED	20	125	Red	5-20R	•	•	•
2095-HGLA	20	125	Light Almond	5-20R	•	•	•

NEW

NEW


Available Spring 2006.

For Configurable Solutions, see Page U-1.




Decorator Devices Illuminated GFCI Receptacles



2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1595-WL



2095-HGWL



Features

- Green indicator light is ON when power is available. Helps identify emergency power branch circuits.
- Meets 2006 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Time: 0.025 sec., nominal per UL Standard
- Trip Threshold: 5± 1mA
- 20 Amp feed-thru capacity

NEW

NEW

NEW

NEW

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
TradeMaster®/Spec Grade Illuminated 15 Amp Duplex GFCI							
1595-IL	15	125	Ivory	5-15R	•	•	•
1595-WL	15	125	White	5-15R	•	•	•
1595-L	15	125	Brown	5-15R	•	•	•
1595-LAL	15	125	Light Almond	5-15R	•	•	•
Specification Grade Illuminated 20 Amp Duplex GFCI							
2095-IL	20	125	Ivory	5-20R	•	•	•
2095-WL	20	125	White	5-20R	•	•	•
2095-L	20	125	Brown	5-20R	•	•	•
2095-GRYL	20	125	Gray	5-20R	•	•	•
2095-LAL	20	125	Light Almond	5-20R	•	•	•
Hospital Grade Illuminated 15 Amp Duplex GFCI							
1595-HGIL	15	125	Ivory	5-15R	•	•	•
1595-HGWL	15	125	White	5-15R	•	•	•
1595-HGL	15	125	Brown	5-15R	•	•	•
1595-HGGRYL	15	125	Gray	5-15R	•	•	•
1595-HGREDL	15	125	Red	5-15R	•	•	•
1595-HGLAL	15	125	Light Almond	5-15R	•	•	•
Hospital Grade Illuminated 20 Amp Duplex GFCI							
2095-HGIL	20	125	Ivory	5-20R	•	•	•
2095-HGWL	20	125	White	5-20R	•	•	•
2095-HGL	20	125	Brown	5-20R	•	•	•
2095-HGGRYL	20	125	Gray	5-20R	•	•	•
2095-HGREDL	20	125	Red	5-20R	•	•	•
2095-HGLAL	20	125	Light Almond	5-20R	•	•	•

Available Spring 2006.

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.