


1595, 2095, 1595-S, 2095-S, 1595-NTL, 2095-NTL, 1595-TR, 2095-TR, 1595-L, 2095-L

Durability and protection that exceeds the 2006 UL standard.

Patented SafeLock™ protection denies power if the GFCI is miswired or if the GFCI is damaged and protection is lost. This prevents the unsafe condition of power without protection. P&S has the broadest range of ground-fault protection, with the first LED Nightlight/GFCI Combination, and the first Tamper-Resistant GFCI, in addition to Auto-Ground and Illuminated versions.



For Hospital Grade GFCIs, refer to SF1102R4.

Features & Benefits

SafeLock™ Protection denies power if the GFCI is miswired or if the GFCI is damaged and protection is lost. This prevents the unsafe condition of power without protection.

Back wire clamp allows for fast installation of ground wires.

Two back wire holes per termination add wiring flexibility, eliminate pigtail and save box space.

Nickel post-plated mounting strap for superior corrosion resistance.

Trip indicator light (red lamp) makes it easy to identify tripped condition.


Side or internal screw-pressure-plate back wire termination with #14 – #10 AWG stranded or solid, copper or copper-clad conductors.

Captive screws make for easier installation.

Prevents line-load reversal miswire: No power to the face or downstream receptacles if wired incorrectly.

High-impact-resistant, thermoplastic construction for superior strength and durability.

1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.



Meets 2006 UL requirements.

2095-LA






The most durable GFCI available. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.


Field Uses/Vertical Markets

- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

GFCIs Specification Grade 15 & 20A, 125VAC

Ordering Information

Additional Features & Benefits	Catalog Number	Rating A.	VAC	Color	NEMA Config. No.
GFCI Receptacles					
 <p>Patented SafeLock™ Protection is standard on all P&S Specification Grade GFCIs.</p>	1595-*	15	125	I, W, Brown, GRY, BK, RED, LA	5-15R
	2095-*	20	125	I, W, Brown, GRY, BK, RED, LA	5-20R
GFCI with Auto-Ground Receptacles					
 <p>Auto-ground clip assures positive ground to metal box.</p>	1595-S*	15	125	I, W, LA	5-15R
	2095-S*	20	125	I, W, LA	5-20R
Combination Nightlight/GFCI Receptacles					
 <p>High impact-resistant lens made of Lexan®. Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement. Photocell turns nightlight ON in dark, OFF in daylight.</p>	1595-NTL*CC4	15	125	I, W, BK, LA	5-15R
	2095-NTL*	20	125	I, W, GRY, RED, LA	5-20R
Tamper-Resistant GFCI Receptacles					
 <p>Dual mechanical shutter system to help prevent insertion of foreign objects. Patented UL Listed shutter system.</p>	1595-TR*CC4	15	125	I, W, BK, LA	5-15R
	2095-TR*	20	125	I, W, Brown, GRY, BK, RED, LA	5-20R
Illuminated GFCI Receptacles					
 <p>Green indicator light ON when power is available. LED turns OFF when unit has tripped or power has failed.</p>	1595-*L	15	125	I, W, Brown, LA	5-15R
	2095-*L	20	125	I, W, Brown, GRY, LA	5-20R



***Color Designation**

I Ivory - Brown BK Black LA Light Almond
W White GRY Gray RED Red

For more information on these and other P&S products refer to our Catalog or visit our web site.

GFCIs Specification Grade 15 & 20A, 125VAC



Pass & Seymour

Technical Specifications

3rd Party Compliance
cULus Listed File Number E42190, Standard UL498 Attachment Plugs and Receptacles, UL943 GFCIs. Federal Specification WC596. Standard CSA C22.2 No. 42 General Use Receptacles, CSA C22.2 No. 144 GFCIs. Conforms to NEMA WD-1 and WD-6.


Performance	
Electrical	
Dielectric Voltage	Withstands 1500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Maximum Working Voltage	125VAC
Voltage Range	102-132VAC
Mechanical	
Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG solid or stranded copper conductor only
Product Identification	Ratings are a permanent part of device
Environmental	
Operating Temperature	-35°C to +66°C
Maximum Humidity	95%
Flammability	UL94 V2

Materials			
Face	Nylon	Hex Head Grounding Screw	Steel (Green)
Body	Nylon	Flat Head Mounting Screws	Zinc-Plated Steel
Contacts	.03" Brass (.8)	Test/Reset Buttons	Nylon
Mounting Straps	.05" Nickel-Plated Steel (1.3)	Auto-Ground Clip	* Brass Alloy C260
Terminal Screws	Nickel-Plated Steel #8 - 32	Nightlight Lens	** Lexan®
		Tamper-Resistant Shutter	*** Thermoplastic

* For 1595-S and 2095-S Auto-Ground versions only.
 ** For 1595-NLT and 2095-NLT Nightlight versions only.
 *** For 1595-TR and 2095-TR Tamper-Resistant versions only.

Warranty

1 Year



**Dimensions for
15 & 20 Amp**



Auto-Ground



Nightlight/GFCI




Illuminated



Tamper-Resistant

Complimentary Devices & Accessories




GFCIs

- Hospital Grade
- Dead Front




HOSPITAL GRADE DEVICES

- Receptacles, Tamper-Resistant, Decorator
- GFCIs
- TVSS
- Isolated Ground
- Plugs & Connectors




DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- PlugTail™ Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF1101R4 — Updated March 2006 — For latest specs visit www.legrand.us/passandseymour