

# **Electrical Specifications**

REL-3P32-SC			
Brand Name	STANDARD ELEC		
Ballast Type	Electronic		
Starting Method	Instant Start		
Lamp Connection	Parallel		
Input Voltage	120		
Input Frequency	60 HZ		
Status	Active		

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (°F/C)	Input Current (Amps)	Input Power (ANSI Watts)	Ballast Factor	MAX THD %	Power Factor	MAX Lamp Current Crest Factor	B.E.F
F17T8	3	17	0/-18	0.39	47	0.99	20	0.99	1.7	2.11
F25T8	2	25	0/-18	0.42	54	1.06	20	0.99	1.7	1.96
F25T8	3	25	0/-18	0.55	66	0.93	20	0.99	1.7	1.41
* F32T8	2	32	0/-18	0.54	65	1.03	20	0.99	1.7	1.58
F32T8	3	32	0/-18	0.71	85	0.88	20	0.99	1.7	1.04
F32T8/ES (30W)	2	30	60/16	0.51	61	1.03	20	0.99	1.7	1.69
F40T8	2	40	0/-18	0.66	79	1.01	20	0.99	1.7	1.28

# Wiring Diagram WHITE BLUE BLUE RED BLUE BALLAST BLUE BLUE

Diag. 70 Insulate unused blue

The wiring diagram that appears above is for the lamp type denoted by the asterisk (\*)

LAMP


Standard Lead Length (inches)

	in.	cm.
Black	25L	63.5
White	25R	63.5
Blue	31R	78.7
Red	37L	94
Yellow		0
Gray		0
Violet		0

LINE

in.	cm.
	0
	0
	0
	0
	0
	0
	0
	in.

# **Enclosure**



## **Enclosure Dimensions**

OverAll (L)	Width (W)	Height (H)	Mounting (M)
9.50 "	1.7 "	1.18 "	8.90 "
9 1/2	1 7/10	1 9/50	8 9/10
24.1 cm	4.3 cm	3 cm	22.6 cm

### Revised 05/14/2009





Data is based upon tests performed by Philips Lighting Electronics N.A. in a controlled environment and is representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.



# **Electrical Specifications**

REL-3P32-SC				
Brand Name	STANDARD ELEC			
Ballast Type	Electronic			
Starting Method	Instant Start			
Lamp Connection	Parallel			
Input Voltage	120			
Input Frequency	60 HZ			
Status	Active			

#### Notes:

#### Section I - Physical Characteristics

- 1.1 Ballast shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable,
- 1.2 Ballast shall be provided with integral leads color-coded per ANSI C82.11.

# Section II - Performance Requirements

- 2.1 Ballast shall be \_\_\_\_\_ (Instant or Rapid) Start.
- 2.2 Ballast shall provide Independent Lamp Operation (ILO) for Instant Start ballasts allowing remaining lamp(s) to maintain full light output when one or more lamps fail.
- 2.3 Ballast shall contain auto restart circuitry in order to restart lamps without resetting power.
- 2.4 Ballast shall operate from 60 Hz input source of 120V, 277V or 347V as applicable with sustained variations of +/- 10% (voltage and frequency).
- 2.5 Ballast shall be high frequency electronic type and operate lamps at a frequency between 20 kHz and 30 kHz or above 42 kHz to avoid interference with infrared devices and eliminate visible flicker.
- 2.6 Ballast shall have a Power Factor greater than 0.98 for primary lamp.
- 2.7 Ballast shall have a minimum ballast factor for primary lamp application as follows: 0.75 for Low Watt, 0.85 for Normal Light Output and 1.20 for High Light.
- 2.8 Ballast shall provide for a Lamp Current Crest Factor of 1.7 or less.
- 2.9 Ballast input current shall have Total Harmonic Distortion (THD) of less than 20% for Standard models and THD of less than 10% for Centium models when operated at nominal line voltage with primary lamp.
- 2.10 Ballast shall have a Class A sound rating for all 4-foot lamps and smaller.
- 2.11 Ballast shall have a minimum starting temperature of \_\_\_\_\_\_ [-18C (0F) for standard T8 lamps, 10C (50F) for T8/HO, standard T12, Slimline T12 and Long Twin Tube lamps, 0C (32F) for Slimline T8, -29C (-20F) for T12/HO lamps,] for primary lamp application. Ballast shall have a minimum starting temperature of 60F (16C) for energy-saving lamps.
- 2.12 Ballast shall tolerate sustained open circuit and short circuit output conditions.

# Section III - Regulatory Requirements

- 3.1 Ballast shall not contain any Polychlorinated Biphenyl (PCB).
- 3.2 Ballast shall be Underwriters Laboratories (UL) listed, Class P and Type 1 Outdoor; and Canadian Standards Association (CSA) certified where applicable.
- 3.3 Ballast shall comply with ANSI C62.41 Category A for Transient protection.
- 3.4 Ballast shall comply with ANSI C82.11 where applicable.
- 3.5 Ballast shall comply with the requirements of the Federal Communications Commission (FCC) rules and regulations, Title 47 CFR part 18, Non-Consumer (Class A) for EMI/RFI (conducted and radiated).
- 3.6 Ballast shall comply with NEMA 410 for in-rush current limits.

#### Section IV - Other

- 4.1 Ballast shall be manufactured in a factory certified to ISO 9001 Quality System Standards.
- 4.2 Ballast shall carry a five-year warranty from date of manufacture against defects in material or workmanship, including replacement, for operation at a maximum case temperature of 70C.
- 4.3 Manufacturer shall have a twenty-year history of producing electronic ballasts for the North American market.

Note: Energy saving T8 lamps (25W, 28W or 30W) may experience lamp striations if operated on ballasts not rated for their use.

#### Revised 05/14/2009





Data is based upon tests performed by Philips Lighting Electronics N.A. in a controlled environment and is representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.

# PHILIPS LIGHTING ELECTRONICS N.A.