



USB Charging Devices Quad USB Chargers 15A & 20A, 125V

TM8USB4

Quad USB Chargers designed with safety and reliability in mind.

The new **Pass & Seymour**® Quad USB Chargers are designed to charge four mobile devices simultaneously. These devices are intended for the commercial and residential markets and boast a slim 1.3" design to fit easily into any standard electrical box. This product features an overall 4.2A USB charging capability and screw-pressure-plate back wiring makes installation fast and easy.



FEATURES & BENEFITS

Overall 4.2A total charging capability – Four 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

Slim 1.3" depth fits easily into any box.

Accepts standard wallplates.



TM8USB4LACC6

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid wire.

Zinc-plated ground terminal screw.

FIELD USES/VERTICAL MARKETS

- Health Care
- Education
- Airports



USB Charging Devices Quad USB Chargers 15A & 20A, 125V

ORDERING INFORMATION

Catalog Number	VDC Rating	Color	Charging Capacity (Amps)
Quad USB Chargers			
TM8USB4BKCC6	5	Black	4.2
TM8USB4ICC6	5	Ivory	4.2
TM8USB4LACC6	5	Light Almond	4.2
TM8USB4NICC6	5	Nickel	4.2
TM8USB4WCC6	5	White	4.2

For more information on these and other P&S products refer to our Catalog or visit our web site.

SF20135 — Updated December 2013 — For latest specs visit www.legrand.us/passandseymour

USB Charging Devices Quad USB Chargers 15A & 20A, 125V



TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed.
Complies with test requirements UL1310.

Performance

Electrical


Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125VAC input, 5VDC, 4.2A output
No Load Power	.04 Watts

Mechanical

Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG copper conductor only
Product Identification	Ratings are permanent part of the device

Environmental

Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C



Materials

Face	Polycarbonate
Body	Polycarbonate
Contacts	CDA 260 Brass
Mounting Strap	.049" Zinc-Plated Steel
Terminal Screws	Tri-Drive Zinc Plated Steel with Either Clear or Yellow Chromate for color identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel

Warranty

1 Year

For more information on these and other P&S products refer to our Catalog or visit our web site.

SF20135 — Updated December 2013 — For latest specs visit www.legrand.us/passandseymour

COMPLEMENTARY DEVICES & ACCESSORIES



TURNLOK® LOCKING DEVICES

- Heavy-Duty Receptacles
- Heavy-Duty Flanged Inlets & Outlets




GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok®



STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use
- Heavy-Duty MaxGrip® M³



SPD & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok® Isolated Ground
- Heavy-Duty Isolated Ground SPD
- Heavy-Duty SPD
- Construction Grade SPD



IEC 309 INDUSTRIAL PRODUCTS

- Fusible & Non-Fusible Mechanical Interlocks
- Fusible & Non-Fusible Safety Switches
- Pin & Sleeve Devices

ALSO AVAILABLE...

- Hospital Grade Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Bulk Solutions



Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour
570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone: 905.738.9195
www.legrand.ca

