



BR30 DimTone LED

9.5BR30/F90 2200-2700 DIM 6/1

Philips BR30 DimTone Dimmable LED Lamps with AirFlux Technology provide a soft, diffused level of light and smooth dimming from 2700K to 2200K to create a warm inviting atmosphere.

Product data

• General Characteristics

Cap-Base	E26
Bulb	BR30
Rated Avg. Life (Hours)	25000 hr

• Light Technical Characteristics

Color Code	WW
Color Designation	Warm White
Beam Angle	90 D
Beam Description	90D [Flood]
Correlated Color Temperature	2700 K
CRI	80
Luminous Efficacy Lamp	76.84 Lm/W
Color Temp. (Kelvin)	2700 K [CCT 2700K]
Rated Luminous Flux	730 Lm

• Electrical Characteristics

Wattage	9.5 W
Wattage Technical	9.5 W
Voltage	120 V
Line Frequency	60 Hz
Power Factor	0.85 -
Lamp Current mA	95 mA
Dimmable	Yes
Wattage Equivalent	65 W

Starting Time	0.5 (max) s
---------------	-------------

• Environmental characteristics

Energy consumption kWh/1000h	10 kWh
------------------------------	--------

• Measuring Conditions

Switching cycle	15000X
-----------------	--------

• Product Dimensions

Overall Length C	131 mm
Diameter D	95 mm

• Product Data

Product number	452243
Product number (full)	452243
Full product name	9.5BR30/F90 2200-2700 DIM 6/1
Short product name	9.5BR30/F90 2200-2700 DIM 6/1
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677452247
Bar code on case	50046677452242
Logistics code(s)	929001111704
eop_net_weight_pp	0.001 kg




PHILIPS

BR30 DimTone LED

Warnings and Safety

- Suitable for use in damp locations.
- Do not use in outdoor fixtures.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.

Dimensional drawing



9.5BR30/F90 2200-2700 DIM 6/1



E26



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, April 15
data subject to change