



# LED InstantFit Lamps

16.5PL-LED/24-4000 IF 10/1

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

## Product data

### • General Information

Cap-Base	2G11 [ 2G11]
Main Application	Industrial
Nominal Lifetime (Nom)	40000 h
Switching Cycle B50L70	50000X 40000

### • Light Technical

Color Code	840 [ CCT of 4000K (841)]
Beam Angle (Nom)	160 °
Luminous Flux (Rated) (Nom)	2100 lm
Rated Beam Angle	160 °
Correlated Color Temperature (Nom)	4000 K
Color Consistency	6 steps
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

### • Operating and Electrical

Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	16.5 W
Starting Time (Max)	0.5 s
Warm Up Time To 60% Light (Nom)	instant full light
Power Factor (Min)	0.9
Voltage (Nom)	120-277 V

### • Temperature

T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	65 °C

### • Controls and Dimming

Dimmable	No
----------	----

### • Mechanical and Housing

Product Length	500 mm
----------------	--------

### • Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Efficiency Label (EEL)	A+
Approval Marks	CE marking UL certificate RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	21 kWh

### • Product Data

Order product name	16.5PL-LED/24-4000 IF 10/1
EAN/UPC - Product	046677456658
Order code	929001151504

# PHILIPS

# LED InstantFit Lamps

Numerator - Quantity Per Pack 1  
 Numerator - Packs per outer box 10


Material Nr. (12NC) 929001151504  
 Net Weight (Piece) 0.170 kg

## Warnings and Safety

- Philips LED T8 InstantFit lamps will only operate properly on compatible instant-start ballasts. Please refer to the Philips LED T8


InstantFit Installation Guide, which can be obtained through your local Philips Sales Representative, or visit [www.philips.com/tled](http://www.philips.com/tled)

## Dimensional drawing




### LEDtube 500mm 16.5W/840

Product	D1	D2	A1	A2	A3
16.5PL-LED/24-4000 IF 10/1	33 mm	43.6 mm	564.0 mm	570.6 mm	570.6 mm



## Photometric data





© 2016 Philips Lighting Holding B.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2016, April 22  
data subject to change