

# PL-T Triple 4-Pin Base

#### PL-T 26W/827/A/4P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum effciency and sleek design solutions are required.

#### Product data

#### • General Information

Cap-Base GX24Q-3 [ GX24q-3]

#### • Light Technical

Color Code 827 [ CCT of 2700K] Initial lumen (Nom) 1750 lm Luminous Flux 1750 lm (Rated) (Nom) Color Designation Incandescent White Chromaticity Coor-453 dinate X (Nom) 418 Chromaticity Coordinate Y (Nom) Correlated Color 2700 K Temperature (Nom) Luminous Efficacy 64.8 lm/W (rated) (Nom) 82 Color Rendering Index (Nom)

### • Operating and Electrical

Power (Rated) 27.0 W (Nom)
Lamp Current (Nom) 0.335 A

#### • Temperature

Design Temperature 28 °C (Nom)

· Controls and Dimming

Dimmable Yes

Mechanical and Housing

Cap-Base Information 4P

#### • Approval and Application

Energy Efficiency B Label (EEL) Mercury (Hg) 1.4 mg Content (Nom)


#### • Product Data

Order product name PL-T 26W/827/A/4P/ALTO EAN/UPC - Product 046677384401 Order code 458240 Numerator - Quantity Per Pack Numerator - Packs 10 per outer box Material Nr. (12NC) 927910982750 Net Weight (Piece) 64.000 g FSM-26/27/1B-E-GX24q=3 ILCOS Code



# PL-T Triple 4-Pin Base

# Dimensional drawing



## PL-T ALTO 26W/827/4P A

 Product
 D
 A
 B
 C

 PL-T 26W/827/A/4P/ALTO
 41 mm
 86.7 mm
 111.0 mm
 126.7 mm



# Photometric data

