

Datasheet

Art.No. 80.010.4106.0

Relay module FLARE-12DC-1W-250V6A-F

flare, mechanical relays with 6,2 mm overall width, 1 change-over contact, spring clamp terminal, input: 12 V DC, output: 250V AC / 6A, voltage / current minimum: 24V / 8mA, jumper At negative pole At the controll side commen contact, type: flare 12DC 1W 250V6A-F



Art.No.	80.010.4106.0
EAN	4015573632240
Order unit	10 pieces

Approvals



Technical data

General

Connection type	Tension clamp connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

Technical data

Type of excitation	
Nominal voltage DC	12 V
Lower nominal voltage DC	9.96 V
Upper nominal voltage DC	15 V

Dimensions

Depth	70 mm
Width	6.2 mm
Height	98 mm