

FSSEZ FluxStream strip EZ LED

4', 4000 lumens

Photometry

4' FluxStream EZ strip LED, 4000 nominal delivered lumens

LER - 114

<p>Catalog No. FSSEZ440L840-UNV Test No. 37445 S/MH 1.3 Lamp Type LED Lumens 3653 Input Watts 32</p> <p>Comparative yearly lighting energy cost per 1000 lumens – \$2.11 based on 3000 hrs. and \$.08 pwr KWH.</p> <p>The photometric results were obtained in the Philips Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.</p> <p>Photometric values based on test performed in compliance with LM-79.</p>	<p>Candlepower</p> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45</th> <th>Cross</th> <th>Back-45</th> </tr> </thead> <tbody> <tr><td>0</td><td>1050</td><td>1050</td><td>1050</td><td>1050</td></tr> <tr><td>5</td><td>1031</td><td>1045</td><td>1053</td><td>1045</td></tr> <tr><td>15</td><td>989</td><td>1010</td><td>1025</td><td>1010</td></tr> <tr><td>25</td><td>904</td><td>938</td><td>967</td><td>938</td></tr> <tr><td>35</td><td>786</td><td>837</td><td>881</td><td>837</td></tr> <tr><td>45</td><td>647</td><td>726</td><td>782</td><td>726</td></tr> <tr><td>55</td><td>493</td><td>587</td><td>667</td><td>587</td></tr> <tr><td>65</td><td>309</td><td>421</td><td>545</td><td>421</td></tr> <tr><td>75</td><td>155</td><td>303</td><td>398</td><td>303</td></tr> <tr><td>85</td><td>29</td><td>204</td><td>298</td><td>204</td></tr> </tbody> </table>	Angle	End	45	Cross	Back-45	0	1050	1050	1050	1050	5	1031	1045	1053	1045	15	989	1010	1025	1010	25	904	938	967	938	35	786	837	881	837	45	647	726	782	726	55	493	587	667	587	65	309	421	545	421	75	155	303	398	303	85	29	204	298	204	<p>Light Distribution</p> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>817</td><td>22.4</td></tr> <tr><td>0-40</td><td>1341</td><td>36.7</td></tr> <tr><td>0-60</td><td>2416</td><td>66.1</td></tr> <tr><td>0-90</td><td>3357</td><td>91.9</td></tr> <tr><td>90-180</td><td>296</td><td>8.1</td></tr> <tr><td>0-180</td><td>3653</td><td>100</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	817	22.4	0-40	1341	36.7	0-60	2416	66.1	0-90	3357	91.9	90-180	296	8.1	0-180	3653	100	<p>Average Luminance</p> <table border="1"> <thead> <tr> <th>Zone</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>13707</td><td>11958</td><td>11915</td></tr> <tr><td>55</td><td>12754</td><td>10817</td><td>11115</td></tr> <tr><td>65</td><td>10675</td><td>9122</td><td>10361</td></tr> <tr><td>75</td><td>8488</td><td>8267</td><td>9143</td></tr> <tr><td>85</td><td>4081</td><td>7810</td><td>8995</td></tr> </tbody> </table>	Zone	End	45°	Cross	45	13707	11958	11915	55	12754	10817	11115	65	10675	9122	10361	75	8488	8267	9143	85	4081	7810	8995																																																																										
Angle	End	45	Cross	Back-45																																																																																																																																																																													
0	1050	1050	1050	1050																																																																																																																																																																													
5	1031	1045	1053	1045																																																																																																																																																																													
15	989	1010	1025	1010																																																																																																																																																																													
25	904	938	967	938																																																																																																																																																																													
35	786	837	881	837																																																																																																																																																																													
45	647	726	782	726																																																																																																																																																																													
55	493	587	667	587																																																																																																																																																																													
65	309	421	545	421																																																																																																																																																																													
75	155	303	398	303																																																																																																																																																																													
85	29	204	298	204																																																																																																																																																																													
Degrees	Lumens	% Luminaire																																																																																																																																																																															
0-30	817	22.4																																																																																																																																																																															
0-40	1341	36.7																																																																																																																																																																															
0-60	2416	66.1																																																																																																																																																																															
0-90	3357	91.9																																																																																																																																																																															
90-180	296	8.1																																																																																																																																																																															
0-180	3653	100																																																																																																																																																																															
Zone	End	45°	Cross																																																																																																																																																																														
45	13707	11958	11915																																																																																																																																																																														
55	12754	10817	11115																																																																																																																																																																														
65	10675	9122	10361																																																																																																																																																																														
75	8488	8267	9143																																																																																																																																																																														
85	4081	7810	8995																																																																																																																																																																														
		<p>Coefficients of Utilization</p> <p>EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)</p> <table border="1"> <thead> <tr> <th rowspan="2">pfc =</th> <th colspan="2">20</th> <th colspan="2">30</th> <th colspan="2">50</th> <th colspan="2">70</th> <th colspan="2">80</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> </tr> </thead> <tbody> <tr><td>Ceil</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> <tr><td>Wall</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> <tr><td>RCR</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> <tr><td>0</td><td>117</td><td>117</td><td>117</td><td>113</td><td>113</td><td>113</td><td>107</td><td>107</td><td></td><td></td></tr> <tr><td>1</td><td>105</td><td>98</td><td>93</td><td>101</td><td>95</td><td>92</td><td>91</td><td>86</td><td></td><td></td></tr> <tr><td>2</td><td>94</td><td>85</td><td>78</td><td>91</td><td>82</td><td>76</td><td>78</td><td>72</td><td></td><td></td></tr> <tr><td>3</td><td>85</td><td>75</td><td>66</td><td>82</td><td>72</td><td>65</td><td>68</td><td>61</td><td></td><td></td></tr> <tr><td>4</td><td>79</td><td>66</td><td>56</td><td>76</td><td>64</td><td>56</td><td>60</td><td>53</td><td></td><td></td></tr> <tr><td>5</td><td>71</td><td>58</td><td>48</td><td>68</td><td>56</td><td>47</td><td>54</td><td>46</td><td></td><td></td></tr> <tr><td>6</td><td>67</td><td>53</td><td>44</td><td>64</td><td>51</td><td>42</td><td>48</td><td>40</td><td></td><td></td></tr> <tr><td>7</td><td>61</td><td>47</td><td>39</td><td>58</td><td>46</td><td>38</td><td>44</td><td>36</td><td></td><td></td></tr> <tr><td>8</td><td>56</td><td>44</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>33</td><td></td><td></td></tr> <tr><td>9</td><td>54</td><td>40</td><td>32</td><td>52</td><td>39</td><td>30</td><td>36</td><td>29</td><td></td><td></td></tr> <tr><td>10</td><td>50</td><td>37</td><td>29</td><td>48</td><td>36</td><td>28</td><td>34</td><td>27</td><td></td><td></td></tr> </tbody> </table>	pfc =	20		30		50		70		80		70	50	30	70	50	30	50	30	70	50	Ceil											Wall											RCR											0	117	117	117	113	113	113	107	107			1	105	98	93	101	95	92	91	86			2	94	85	78	91	82	76	78	72			3	85	75	66	82	72	65	68	61			4	79	66	56	76	64	56	60	53			5	71	58	48	68	56	47	54	46			6	67	53	44	64	51	42	48	40			7	61	47	39	58	46	38	44	36			8	56	44	34	55	41	34	40	33			9	54	40	32	52	39	30	36	29			10	50	37	29	48	36	28	34	27		
pfc =	20			30		50		70		80																																																																																																																																																																							
	70	50	30	70	50	30	50	30	70	50																																																																																																																																																																							
Ceil																																																																																																																																																																																	
Wall																																																																																																																																																																																	
RCR																																																																																																																																																																																	
0	117	117	117	113	113	113	107	107																																																																																																																																																																									
1	105	98	93	101	95	92	91	86																																																																																																																																																																									
2	94	85	78	91	82	76	78	72																																																																																																																																																																									
3	85	75	66	82	72	65	68	61																																																																																																																																																																									
4	79	66	56	76	64	56	60	53																																																																																																																																																																									
5	71	58	48	68	56	47	54	46																																																																																																																																																																									
6	67	53	44	64	51	42	48	40																																																																																																																																																																									
7	61	47	39	58	46	38	44	36																																																																																																																																																																									
8	56	44	34	55	41	34	40	33																																																																																																																																																																									
9	54	40	32	52	39	30	36	29																																																																																																																																																																									
10	50	37	29	48	36	28	34	27																																																																																																																																																																									

Accessories



Accessory Catalog Code	Description	
FSTH	Sliding hanger bracket (pair)	
SV5F12	12" Stem and canopy kit	White stem and canopy kit, 1/4" trade size (1/2" O.D.) locknuts included. Works with 9/16" k.O. on base of housing.
SV5F18	18" Stem and canopy kit	
SV5F24	24" Stem and canopy kit	
SV5F36	36" Stem and canopy kit	
SV5F48	48" Stem and canopy kit	
FKR-126	Chain hanger set (pair)	Includes two 5' heavy duty link chains with "V" hooks. Attaches to base of housing.
DACHxx	Adjustable cable hanger kit (single)	Works with 1/4" hole on base of housing or FSTH hanger bracket. xx=cable length in inches, enter 48" to 180" lengths in 12" increments
DACHxx-1-SC	Adjustable cable hanger kit with white straight 18/3 cord (single)	
DACHxx-1-CC	Adjustable cable hanger kit with white coiled 18/3 cord (single)	
DACHxx-2-SC	Adjustable cable hanger kit with white straight 18/4 cord (single)	
DACHxx-2-CC	Adjustable cable hanger kit with white coiled 18/4 cord (single)	
LSXR10	Low bay pir motion sensor (120-277v)	
FSSWG4	4' Wire guard	
FSSD4L	4' Diffuse replacement lens	

© 2017 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. philips.com/luminaires



Philips Lighting North America Corporation
 200 Franklin Square Drive, Somerset, NJ 08873
 Tel. 855-486-2216

Philips Lighting Canada Ltd.
 281 Hillmount Rd, Markham, ON, Canada L6C 2S3
 Tel. 800-668-9008