


## Datasheet

Art.No. 57.904.5755.0

Fuse terminal WK 4/THSI5 GL 250U /V0

Fuse terminal block with screw connection for mounting on TS 35 and TS 32, nominal cross section 4 mm<sup>2</sup>, width 6 mm, color gray



Art.No.	57.904.5755.0
EAN	4015573528338
Order unit	50 pieces

## Approvals



## Technical data

### General

Nominal cross section	4 mm <sup>2</sup>
Colour	Grey
Number of levels	1
Width/grid dimension	8 mm
Insulating housing	PA666
Inflammability class of insulation material acc. with UL94	V0
Mounting method	DIN rail (top hat rail)/G-rail
Terminal blocks for electrical installations	No
Fuse insert	G-fuse 5x30 mm

### Technical data

Rated current	6.3 A
Rated voltage	250 V
Rated impulse voltage	8 kV
Pollution degree	3
Closing plate required	No
Type of insulation material	Thermoplastic
Length	77.2 mm

### Connection Data

Connection type 1	Screw connection
Connection type 2	Screw connection
Minimum cross section solid	0.5 mm <sup>2</sup>

Maximum cross section solid	6 mm <sup>2</sup>
Minimum cross section fine stranded	0.5 mm <sup>2</sup>
Maximum cross section fine stranded	4 mm <sup>2</sup>
Wire strip length	8 mm
Torque conductor mounting	0.5 Nm

#### Technical Data UL/CSA

Cross section UL	22-10 AWG
Voltage UL	250 V
Current factory wiring	15 A
Current field wiring	15 A
Cross section CSA	22-10 AWG
Voltage CSA	250 V
Current CSA	6.3 A

#### Note

Remark to rated voltage	Note max power loss
Remark to rated current	Note max power loss
Defect indicator	Glow lamp
Voltage type for defect indication	
Minimum operating voltage of defective display	110 V
Maximum operating voltage of defective display	250 V