

Classic
Heat Gun Kit

Great Value!



Part No. 34838

Featuring STEINEL's Most Popular Heat Gun and Accessories:

- HL 1910 E Variable Temperature Electronic Heat Gun
- 14mm Reflector Nozzle
- 9mm Reduction Nozzle
- 39mm Reflector Nozzle
- Overhead Hanger
- Aluminum Carrying Case
- Application Hand Book

STEINEL[®]
Classic Quality




HL 1910 E
Variable Temperature
Electronic Heat Gun

Variable temperature: 120° F - 1100° F
3 Stage airflow: cool / 10.6 / 17.6 CFM
Watts: 1500
Voltage: 120 VAC / 60 Hz
Amps: 12.5
Nozzle Diameter: 1.30" (33.02 mm)
Net Weight: 2.05 lbs (32.80 oz)
Warranty: One year limited



Electronic Thermocouple Control

Microprocessor measures and regulates heat produced, preventing heat back-up even with restricted airflow. Extends life of tool and enables use of specialty reduction nozzles.



DuraTherm™
Heating Element

Ceramic Encapsulated Heating System is unsurpassed for even heat and long life. Coils are wound through a series of stacked ceramic disks achieving a "honey-comb" effect that fully encapsulates and supports.

