



Data and specifications subject to change without notice

Project name	Type
Order number	
Date	



514 585
Surface Mount




514 580
Recessed Mount

20 WATT SERIES


SPECIFICATIONS

Standard Features


- ◆ Clear lens standard
- ◆ Screw installation
- ◆ 6ft (2m) lead is standard, custom lead length available, contact factory
- ◆ 20W max G4 bi-pin halogen lamp (Osram lamp included and installed)
- ◆ Approved for blind hole applications
- ◆ Certified as a stand alone luminaire
- ◆ 24V available, consult factory for availability



514 580
Recessed Mount




514 585
Surface Mount



Optional anti-glare shield accessory

ORDER GUIDE

SERIES	MOUNTING	FINISH	ACCESSORIES
514	580 - Recessed Mount 585 - Surface Mount	01 - White 02 - Chrome 04 - Black 05 - Matte Silver 09 - Gold 11 - Matte Nickel	Anti-glare shield 02 - Chrome Anti-glare shield 04 - Black Anti-glare shield 09 - Gold Anti-glare shield 11 - Matte Nickel
 <p>Note:</p> <p>1) All cabinet luminaires are to be powered with remote Class 2 transformers sold separately</p> <p>2) See transformer section for requirement</p> <p>3) See under cabinet light installation sheet for typical installation methods (Install 1)</p>			

*Spec sheets are subject to change without notice