

SOCKET TAPPING SCREWS VIS TARAUDEUSES CREUSE

208
Pan
Head



209
Flat
Head



210
Truss
Head



- Sheet Metal Screws, Self-Tapping, Hardened.

Loxon® Square Socket Drive

Specify Papco® Pan, Flat or Truss Socket Head Tapping Screws where a positive driver engagement, or where high-speed assembly of sheet metal parts, is required. They are used in body work, moldings, trim, sheet metal work and many other applications.

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Pan Head Stock No.	Flat Head Stock No.	Truss Head Stock No.	Screw Dia.	Screw Length	Decimal Equiv. of Dia.	Drill Hole	Pan Head Stock No.	Flat Head Stock No.	Truss Head Stock No.	Screw Dia.	Screw Length	Decimal Equiv. of Dia.	Drill Hole
208-039				1/4			208-187				3/8		
208-041	209-041			3/8			208-189	209-189	210-189		1/2		
208-043	209-043		4	1/2	.112	5/64	208-190	209-190	210-190		5/8		
208-045	209-045			3/4			208-191	209-191	210-191	10	3/4	.191	9/64
208-047	209-047			1			208-193	209-193	210-193		1		
208-083				1/4			208-195	209-195	210-195		1-1/4		
208-085	209-085	210-085		3/8			208-197	209-197			1-1/2		
208-087	209-087	210-087		1/2			208-200	209-200			2		
208-088	209-088	210-088	6	5/8	.138	3/32	208-246	209-246			1/2		
208-089	209-089	210-089		3/4			208-248	209-248			3/4		
208-091	209-091	210-091		1			208-250	209-250		12	1	.218	5/32
208-093	209-093			1-1/4			208-252	209-252			1-1/4		
208-095	209-095			1-1/2			208-254	209-254			1-1/2		
208-135		210-135		3/8			208-257				2		
208-137	209-137	210-137		1/2			208-277	209-277			5/8		
208-138	209-138	210-138		5/8			208-278	209-278			3/4		
208-139	209-139	210-139	8	3/4	.165	1/8	208-280	209-280		14	1	.251	3/16
208-141	209-141	210-141		1			208-282	209-282			1-1/4		
208-143	209-143	210-143		1-1/4			208-284	209-284			1-1/2		
208-145	209-145	210-145		1-1/2			208-287	209-287			2		
208-148	209-148			2									

HEX HEAD TAPPING SCREWS VIS TARAUDEUSES TÊTE HEX

213
Hex Head



- Self-Tapping and Hardened.

Oversize Hexagon Washer Heads to fit Automotive Cap Screw Wrenches.

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Stock No.	Screw Dia.	Screw Length	Decimal Equiv. of Dia.	Across Flats	Drill Hole	Stock No.	Screw Dia.	Screw Length	Decimal Equiv. of Dia.	Across Flats	Drill Hole
213-085	6	3/8	.138	1/4	3/32	213-250	12	1	.218	5/16	5/32
213-137		1/2				213-276		1/2			
213-139		3/4				213-277		5/8			
213-141	8	1	.165	1/4	1/8	213-278	14	3/4	.251	7/16	3/16
213-143		1-1/4				213-280		1			
213-145		1-1/2				213-282		1-1/4			
213-187		3/8				213-284		1-1/2			
213-189		1/2				213-442		3/4			
213-190	10	5/8	.191	5/16	9/64	213-444	5/16	1	.312	1/2	9/32
213-191		3/4				213-446		1-1/4			
213-193		1				213-448		1-1/2			
213-246		1/2				213-489		1			
213-248	12	3/4	.218	5/16	5/32	213-493	3/8	1-1/2	.375	9/16	11/32

'SUPER-SERVICE' ASSORTMENT

No. 020-808

Contains 650 Hexagon Head Tapping Screws and Fender Washers. Large size, rigid metal box with high-strength plastic compartments. For more details see page 10. Size: 12" W x 18" L x 3" D.



020-808

**SPEE-DRILL[®] SCREWS
VIS SPEE-DRILL[®]**

**222
Series**



- Thread Forming
- Self Drilling

Papco[®] Spee-Drill[®] Screws are driven with a standard electric drill. The special hardened conical point bores through sheet metal and the serrated washer face prevents thread stripping.

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces, * Standard Package: 1,000 Pieces

Stock No.	Stock No.	Diameter x Length	Stock No.	Stock No.	Diameter x Length
100's	1,000's*	Size	100's	1,000's*	Size
222-085	222-585	6 x 3/8	222-189	222-689	10 x 1/2
222-111	222-611	7 x 1/2	222-191	222-691	10 x 3/4
222-137	222-637	8 x 1/2			

Note: All Papco[®] Spee-Drill[®] Screws are Hex, Slotted, Washer Head with 1/4 across flats head size.

SPEE-DRILL SCREW KIT

No. 020-617

Contains 1,000 Papco[®] Spee-Drill[®] Screws, 5 sizes and includes the Papco[®] Magnetic Chuck No. 222-360.

- All-metal box with hinged lid.
- Safety snap lock and carrying handle.
- Grease-resistant lid label with retail codes.



020-617

**6 IN 1 MAGNETIC SCREWDRIVER SET
JEU DE TOURNEVIS AIMANTE**

No. 222-996

Uses 1/4" Hex Base Bits

Magnetized shaft holds bit and screw for easy use. Driver comes complete with six high quality bits - 1/4" Slotted, No. 1 and No. 2 Phillips, No. 1 and No. 2 Loxxon[®] Square Socket and a T-15 6-Lobe. When not in use bits are stored in an impact-resistant, plastic handle. Shaft end can be used as a nut driver. Screw driver with 6 bits skin-packed on a handy point-of-purchase display card.



222-996

**6-LOBE MAGNETIC SCREWDRIVER SET
JEU DE TOURNEVIS AIMANTE**

No. 231-975

Same Magnetic Screwdriver as above. Driver comes complete with four high quality 6-Lobe bits - T-10, T-15, T-20 and T-25. Driver and bits skin-packed on colourful self-selling display card.



231-975

**MAGNETIC NUT SETTER
TOURNE-ÉCROUS MAGNÉTIQUE**

No. 222-570


Individually Packaged. Fits all five sizes of Papco[®] Spee-Drill[®] Screws. Fits standard electric drill. Has hexagon shank for positive drive. Permanent high-strength Alnico magnet. Made of heat treated tool steel for long life.



222-570

**TRIM SCREWS
VIS DE FINITION**

**229
Series**



ORDER BY STOCK NUMBER

Standard Package: Type 1 = 100 pieces, Types 2 to 5 = 50 pieces

Bright Chromium or Black Oxide Plated

Stock No.	Diameter x Length	Head Type	Stock No.	Diameter x Length	Head Type	Stock No.	Diameter x Length	Head Type
229-401	8 x 1/2	1	229-806	6 x 3/4	2 O. R.	229-849	8 x 5/8	3 O. S.
229-402	8 x 5/8	1	229-811	8 x 3/4	2 O. S.	229-851	8 x 3/4	3 O. S.
229-403	8 x 3/4	1	229-815	8 x 1	2 O. S.	229-855	8 x 1	3 O. S.
229-405	8 x 1	1	229-819	8 x 1-1/4	2 O. S.	229-883	10 x 3/4	3 O. S.
229-407	8 x 1-1/4	1	229-833	10 x 3/4	2 O. S.	229-887	10 x 1	3 O. S.
229-414	10 x 3/4	1	229-837	10 x 1	2 O. S.	229-985	8 x 3/4	4 O. S.
229-416	10 x 1	1				229-986	8 x 1	4 O. S.
						229-987	8 x 3/4	5 O. S.
						229-988	8 x 1	5 O. S.

O. S. - Oval Small Head

O. R. - Oval Regular Head

For Papco[®] Trim Screws Master Assortments No. 020-661 see pages 8 and 50.

**BLACK TRIM SCREWS
MASTER ASSORTMENT**

No. 020-662

Contains 350 screws. For more details see page 8.

020-662



**PHILLIPS TAPPING SCREWS
VIS TARAUDEUSES PHILLIPS**



**229
Series**

- Recessed Head, Self-tapping.
- Bright Plated, Hardened.



Oval Regular



Pan Head

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Stock No.	Diameter x Length	Head Type	Stock No.	Diameter x Length	Head Type	Stock No.	Diameter x Length	Head Type
229-010	6 x 1/2	O. R.	229-041	10 x 5/8	O. R.	229-124	8 x 1	P. H.
229-012	6 x 3/4	O. R.	229-044	10 x 1	O. R.	229-140	10 x 1/2	P. H.
229-014	6 x 1	O. R.	229-108	6 x 3/8	P. H.	229-142	10 x 3/4	P. H.
229-016	6 x 1-1/4	O. R.	229-110	6 x 1/2	P. H.	229-144	10 x 1	P. H.
229-022	8 x 3/4	O. R.	229-119	8 x 3/8	P. H.	229-160	12 x 1/2	P. H.
229-024	8 x 1	O. R.	229-120	8 x 1/2	P. H.	229-164	12 x 1	P. H.
229-026	8 x 1-1/4	O. R.	229-122	8 x 3/4	P. H.			

O. R. - Oval Regular

P. H. - Pan Head

**TRIM SCREWS
VIS DE FINITION**



- Zinc or Black Oxide plated.

These Oval and Pan Phillips Head Screws are used in all interior and exterior trim applications on cars and trucks.



Oval Head



Pan Head

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Stock No.	Diameter x Length	Head Type	Stock No.	Diameter x Length	Head Type	Stock No.	Diameter x Length	Head Type
229-219	8 x 3/8 Zinc	O. S.	229-242	10 x 3/4 Zinc	O. S.	229-923	8 x 1-1/2 Black	O. S.
229-220	8 x 1/2 Zinc	O. S.	229-244	10 x 1 Zinc	O. S.	229-933	10 x 3/4 Black	O. S.
229-222	8 x 3/4 Zinc	O. S.	229-248	10 x 1-1/2 Zinc	O. S.	229-937	10 x 1 Black	O. S.
229-224	8 x 1 Zinc	O. S.	229-250	10 x 2 Zinc	O. S.	229-945	10 x 1-1/2 Black	O. S.
229-225	8 x 1-1/8 Zinc	O. S.	229-252	10 x 2-1/2 Zinc	O. S.	229-960	6 x 1/2 Black	P. H.
229-226	8 x 1-1/4 Zinc	O. S.	229-911	8 x 3/4 Black	O. S.	229-962	8 x 1/2 Black	P. H.
229-227	8 x 1-3/8 Zinc	O. S.	229-912	8 x 3/4 Black	O. R.	229-968	8 x 3/4 Black	P. H.
229-228	8 x 1-1/2 Zinc	O. S.	229-915	8 x 1 Black	O. S.	229-972	8 x 1 Black	P. H.
229-229	8 x 1-3/4 Zinc	O. S.	229-916	8 x 1 Black	O. R.	229-980	10 x 3/4 Black	P. H.
229-240	10 x 1/2 Zinc	O. S.	229-919	8 x 1-1/4 Black	O. S.	229-982	10 x 1 Black	P. H.
229-241	10 x 5/8 Zinc	O. S.						

O.S. - Oval Small Head

O.R. - Oval Regular Head

P. H. - Pan Head

**TRIM SCREW ASSORTMENTS
ASSORTIMENTS DE VIS DE FINITION**

GARGAGE ASSORTMENT

No. 020-023

- Contains 100 Phillips Head Self-Tapping Sheet Metal Screws in nine popular sizes - in Oval Regular and Oval Small types.
- Packed in a rigid, clear plastic box with hinged lid.



020-023

No. 020-027

- Contains 100 Metric Zinc plated Trim Screws in Pan Oval and Round Washer heads.
- Six sizes in a clear plastic box.



020-027

MASTER ASSORTMENT

No. 020-613

- A well-balanced assortment of Tapping Screws for Trim, Body and Fender work.
- Contains 530 Screws. 25 sizes Phillips Head - Self-Tapping Sheet Metal Screws.
- Safety snap carrying handle.
- Metal box with handy molded compartments.
- Actual size illustrated lid label with retail codes.
- Refills available in standard packages of 100.
- Size: 9-3/4" W x 13-3/4" L x 2" D.



020-613

'SUPER-SERVICE' ASSORTMENT

No. 020-809

- Contains 1225 Phillips Trim Tapping Screws - 30 items
- Large size, rigid metal box with high-strength plastic compartments.
- Size: 12" W x 18" L x 3" D.
- For more details see page 10.



020-809

METRIC TRIM SCREWS VIS DE FINITION MÉTRIQUE

230
Series



- Pozi-Driv Tapping Screws and Bright Chromium plated*.

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Pan Head			Oval Small Head		
Stock No.	Dia. x Length	O. E. M. No.	Stock No.	Dia. x Length	O. E. M. No.
230-203	4.2 x 13 mm	11503482	230-207	4.2 x 20 mm	11502471
230-205	4.2 x 20 mm	11501929			
230-206*	4.2 x 20 mm	11500406			

*18.8 Stainless Steel Bright Chromium plated

Note: 4.2 mm = No. 8 diameter (.164)

METRIC MOULDING TRIM SCREWS VIS DE FINITION MOULURE MÉTRIQUE

230
Series



- Round Large Crowned Washer Head (Pozi-Driv Tapping Screws).
- Bright Chromium Plated.

Used in body work for attaching the chrome moulding in the wheel well and floor stripping of late model cars and trucks.

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Stock No.	Dia. x Length	O. E. M. No.	Stock No.	Dia. x Length	O. E. M. No.
230-301	4.2 x 8 mm	11503266	230-304	4.2 x 16 mm	11503635
230-302	4.2 x 12 mm	11501794	230-305	4.2 x 20 mm	-
230-303	4.2 x 12 mm Black	11501896	230-306	4.2 x 20 mm Black	11501884

Note: 4.2 mm = No. 8 diameter (.164)

TRUCK AND TRAILER FASTENERS ATTACHES DE CAMION ET REMORQUE

225
Series

- Plywood Lining Screws

Used to fasten plywood liners to body studs and frames.

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Stock No.	Diameter x Length	Stock No.	Diameter x Length
225-182	No. 18 x 2" Special Flush Head - Phillips - Wood Screw Bright plated Steel	225-186	No. 10 x 1-1/4" Special Flush Head - Phillips - Type A Bright plated Steel Hardened Tapping Screws
225-183	No. 10 x 3/4" Special Flush Head - Phillips - Thread Forming - Type 'B' Bright plated Steel Hardened Tapping Screws Drill 3/32" pilot hole.	225-188	No. 14 x 2-1/2" Flat Socket Head - Wood Screw Bright plated Steel
225-184	No. 14 x 3" Flat Head - Phillips - Wood Screw Bright plated Steel	225-196 225-197	Aluminium Panel Rivets 225-196 225-197 Made from heat treated aluminium. 225-196 3/16 x 7/16 Full Brazier Head. 225-197 1/4 x 7/16 Mod. Brazier Head. Used to fasten aluminium panels.

**THREAD CUTTING FLOORBOARD SCREWS
VIS AUTOTARAUEUSES POUR PLANCHER**

**225
Series**



- Flat Head Type 'F'

Used to fasten wood plank, laminated plywood or corrugated aluminium flooring to the supporting steel cross members of trucks and trailers.

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Stock No.	Size	Driver	Stock No.	Size	Driver
225-792	1/4-20 x 1-1/2	No. 3 Phillips	225-752	1/4-20 x 1-1/2	No. 3 Square
225-793	1/4-20 x 2	No. 3 Phillips	225-753	1/4-20 x 2	No. 3 Square
225-794	1/4-20 x 2-1/2	No. 3 Phillips	225-754	1/4-20 x 2-1/2	No. 3 Square
225-795	1/4-20 x 3	No. 3 Phillips	225-755	1/4-20 x 3	No. 3 Square

**6-LOBE FLOORBOARD SCREWS
VIS À SIX PANS POUR PLANCHER**

- 6-Lobe Flat Head Tri-Lobular, Phosphate and Oil Finish.



ORDER BY STOCK NUMBER

Standard Package: 50 Pieces

Stock No.	Size	Driver	Stock No.	Size	Driver
225-890	1/4-20 x 1	T-30	225-895	1/4-20 x 3	T-30
225-891	1/4-20 x 1-1/4	T-30	225-896	5/16-18 x 1-3/4	T-40
225-892	1/4-20 x 1-1/2	T-30	225-897	5/16-18 x 2	T-40
225-893	1/4-20 x 2	T-30	225-898	5/16-18 x 2-1/2	T-40
225-894	1/4-20 x 2-1/2	T-30			


**DRILL-X[®] SELF-DRILLING TAPPING SCREWS
VIS TARAUD FORET DRILL-X[®]**

**232
Series**


- Papco[®] Self-Drilling and Tapping Screws are made of high-quality steel and are specially heat treated.
- The drill point has been incorporated into the screw in the familiar twist drill design.
- These screws drill their own hole - form mating threads - fasten securely and can be used in steel, plastics, composite materials, wood plus various laminates.
- Determine total thickness of the material to be drilled then choose No. 2 or No. 3 point to allow complete drilling.
- Available in Pan Phillips, Pan Socket and Hex Head.

ORDER BY STOCK NUMBER

Standard Package: 100 Screws



Drill Point length determines maximum Metal thickness drillable.
No. 2 Point up to .110 Thick No. 3 Point up to .250 Thick



Stock No.	Dia. x (L)	Drill Point	Max-Metal Drillable (B)	Driver	Stock No.	Dia. x (L)	Drill Point	Max-Metal Drillable (B)	Driver
Pan Phillips Head									
232-010	6 x 3/8	No. 2	.090	No. 2	232-016	8 x 1	No. 2	.100	No. 2
232-011	6 x 1/2	No. 2	.090	No. 2	232-020	10 x 1/2	No. 2	.110	No. 2
232-013	8 x 1/2	No. 2	.100	No. 2	232-021	10 x 5/8	No. 3	.175	No. 2
232-014	8 x 5/8	No. 2	.100	No. 2	232-022	10 x 3/4	No. 3	.175	No. 2
232-015	8 x 3/4	No. 2	.100	No. 2	232-024	10 x 1	No. 3	.175	No. 2
Pan Socket Head									
232-030	6 x 3/8	No. 2	.090	No. 2	232-041	8 x 2	No. 2	.100	No. 2
232-031	6 x 1/2	No. 2	.090	No. 2	232-037	10 x 1/2	No. 2	.110	No. 2
232-032	8 x 1/2	No. 2	.100	No. 2	232-038	10 x 5/8	No. 3	.175	No. 2
232-033	8 x 5/8	No. 2	.100	No. 2	232-039	10 x 3/4	No. 3	.175	No. 2
232-034	8 x 3/4	No. 2	.100	No. 2	232-044	10 x 1	No. 2	.175	No. 3
232-035	8 x 1	No. 2	.100	No. 2	232-045	10 x 1-1/4	No. 2	.175	No. 3
232-036	8 x 1-1/2	No. 2	.100	No. 2	232-046	10 x 1-1/2	No. 2	.175	No. 3
232-040	8 x 1-1/4	No. 2	.100	No. 2	232-048	10 x 2	No. 2	.175	No. 3

DRILL-X® SELF-DRILLING TAPPING SCREWS VIS TARAUD FORET DRILL-X®

ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Stock No.	Dia. x (L)	Drill Point	Max-Metal Drillable (B)	Driver	Stock No.	Dia. x (L)	Drill Point	Max-Metal Drillable (B)	Driver
Hex Washer Head									
232-070	6 x 1/2	No. 2	.100	3/16	232-086	12 x 3/4	No. 3	.210	5/16
232-071	8 x 1/2	No. 2	.100	1/4	232-087	12 x 1	No. 3	.210	5/16
232-072	8 x 5/8	No. 2	.100	1/4	232-101	12 x 1-1/4	No. 3	.210	5/16
232-073	8 x 3/4	No. 2	.100	1/4	232-088	12 x 1-1/2	No. 3	.210	5/16
232-074	8 x 1	No. 2	.100	1/4	232-089	12 x 2	No. 3	.210	5/16
232-075	8 x 1-1/4	No. 2	.100	1/4	232-090	12 x 2-1/2	No. 3	.210	5/16
232-076	8 x 1-1/2	No. 2	.100	1/4	232-091	12 x 3	No. 3	.210	5/16
232-077	8 x 2	No. 2	.100	1/4	232-092	14 x 3/4	No. 3	.250	3/8
232-078	10 x 1/2	No. 2	.175	5/16	232-093	14 x 1	No. 3	.250	3/8
232-079	10 x 5/8	No. 3	.175	5/16	232-094	14 x 1-1/4	No. 3	.250	3/8
232-080	10 x 3/4	No. 3	.175	5/16	232-095	14 x 1-1/2	No. 3	.250	3/8
232-082	10 x 1	No. 3	.175	5/16	232-097	14 x 2	No. 3	.250	3/8
232-083	10 x 1-1/4	No. 3	.175	5/16	232-098	14 x 2-1/2	No. 3	.250	3/8
232-084	10 x 1-1/2	No. 3	.175	5/16	232-099	14 x 3	No. 3	.250	3/8
232-085	10 x 2	No. 3	.210	5/16	232-100	14 x 4	No. 3	.250	3/8

MASTER ASSORTMENT

No. 020-668

- Contains 20 sizes (complete coverage) of Papco® Drill-X® Self-Drilling Tapping Screws in Pan Socket and Hexagon Washer Head.
- Packed in a metal box with high-strength plastic compartments.
- Grease-resistant lid label shows actual size illustrations, measuring chart and retail price codes.



020-668

6-LOBE TRIM SCREWS VIS FINITION À SIX PANS

231
Series



Oval Head



Pan Head

- Metric Stainless Steel Tapping Screws
- Used on automotive trim, headlight and tail-light bezels and many other vehicle and appliance applications.
- The six-lobed drive system improves driver tool life, stops cam-out and increases mechanic's efficiency.
- These stainless steel screws have Bright Chromium or Black Oxide finish to conform to original specifications.

ORDER BY STOCK NUMBER

Standard Package: 25 Pieces

Oval Trim Head					Pan Head				
Stock No.	Size	Finish	Driver	O. E. M. No.	Stock No.	Size	Finish	Driver	O. E. M. No.
231-205	4.2 x 20 mm	Chrome	T-15	11504069	231-251	4.2 x 20 mm	Chrome	T-15	11504647
231-206	4.2 x 20 mm	Black	T-15	11504659	231-252	4.2 x 20 mm	Black	T-15	11504655
231-209	4.2 x 30 mm	Chrome	T-15	11504522	231-257	4.2 x 35 mm	Chrome	T-15	11504663
231-210	4.2 x 30 mm	Black	T-15	11504656	231-264	4.2 x 50 mm	Black	T-15	11504774
231-213	4.2 x 40 mm	Chrome	T-15	11504654					
231-219	4.2 x 55 mm	Chrome	T-15	11504664					

Note: 4.2 mm = No. 8 diameter (.164)

GARAGE ASSORTMENT

No. 020-070

Contains 70 6-Lobe Oval Head Trim Screws - 6 popular sizes in a clear styrene box.

No. 020-071

Contains 70 6-Lobe Pan Head Trim Screws - 4 popular sizes in a clear styrene box.



020-070