


Electrical Specifications

| ICN-1P32-N @ 120V | | | | |
|-------------------|---------------|--|--|--|
| Brand Name | CENTIUM | | | |
| Ballast Type | Electronic | | | |
| Starting Method | Instant Start | | | |
| Lamp Connection | Parallel | | | |
| Input Voltage | 120-277 | | | |
| Input Frequency | 50/60 HZ | | | |
| Status | Active | | | |

| Lamp Type | Num. of Lamps | Rated Lamp Watts | Min. Start Temp (F/C) | Input Current (Amps) | Input Power (ANSI Watts) | Ballast Factor | MAX THD % | Power Factor | MAX Lamp Current Crest Factor | B.E.F. |
|----------------|---------------------|---------------------|--------------------------|-------------------------|--------------------------------|-------------------|-----------------|-----------------|-------------------------------------|--------|
| * F17T8 | 1 | 17 | 0/-18 | 0.15 | 18 | 0.93 | 10 | 0.99 | 1.6 | 5.17 |
| F25T8 | 1 | 25 | 0/-18 | 0.21 | 25 | 0.92 | 10 | 0.99 | 1.6 | 3.68 |
| F32T8 | 1 | 32 | 0/-18 | 0.26 | 29 | 0.91 | 10 | 0.99 | 1.6 | 3.14 |
| F32T8/ES (25W) | 1 | 25 | 60/16 | 0.21 | 25 | 1.00 | 10 | 0.99 | 1.6 | 4.03 |
| F32T8/ES (28W) | 1 | 28 | 60/16 | 0.22 | 26 | 0.92 | 10 | 0.99 | 1.6 | 3.54 |
| F32T8/ES (30W) | 1 | 30 | 60/16 | 0.22 | 26 | 0.92 | 10 | 0.99 | 1.6 | 3.54 |




The wiring diagram that appears above is for the lamp type denoted by the asterisk (*)

Standard Lead Length (inches)

| | in. | cm. |
|--------|-----|-------|
| Black | | 0 |
| White | 24 | 61 |
| Blue | 28 | 71.1 |
| Red | 45 | 114.3 |
| Yellow | | 0 |
| Gray | | 0 |
| Violet | | 0 |

| | in. | cm. |
|--------------|-----|-----|
| Yellow/Blue | | 0 |
| Blue/White | | 0 |
| Brown | | 0 |
| Orange | | 0 |
| Orange/Black | | 0 |
| Black/White | 24 | 61 |
| Red/White | | 0 |
| | | |

Enclosure



Enclosure Dimensions

| OverAll (L) | Width (W) | Height (H) | Mounting (M) |
|-------------|-----------|------------|--------------|
| 9.5 " | 1.3 " | 1.0 " | 8.9 " |
| 9 1/2 | 1 3/10 | 1 | 8 9/10 |
| 24.1 cm | 3.3 cm | 2.5 cm | 22.6 cm |





Revised 01/31/12



Electrical Specifications

| ICN-1P32- | ICN-1P32-N @ 120V | | | | | |
|-----------------|-------------------|--|--|--|--|--|
| Brand Name | CENTIUM | | | | | |
| Ballast Type | Electronic | | | | | |
| Starting Method | Instant Start | | | | | |
| Lamp Connection | Parallel | | | | | |
| Input Voltage | 120-277 | | | | | |
| Input Frequency | 50/60 HZ | | | | | |
| Status | Active | | | | | |

Notes:

Section I - Physical Characteristics

- 1.1 Ballast shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable.
- 1.2 Ballast shall be provided with integral leads color-coded per ANSI C82.11.

Section II - Performance

- 2.1 Ballast shall be _____ (Instant, Rapid or Programmed) Start.
- 2.2 Ballast shall provide Independent Lamp Operation (ILO) for Instant Start ballasts allowing remaining lamp(s) to maintain full light output when one or more lamps fail.
- 2.3 Ballast shall contain auto restart circuitry in order to restart lamps without resetting power (except T8/HO ballast).
- 2.4 Ballast shall operate from 50/60 Hz input source of _____ (120V through 277V or 347V through 480V) with sustained variations of
- +/- 10% (voltage and frequency).
- 2.5 Ballast shall be high frequency electronic type and operate lamps at a frequency above 42 kHz to avoid interference with infrared devices and eliminate visible flicker.
- 2.6 Ballast shall have a Power Factor greater than 0.98 for primary lamp.
- 2.7 Ballast shall have a minimum ballast factor for primary lamp application as follows: 0.75 for Low Watt, 0.85 for Normal Light Output and 1.20 for High Light.
- 2.8 Ballast shall provide for a Lamp Current Crest Factor of 1.7 or less.
- 2.9 Ballast input current shall have Total Harmonic Distortion (THD) of less than 10% when operated at nominal line voltage with primary lamp.
- 2.10 Ballast shall have a Class A sound rating for all 4-foot lamps and smaller.
- 2.11 Ballast shall have a minimum starting temperature of _____ [-18C (0F) for standard T8 and Long Twin Tube lamps, 10C (50F) for standard T12 lamps, 0C (32F) for Slimline T8 lamps, -29C (-20F) for HO lamps,] for primary lamp application. Ballast shall have a minimum starting temperature of 16C (60F) for energy-saving lamps.
- 2.12 Ballast shall tolerate sustained open circuit and short circuit output conditions.
- 2.13 Ballast for T8 lamps shall provide lamp striation-reduction circuitry.
- 2.14 Ballast for FT5 lamps shall provide lamp EOL protection circuitry.

Section III - Regulatory

- 3.1 Ballast shall not contain any Polychlorinated Biphenyl (PCB).
- 3.2 Ballast shall be Underwriters Laboratories (UL) listed, Class P and Type 1 Outdoor; and Canadian Standards Association (CSA) certified where applicable.
- 3.3 Ballast shall comply with ANSI C62.41 Category A for Transient protection.
- 3.4 Ballast shall comply with ANSI C82.11 where applicable.
- 3.5 Ballast shall comply with applicable requirements of the Federal Communications Commission (FCC) rules and regulations, Title 47 CFR part 18, for Non-Consumer equipment.
- 3.6 Ballast shall comply with NEMA 410 for in-rush current limits.
- 3.7 Ballast for T8 lamps shall meet NEMA Premium/CEE High Performance T8 Lighting System Specifications.
- 3.8 Ballast shall meet RoHS Compliance Standards

Section IV - Other

- 4.1 Ballast shall be manufactured in a factory certified to ISO 9001 Quality System Standards.
- 4.2 Ballast shall carry a five-year warranty from date of manufacture against defects in material or workmanship, including replacement, for operation at a maximum case temperature of 70C.
- 4.3 Manufacturer shall have a twenty-year history of producing electronic ballasts for the North American market.
- 4.4 Energy saving T8 lamps (25W, 28W or 30W) may experience lamp striations if operated on ballasts not rated for their use.






Revised 01/31/12



| ICN-1P32-N @ 277V | | | | |
|-------------------|---------------|--|--|--|
| Brand Name | CENTIUM | | | |
| Ballast Type | Electronic | | | |
| Starting Method | Instant Start | | | |
| Lamp Connection | Parallel | | | |
| Input Voltage | 120-277 | | | |
| Input Frequency | 50/60 HZ | | | |
| Status | Active | | | |

| Lamp Type | Num. of Lamps | Rated Lamp Watts | Min. Start Temp (F/C) | Input Current (Amps) | Input Power (ANSI Watts) | Ballast Factor | MAX THD % | Power Factor | MAX Lamp Current Crest Factor | B.E.F. |
|----------------|---------------------|---------------------|--------------------------|-------------------------|--------------------------------|-------------------|-----------------|-----------------|-------------------------------------|--------|
| * F17T8 | 1 | 17 | 0/-18 | 0.07 | 18 | 0.93 | 10 | 0.96 | 1.6 | 5.17 |
| F25T8 | 1 | 25 | 0/-18 | 0.09 | 25 | 0.92 | 10 | 0.98 | 1.6 | 3.68 |
| F32T8 | 1 | 32 | 0/-18 | 0.11 | 30 | 0.94 | 10 | 0.97 | 1.6 | 3.13 |
| F32T8/ES (25W) | 1 | 25 | 60/16 | 0.09 | 25 | 1.00 | 10 | 0.98 | 1.6 | 4.03 |
| F32T8/ES (28W) | 1 | 28 | 60/16 | 0.10 | 26 | 0.92 | 10 | 0.98 | 1.6 | 3.54 |
| F32T8/ES (30W) | 1 | 30 | 60/16 | 0.10 | 26 | 0.92 | 10 | 0.98 | 1.6 | 3.54 |




The wiring diagram that appears above is for the lamp type denoted by the asterisk (*)

Standard Lead Length (inches)

| | in. | cm. |
|--------|-----|-------|
| Black | | 0 |
| White | 24 | 61 |
| Blue | 28 | 71.1 |
| Red | 45 | 114.3 |
| Yellow | | 0 |
| Gray | | 0 |
| Violet | | 0 |

| in. | cm. |
|-----|-----|
| | 0 |
| | 0 |
| | 0 |
| | 0 |
| | 0 |
| 24 | 61 |
| | 0 |
| | |

Enclosure



Enclosure Dimensions

| OverAll (L) | Width (W) | Height (H) | Mounting (M) |
|-------------|-----------|------------|--------------|
| 9.5 " | 1.3 " | 1.0 " | 8.9 " |
| 9 1/2 | 1 3/10 | 1 | 8 9/10 |
| 24.1 cm | 3.3 cm | 2.5 cm | 22.6 cm |





Revised 07/10/12



Electrical Specifications

| ICN-1P32-N @ 277V | |
|-------------------|---------------|
| Brand Name | CENTIUM |
| Ballast Type | Electronic |
| Starting Method | Instant Start |
| Lamp Connection | Parallel |
| Input Voltage | 120-277 |
| Input Frequency | 50/60 HZ |
| Status | Active |

Notes:

Section I - Physical Characteristics

- 1.1 Ballast shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable.
- 1.2 Ballast shall be provided with integral leads color-coded per ANSI C82.11.

Section II - Performance

- 2.1 Ballast shall be _____ (Instant, Rapid or Programmed) Start.
- 2.2 Ballast shall provide Independent Lamp Operation (ILO) for Instant Start ballasts allowing remaining lamp(s) to maintain full light output when one or more lamps fail.
- 2.3 Ballast shall contain auto restart circuitry in order to restart lamps without resetting power (except T8/HO ballast).
- 2.4 Ballast shall operate from 50/60 Hz input source of _____ (120V through 277V or 347V through 480V) with sustained variations of
- +/- 10% (voltage and frequency).
- 2.5 Ballast shall be high frequency electronic type and operate lamps at a frequency above 42 kHz to avoid interference with infrared devices and eliminate visible flicker.
- 2.6 Ballast shall have a Power Factor greater than 0.98 for primary lamp.
- 2.7 Ballast shall have a minimum ballast factor for primary lamp application as follows: 0.75 for Low Watt, 0.85 for Normal Light Output and 1.20 for High Light.
- 2.8 Ballast shall provide for a Lamp Current Crest Factor of 1.7 or less.
- 2.9 Ballast input current shall have Total Harmonic Distortion (THD) of less than 10% when operated at nominal line voltage with primary lamp.
- 2.10 Ballast shall have a Class A sound rating for all 4-foot lamps and smaller.
- 2.11 Ballast shall have a minimum starting temperature of _____ [-18C (0F) for standard T8 and Long Twin Tube lamps, 10C (50F) for standard T12 lamps, 0C (32F) for Slimline T8 lamps, -29C (-20F) for HO lamps,] for primary lamp application. Ballast shall have a minimum starting temperature of 16C (60F) for energy-saving lamps.
- 2.12 Ballast shall tolerate sustained open circuit and short circuit output conditions.
- 2.13 Ballast for T8 lamps shall provide lamp striation-reduction circuitry.
- 2.14 Ballast for FT5 lamps shall provide lamp EOL protection circuitry.

Section III - Regulatory

- 3.1 Ballast shall not contain any Polychlorinated Biphenyl (PCB).
- 3.2 Ballast shall be Underwriters Laboratories (UL) listed, Class P and Type 1 Outdoor; and Canadian Standards Association (CSA) certified where applicable.
- 3.3 Ballast shall comply with ANSI C62.41 Category A for Transient protection.
- 3.4 Ballast shall comply with ANSI C82.11 where applicable.
- 3.5 Ballast shall comply with applicable requirements of the Federal Communications Commission (FCC) rules and regulations, Title 47 CFR part 18, for Non-Consumer equipment.
- 3.6 Ballast shall comply with NEMA 410 for in-rush current limits.
- 3.7 Ballast for T8 lamps shall meet NEMA Premium/CEE High Performance T8 Lighting System Specifications.
- 3.8 Ballast shall meet RoHS Compliance Standards

Section IV - Other

- 4.1 Ballast shall be manufactured in a factory certified to ISO 9001 Quality System Standards.
- 4.2 Ballast shall carry a five-year warranty from date of manufacture against defects in material or workmanship, including replacement, for operation at a maximum case temperature of 70C.
- 4.3 Manufacturer shall have a twenty-year history of producing electronic ballasts for the North American market.
- 4.4 Energy saving T8 lamps (25W, 28W or 30W) may experience lamp striations if operated on ballasts not rated for their use.





Revised 07/10/12