



Commercial Specification Grade Straight Blade Power Devices


**2-Pole, 3-Wire Grounding
NEMA 5-50, 6-30
50A 125V, 30A 250V**

Power Devices


FEATURES

- Heavy gauge galvanized steel mounting strap for corrosion resistance.
- Receptacles for use with copper or aluminum wire.
- Surface receptacles have patented lay-in terminals and accept up to #4 wire.
- Universal plugs include blades for 30A & 50A configurations.
- Surface receptacles 0.75" (19.05mm) and 1.0" (25.4mm) concentric knockouts and adjustable cord clamp allow for wiring from bottom or back.
- Flush receptacles fit one or two gang enclosures.
- High strength glass reinforced nylon body resists breakage in high abuse areas for Catalog No. 5700N.

G-23 Straight Blade Receptacles



1253



S41



1232



S42

TESTING & CODE COMPLIANCE

- Listed to UL 498 & meets Federal Spec. WC-596 (file no. E2369) except as noted. Receptacles: file no. E15058; Plugs: file no. E15012.
- CSA Certified to C22.2 no. 42 (file no. LR7087); Plugs: file no. 2081 (6221-02); Receptacles: file no. 6914 (6233-01).
- NOM Certified.

MATERIAL CHARACTERISTICS

- Plugs: PVC. Flush Receptacles: Phenolic; Surface Receptacles: PVC.
- Temperature Rating: -20°C (without impact) to 75°C max. continuous. 5700N, V2 rated; -40°C (without impact) to 105°C max. continuous.

NEMA 5-50 Rating 50A 125V

Receptacles

Description	Color	Catalog No.
Flush	Brown	1253

Plug

Description	Cord Diameter	Color	Catalog No.
Angle Universal - PVC	1.10" max. (27.94mm)	Black	S41

NEMA 6-30 Rating 30A 250V

Receptacles

Description	Color	Catalog No.
Surface	Black	1232
Flush	Black	5700N
Flush	Brown	1234

Plug

Description	Cord Diameter	Color	Catalog No.
Angle Universal - PVC	1.10" max. (27.94mm)	Black	S42

Wallplate Guide for Power Devices

Power Device Catalog No.	Wallplate Catalog No.
1234, 1253, 5700N	39CH, 68, 2068, 2168, 93221, 93227, 5068, PJ724, PJ703

