

Standard Grade Straight Blade Receptacles

2-Pole, 3-Wire Grounding
15A 125V




Standard Grade Duplex Receptacles

FEATURES

- Longer, wider strap provides 40% more contact area to wall board. Virtually eliminates floating installations.
- Screw-Catch™ feature automatically holds the wallplate and mounting screw in place.
- Built-in wire stripper for #14 and #12 wire provides backup for misplaced tools.
- Built-in wire looper designed to speed termination of both #14 and #12 wire.
- High impact-resistant thermoplastic face and back body eliminates job site breakage.
- Double wipe ground contacts ensure long-term ground retention.
- Easy access split circuit break-off tab.
- Side wire terminals accept up to #10 solid or stranded wire.
- Push-in terminals accept #14 solid wire.
- Terminal screws backed out – ready for wiring.
- Combination slot/Phillips head mounting and terminal screws ease installation (slot/Robertson screws in Canada where available).

Side Wire and Push Wire

Rating A V	NEMA	Color	Catalog No.		
			Standard	Automatic Ground	Less Ears
15 125	5-15R	Almond	270A	270-9A	4270A
		Black	270BLK	–	–
		Brown	270B	270-9B	4270B
		Ivory	270V	270-9V	4270V
		Light Almond	270LA	270-9LA	4270LA
		White	270W	270-9W	4270W



G-16 Straight Blade Receptacles

Standard Grade Duplex Receptacles


FEATURES

- Double wipe ground contacts to ensure long-term ground retention.
- Easy access split circuit break-off tab.
- Push-in terminals (8) accept #14 solid wire.
- Combination slot/Phillips head mounting and ground screws ease installation.

Push Wire Only

Rating A V	NEMA	Color	Catalog No.		
			Standard	Less Ears	No Strap
15 125	5-15R	Black	–	–	298-2BK
		Brown	298B*	–	–
		Ivory	298V*	–	298-2V
		White	298W*	298-3W	–

*Not CSA



TESTING & CODE COMPLIANCE

- Listed to UL 498 (file no. E15058)
- CSA (file no. 6914 (6233-01)).
- Meets all CSA requirements, C22.2 no. 42.
- NOM certified.

MATERIAL CHARACTERISTICS

Meets flammability requirements per UL 94, VO rated. Temperature Rating: Side Wire & Push Wire: -20°C to 60°C. Push Wire Only: -40°C to 65°C.



5-15R