

Receptacles

TRAFCI15W



Outlet branch circuit AFCI receptacles

Product description

2-pole, 3-wire grounding 15A, 125V/AC 20A, 125V/AC

Design features

- Designed to recognize an arc fault and quickly trip to stop the flow of electricity to prevent the electrical system from being an ignition source of fire
- Meets 2014 NEC[®] 406.4 (D)(4) requirements for replacement receptacles for dwelling units
- Meets 2014 NEC[®] requirements when installed as defined in Article 210.12 (A) for dwelling units
- Proven Eaton AFCI technology refined over several years to minimize unwanted tripping
- Lockout feature provides safest design by prohibiting the AFCI from resetting if the AFCI circuit is not functioning properly

Tamper resistant AFCI receptacle



- Tamper resistant receptacles provide compliance with 2014 NEC[®] Article 406.12 which states that all 15A and 20A, 125V/AC receptacles installed in dwelling units must be tamper resistant
- Perfect for use in dwelling units, remodel/ retrofit applications, dormitories and commercial buildings

	Rating			
Α	V/AC	Description	Color suffix	Catalog no.
15	120	AFCI duplex receptacle, tamper resistant	A, B, BK, GY, LA, V, W	TRAFCI15
20	125	AFCI duplex receptacle, tamper resistant	A, B, BK, GY, LA, V, W	TRAFCI20

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White).



Dimensional information: B-69 Specification information: Please visit www.cooperwiringdevices.com Compliances, specifications and availability are subject to change without notice.

Tamper resistant