

Compact Fluorescent Energy Saver Decorative Twisters

Ordering, Electrical and Technical Data

Product Number	Description	Volts	Nom. Watts	Approx. Incand. Equiv.	Base	Color Temp. (Kelvin)	CRI	Approx. Initial Lumens ¹	MOL (In.)	Diam. (In.)	Rated Avg. Life (Hrs.) ²	Min. Starting Temp.	Max. Ambient Temp.
14792-6	Dec Twister EL/mdT 5	120	5	25 A19	Med.	2700	82	250	4	1.75	8000	-4°F/-20°C	122°F/50°C
14793-4	Dec Twister EL/mdT 9	120	9	40 A19	Med.	2700	82	550	4 ¼	1.75	8000	-4°F/-20°C	122°F/50°C
13804-0	Dec Twister EL/mdT 11	120	11	40 A19	Med.	2700	82	675	4 ⅝	1.75	8000	-4°F/-20°C	122°F/50°C
15638-0	Dec Twister EL/mdT 13	120	13	60 A19	Med.	2700	82	900	4	2.0	10,000	-4°F/-20°C	122°F/50°C
14786-8	Dec Twister EL/mdT 13 4100K	120	13	60 A19	Med.	4100	82	900	4 ¼	1.75	10,000	-4°F/-20°C	122°F/50°C
14787-6	Dec Twister EL/mdT 13 5000K	120	13	60 A19	Med.	5000	82	900	4 ¼	1.75	10,000	-4°F/-20°C	122°F/50°C
20286-1	Dec Twister EL/mdT 18	120	18	75 A19	Med.	2700	82	1250	5 ½	1.89	10,000	-4°F/-20°C	122°F/50°C
15697-5	Dec Twister EL/mdT 23	120	23	100 A19	Med.	2700	82	1600	5	1.89	10,000	-4°F/-20°C	122°F/50°C
13715-8	Dec Twister EL/mdT 27	120	27	100 A19	Med.	2700	82	1750	5 ⅝	2.05	10,000	-4°F/-20°C	122°F/50°C
14788-4	Dec Twister EL/mdT 27 4100K	120	27	100 A19	Med.	4100	82	1850	5 ⅝	2.05	10,000	-4°F/-20°C	122°F/50°C
14789-2	Dec Twister EL/mdT 27 5000K	120	27	100 A19	Med.	5000	82	1850	5 ⅝	2.05	10,000	-4°F/-20°C	122°F/50°C
15639-8	Dec Twister EL/mdT 32	120	32	150 A19	Med.	2700	82	2200	5 ½	2.05	10,000	-4°F/-20°C	122°F/50°C
13948-5	Dec Twister EL/dT 42	120	42	150 A21	Med.	2700	82	2600	7 ½	2.52	8000	-4°F/-20°C	122°F/50°C

Shipping Data

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
14792-6	14792-1	14792-6	6	1.72	0.083	2646	378	7	2.0 x 2.0 x 4.4	4.4 x 6.4 x 5.1	39.4 x 45.1 x 35.4
14793-4	14793-8	14793-3	6	1.82	0.087	2646	378	7	2.0 x 2.0 x 4.6	4.3 x 6.4 x 5.3	39.4 x 45.1 x 37.2
13804-0	13804-2	13804-7	6	0.82	0.109	2088	348	6	2.0 x 2.0 x 5.0	4.6 x 6.7 x 6.1	38.4 x 46.6 x 42.8
15638-0	15638-1	15638-6	6	1.70	0.152	1152	192	6	2.6 x 2.6 x 5.2	5.4 x 8.3 x 5.9	33.3 x 46.5 x 35.3
14786-8	14786-0	14786-5	6	2.14	0.161	1404	234	6	2.6 x 2.6 x 5.2	5.7 x 8.3 x 5.9	39.8 x 47.2 x 35.3
14787-6	14787-7	14787-2	6	2.14	0.161	1404	234	6	2.3 x 2.3 x 5.8	5.7 x 8.3 x 5.9	39.8 x 47.2 x 35.3
20286-1	20286-6	20286-1	6	6.0	0.153	1620	270	6	2.6 x 2.6 x 5.8	5.1 x 7.5 x 6.9	37.5 x 46.1 x 41.1
15697-5	15697-8	15697-3	6	6.0	0.179	1332	222	6	2.6 x 2.6 x 6.1	5.7 x 8.4 x 6.5	39.2 x 46.5 x 39.0
13715-8	13715-1	13715-6	6	1.39	0.209	1020	204	5	2.6 x 2.6 x 6.1	5.9 x 8.5 x 7.2	39.4 x 47.2 x 41.7
14788-4	14788-4	14788-9	6	2.38	0.188	1170	234	5	2.6 x 2.6 x 6.1	5.7 x 8.3 x 6.9	39.8 x 47.2 x 34.4
14789-2	14789-1	14789-6	6	2.39	0.188	1170	234	5	2.6 x 2.6 x 6.1	5.7 x 8.3 x 6.9	39.8 x 47.2 x 34.4
15639-8	15639-8	15639-3	6	1.64	0.260	900	180	5	3.0 x 3.0 x 6.2	6.4 x 9.4 x 7.5	38.3 x 47.0 x 37.5
13948-5	13948-3	13948-8	6	2.70	0.303	1080	180	6	3.1 x 3.1 x 7.6	6.7 x 9.9 x 7.9	40.1 x 49.4 x 47.6

1) Approximate initial lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life under standard laboratory conditions.

2) Average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Use in recessed cans or enclosed indoor fixtures could result in reduced lamp life.

■ ENERGY STAR® Bulb: As an ENERGY STAR® Partner, Philips has determined that this product meets the ENERGY STAR® guidelines for energy efficiency.

Above specifications are subject to change without notice.

WARNINGS & CAUTIONS: Do not use with dimmers. Some electronic timer and photosensor switches contain dimming circuitry, so before using such a switch, check with its manufacturer to ensure compatibility with electronic CFL bulbs. Do not use with emergency exit fixtures or lights. Outdoor use requires a weather-protected fixture. Turn off power before changing bulb. This device complies with Part 18 of the FCC Rules.

Use in recessed cans or enclosed indoor fixtures could result in reduced lamp life.

Reliable operating temperature range -4F/-20C to 122F/50C.

Note: This product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.

Bulb Type	Table/Floor Lamp	Outdoor Postlight	Wall Sconce	Surface Mount	Reading Lamp	Border Lights	Recessed Fixture	Open Hanging	Vanity Strip	Ceiling Fan
Decorative Twister	●		●		●			●		
Universal	●	●	●	●	●	●	●	●		
3-Way	●									
Reflector Flood							●	●		
Dimmable Reflector Flood							●	●		
Candle		●	●		●					●
Vanity & Decor Globe								●	●	●
Soft White Plus	●	●	●		●	●		●		●
Outdoor		●				●				
Bug-A-Way		●								
Circline	●									
Genie	●	●	●	●	●	●	●	●	●	●



© 2008 Philips Lighting Company. All rights reserved.
 Printed in USA 1/08
 P-8514-D
 www.philips.com

Philips Lighting Company
 200 Franklin Square Drive
 P.O. Box 6800
 Somerset, NJ 08875-6800
 1-800-555-0050
 A Division of Philips Electronics North America Corporation

Philips Lighting
 281 Hillmount Road
 Markham, Ontario
 Canada L6C 2S3
 1-800-555-0050
 A Division of Philips Electronics Ltd.

Compact Fluorescent
Energy Saver
Decorative Twisters

*Ideal for general
household use*

ENERGY SAVER



Energy saver twisters

Philips Compact Fluorescent Energy Saving Decorative Twisters provide energy savings and reduce operating costs without sacrificing quality of light compared to incandescent equivalents.

Direct replacement for incandescent bulbs

- Instant on
- Fits into incandescent fixtures
- Compact size fits many small fixtures
- Provides warm and inviting soft white light

Available in a variety of color temperatures

Long life

- Lasts at least 5 years*

Energy savings

- Saves up to \$86 over the life of the lamp when you replace a 150W A21 incandescent lamp with a 42W energy saving decorative twister**

* Based on an average daily usage of 3–4 hours per day, 7 days per week.

** Energy savings based on wattage saved x replacement lamp rated average life (8000 hours) ÷ 1000 x \$0.10 kWh rate.

PHILIPS
sense and simplicity