



# Industrial Specification Grade Hart-Lock® Locking Devices

2 Pole, 3 Wire Grounding  
NEMA L5-20, 20A 125V  
NEMA L6-20, 20A 250V  
NEMA L7-20, 20A 277V  
NEMA L8-20, 20A 480V  
NEMA L9-20, 20A 600V


## 20A 2 Pole, 3 Wire Grounding Industrial Specification Grade Locking Receptacles

### FEATURES



- Rugged fiberglass reinforced nylon body.
- Clearly marked rating, NEMA configuration and approval listings on receptacle face.
- One piece brass contacts offer superior performance and minimum heat rise.
- Back wire terminal clamps for easy secure wiring.
- Combination head screws standard - slot/Phillips in the U.S.
- Add -C to catalog number for Canadian screws - slot/Robertson head combination.
- Safety ground clip provided for fast installation.

INDUSTRIAL  
COMMERCIAL

## E-9 LOCKING DEVICES



**CRL520R**



### Industrial Specification Grade Locking Receptacles

Rating	A	V/AC	NEMA	Description	Color	Catalog No.
20	125	L5-20	Standard	Black	CWL520R*	
			Corrosion Resistant	Yellow	CRL520R*	
			Isolated Ground	Orange	IGL520R	
20	250	L6-20	Standard	Black	CWL620R*	
			Corrosion Resistant	Yellow	CRL620R*	
			Isolated Ground	Orange	IGL620R	
20	277	L7-20	Standard	Black	CWL720R*	
			Isolated Ground	Orange	IGL720R	
20	480	L8-20	Standard	Black	CWL820R*	
			Isolated Ground	Orange	IGL820R	
20	600	L9-20	Standard	Black	CWL920R	

\*UL Listed to Federal Spec. WC-596

NOTE: Weather Protective Covers from Cooper Wiring Devices that may be used with these products are described on page E-71 in this section.

### TESTING & CODE COMPLIANCE

- Listed to UL 498 (file no. E2369).
- CSA Certified to C22.2 no. 42 (file no. LR7087).

### MATERIAL CHARACTERISTICS

Glass filled Nylon.  
 Environmental:  
 Flammability per UL 94 requirements, VO rated.  
 Temperature Rating:  
 Receptacles:  
 -40°C to 105°C.



**L5-20R**



**L6-20R**



**L7-20R**



**L8-20R**



**L9-20R**