

# **Electrical Specifications**

IOP-2P59-SC@120V					
Brand Name	OPTANIUM				
Ballast Type	Electronic				
Starting Method	Instant Start				
Lamp Connection	Parallel				
Input Voltage	120-277				
Input Frequency	50/60 HZ				
Status	Active				

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (°F/C)	Input Current (Amps)	Input Power (ANSI Watts)	Ballast Factor	MAX THD %	Power Factor	MAX Lamp Current Crest Factor	B.E.F
F72T8	1	46	32/00	0.46	54	1.09	10	0.98	1.6	2.02
F72T8	2	46	32/00	0.74	88	0.92	10	0.98	1.6	1.05
* F96T8	1	59	32/00	0.56	67	1.05	10	0.98	1.6	1.57
F96T8	2	59	32/00	0.91	108	0.87	10	0.98	1.6	0.81
F96T8/ES	1	57	60/16	0.54	64	1.05	10	0.98	1.6	1.64
F96T8/ES	2	57	60/16	0.86	104	0.87	10	0.98	1.6	0.84
F96T8/ES(51W)	2	51	60/16	0.84	94	0.87	10	0.98	1.6	0.93

## 

Diag. 69

Insulate unused blue lead for 1000V


The wiring diagram that appears above is for the lamp type denoted by the asterisk (\*)

Standard Lead Length (inches)

	in.	cm.
Black	22	55.9
White	22	55.9
Blue	46	116.8
Red	70	177.8
Yellow		0
Gray		0
Violet		0

1 <del>611651</del>		
.511007	in.	cm.
Yellow/Blue		0
Blue/White		0
Brown		0
Orange		0
Orange/Black		0
Black/White		0
Red/White		0

# **Enclosure**



### **Enclosure Dimensions**

OverAll (L)	Width (W)	Height (H)	Mounting (M)
9.50 "	1.7 "	1.18 "	8.90 "
9 1/2	1 7/10	1 9/50	8 9/10
24.1 cm	4.3 cm	3 cm	22.6 cm

### Revised 11/12/2009





Data is based upon tests performed by Philips Lighting Electronics N.A. in a controlled environment and is representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.



# **Electrical Specifications**

IOP-2P59-SC@120V						
Brand Name	OPTANIUM					
Ballast Type	Electronic					
Starting Method	Instant Start					
Lamp Connection	Parallel					
Input Voltage	120-277					
Input Frequency	50/60 HZ					
Status	Active					

#### Notes:

Section I - Physical Characteristics

- 1.1 Ballast shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable,
- 1.2 Ballast shall be provided with integral leads color-coded per ANSI C82.11.

#### Section II - Performance Requirements

- 2.1 Ballast shall be \_\_\_\_\_ (Instant or Programmed) Start.
- 2.2 Ballast shall provide Independent Lamp Operation (ILO) for Instant Start or Programmed Start Parallel ballasts allowing remaining lamp(s) to maintain full light output when one or more lamps fail.
- 2.3 Ballast shall contain auto restart circuitry in order to restart lamps without resetting power.
- 2.4 Ballast shall operate from 50/60 Hz input source of 120V through 277V with sustained variations of +/- 10% (voltage and frequency). GOPA ballasts shall operate from an input source of 347V.
- 2.5 Ballast shall be high frequency electronic type and operate lamps at a frequency between 42 kHz and 52 kHz to avoid interference with infrared devices, eliminate visible flicker and avoid Article Surveillance System, such as anti-theft devices.
- 2.6 Ballast shall have a Power Factor greater than 0.98 for primary lamp.
- 2.7 Ballast shall have a minimum ballast factor for primary lamp application as follows: 0.77 for Low Watt, 0.87 for Normal Light Output, and
- 1.18 for High Light for Instant Start ballasts or 0.71 for Low Watt and 0.88 for Normal Light Output for Programmed Start ballasts.
- 2.8 Ballast shall provide for a Lamp Current Crest Factor of 1.7 or less.
- 2.9 Ballast input current shall have Total Harmonic Distortion (THD) of less than 10% when operated at nominal line voltage with primary lamp.
- 2.10 Ballast shall have a Class A sound rating for all 4-foot lamps and smaller.
- 2.11 Ballast shall have a minimum starting temperature of -29C (-20F) on Instant Start ballasts or -18C (0F) on Programmed Start ballasts for standard T8 lamps and 16C (60F) for energy-saving T8 lamps. Consult lamp manufacturer for temperature versus light output characteristics.
- 2.12 Ballast shall tolerate sustained open circuit and short circuit output conditions.
- 2.13 Ballast shall have lamp striation-reduction circuitry.
- 2.14 Programmed Start ballast shall provide lamp EOL protection circuitry.
- 2.15 Maximum remote distance for Energy Saving Lamps in Remote/Tandem applications is 6 feet for ICN, IOP, and IOPA Instant Start and Programmed Start models.

### Section III - Regulatory Requirements

- 3.1 Ballast shall not contain any Polychlorinated Biphenyl (PCB).
- 3.2 Ballast shall be Underwriters Laboratories (UL) listed, Class P and Type 1 Outdoor; and Canadian Standards Association (CSA) certified where applicable.
- 3.3 Ballast shall comply with ANSI C62.41 Category A for Transient protection.
- 3.4 Ballast shall comply with ANSI C82.11 where applicable.
- 3.5 Ballast shall comply with the requirements of the Federal Communications Commission (FCC) rules and regulations, Title 47 CFR part 18, Non-Consumer (Class A) for EMI/RFI (conducted and radiated).
- 3.6 IOP and IOPA Ballasts shall meet NEMA Premium/CEE High Performance T8 Lighting System Specifications.
- 3.7 IOP ballasts shall comply with UL Type CC rating.
- 3.8 Ballast shall comply with NEMA 410 for in-rush current limits.
- 3.9 Ballast shall meet RoHS Compliance Standards

### Section IV - Other

- 4.1 Ballast shall be manufactured in an ISO 9001 Qualified factory.
- 4.2 Ballast shall carry a five-year warranty from date of manufacture against defects in material or workmanship, including replacement, for operation at a maximum case temperature of 70C. Ballasts with a "90C" designation in their catalog number shall also carry a three-year warranty at maximum case temperature of 90C.

otes: . Energy-saving T8 lamps (25W, 28W or 3	OW) may experience lam	p striations if operated o	on ballasts not rated for t	heir use.
3 3 4 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7	, , , , , , , , , , , , , , , , , , , ,	,		
	_			
evised 11/12/2009	(D)			
, VIGGU I I/ 14/4UUJ		®		
		d environment and is represer		A - t 1 f

4.3 Manufacturer shall have a twenty-year history of producing electronic ballasts for the North American market.