




POWER TOOL ACCESSORIES

GREENLEE DELIVERS POWER TOOL ACCESSORIES THAT ARE SECOND-TO-NONE IN THE INDUSTRY. FROM THE DOUBLE-FLUTE CUTTING POWER OF KWIK STEPPER® STEP BITS TO REPLACEABLE TIP NAIL EATER® AUGER BITS, GREENLEE POWER TOOL ACCESSORIES CUT FASTER, LAST LONGER, AND IMPROVE YOUR PRODUCTIVITY ON THE JOB SITE. GET THROUGH IT WITH GREENLEE.



Contents

Step Bits	110
Drill/Taps	112
Steel Hole Cutters	114
Carbide-Tipped Hole Cutters	115
Ultra Cutters	116
Hole Saws	117
Quick Change Hole Saw Kit	120
Carbide-Grit Hole Saws	121
Recessed Light Hole Saws	122
Auger Bits	124
D'versibit® Auger Bits & Accessories	128
Spade Bits	132
E-Z Bore® Self-Feed Bits	134
Saw Blades	135
Hand Saws	137
Band Saws	138
Anchors And Fasteners	139



STEP BITS

Kwik Stepper® Step Bits



- Steam oxide finish runs cooler for longer life
- Unique split-tip design penetrates through steel faster
- Resists walking or skidding, even on round surfaces
- Balanced, double-flute construction requires less pressure, does the work for you

CAT. NO.	UPC NO.	DESCRIPTION
35884	35884	Kwik Stepper® Step Bit Kit
03607	03607	Kwik Stepper® Step Bit Kit

SPECIFICATIONS

Hole Sizes From 1/8" through 1-3/8" (3.2 - 34.9 mm)
Capacity Cut up through 3/8" (9.5 mm) mild steel, copper, brass, aluminum, wood, plastic and laminates


CAT. NO.	UPC NO.	DESCRIPTION	KIT CAT./UPC NO.	
			03607	35884
34401	34401	1/2" Multi-Hole Step Bit	✓	✓
34403	34403	7/8" Multi-Hole Step Bit	✓	✓
30008	30008	1-1/8" Multi-Hole Step Bit		✓
35936	35936	Plastic Case	✓	✓

CAT. NO.	UPC NO.	DESCRIPTION	BULK
			QTY.
30008-B	01500	K/S Step #8 Bit (Bulk Pop)	25
34403-B	01501	K/S Step #3 Bit (Bulk Pop)	25
36414-B	01502	K/S Step #14 Bit (Bulk Pop)	25



METRIC

Single-hole bits are designed to drill one indicated hole size through a series of steps from bit tip to full size



Multi-hole bits allow you to drill a hole in any of the stated diameters

1/2" (12.7 mm)	1/2" (12.7 mm)	1/2" (12.7 mm)	13/16" (20.6 mm)	7/8" (22.2 mm)	7/8" (22.2 mm)	1-1/8" Electrician's	1-3/8" (34.9 mm)	9.7 mm (.382")	30.5 mm (1.201")	32.5 mm (1.280")
Single-Hole Step Bit	Multi-Hole Step Bit	Multi-Hole Step Bit	Multi-Hole Step Bit	Single-Hole Step Bit	Multi-Hole Step Bit	Step Bit	Multi-Hole Step Bit	Multi-Hole Step Bit	Multi-Hole Step Bit	Multi-Hole Step Bit

SIZE		CAT/UPC NO.										
Inches	mm	34410	34401	36402	30005	34411	34403	30008	36414	36018	36020	36022
1/8	3.2		✓									
5/32"	4.0		✓									
3/16"	4.8		✓	✓	✓		✓					
7/32"	5.6		✓									
1/4"	6.4		✓	✓	✓		✓					
9/32"	7.1		✓									
5/16"	7.9		✓	✓	✓		✓					
11/32"	8.7		✓									
3/8"	9.5		✓	✓	✓		✓					
0.382"	9.7										✓	
13/32"	10.3		✓									
7/16"	11.1		✓	✓	✓		✓					
15/32"	11.9		✓									
0.492"	12.5										✓ Pg-7	
1/2"	12.7	✓	✓	✓	✓		✓	✓				
9/16"	14.3				✓		✓					
0.598"	15.2										✓ Pg-9	
5/8"	15.9				✓		✓					
0.638"	16.2											✓ ISO-16
11/16"	17.5				✓		✓					
0.732"	18.6										✓ Pg-11	
3/4"	19.1				✓		✓					
0.803"	20.4										✓ Pg-13	✓ ISO-20
13/16"	20.6				✓		✓					
7/8"	22.2					✓	✓	✓	✓			
0.886"	22.5										✓ Pg-16	
1.00"	25.4											✓ ISO-25
1.114"	28.3										✓ Pg-21	
1-1/8"	28.6							✓	✓			
1.201"	30.5								✓			
1-7/32"	31.0								✓			
1-1/4"	31.8								✓			
1.280"	32.5											✓ ISO-32
1-3/8"	34.9								✓			
Overall Length		1-7/8" (47.6 mm)	3-3/8" (85.7 mm)	3-7/16" (87.3 mm)	3-7/16" (87.3 mm)	2-1/8" (53.9 mm)	3-9/16" (90.5 mm)	2-15/16" (74.6 mm)	3-1/8" (79.4 mm)	1-7/8" (47.6 mm)	3-3/4" (95.3 mm)	3-3/8" (85.7 mm)
Minimum Chuck Size		3/8" (9.5 mm)	3/8" (9.5 mm)	3/8" (9.5 mm)	3/8" (9.5 mm)	3/8" (9.5 mm)	3/8" (9.5 mm)	3/8" (9.5 mm)	3/8" (9.5 mm)	3/8" (9.5 mm)	3/8" (9.5 mm)	3/8" (9.5 mm)
Maximum Material Thickness		10 gauge (3.5 mm)	10 gauge (3.5 mm)	3/8" (9.5 mm)	10 gauge (3.5 mm)	10 gauge (3.5 mm)	10 gauge (3.5 mm)	10 gauge (3.5 mm)	10 gauge (3.5 mm)	10 gauge (3.5 mm)	1/4" (6.4 mm)	1/4" (6.4 mm)

DRILL/TAPS

Electrician's Drill/Driver Set



DDKIT-1-68



A PRODUCT VIDEO IS AVAILABLE, SCAN THIS QR CODE OR VISIT:
www.youtube.com/GreenleeDEMO



SPECIFICATIONS **DDKIT-1-68**

Length	12.32" (313 mm)
Width	10.75" (273 mm)
Height	1.95" (49 mm)
Weight	2.35 lbs (1.06 kg)

- 1/4" Quick Change technology
- Professional grade driver bits
- Titanium Nitride coated self-centering high speed drill bits
- High quality shock resistant case stays intact even after accidental drops
- Hammer drill rated carbide grade tips and hardened shank masonry drill bits
- Hardened forged magnetic nut drivers fit most TapCon® fasteners
- Quick release chuck with precise fit
- Includes security bits that fit most security fasteners frequently used in public facilities

CAT. NO.	UPC NO.	DESCRIPTION
DDKIT-1-68	26313	68-Piece Electrician's Drill/Driver Kit

Combination Drill/Tap Bits



DTAPKIT



LDTAPKIT

**UP TO
4X
FASTER***

Standard Length:




DTAP1/4-20

Long Length:



LDTAP1/4-20



- Tap holes up to 4X faster than traditional methods
- One-piece Drill/Tap design ensures proper hole for tap size
- Hardened High-Speed Steel construction
- Standard length: Drills and taps up to 1/8" material
- Long length: Drills and taps up to 1/2" material*
- Quick-change adapter included in all kits

SPECIFICATIONS

Material thickness	Standard length: up to 1/8" material Long length: up to 1/2" material
Material type	Mild steel, copper, brass, aluminum
Shank	1/4" quick change hex
Drill Material	High-speed steel
Drill point	Split point with web thinning

CAT. NO.	UPC NO.	DESCRIPTION	DTAPKIT	DTAPKITM	LDTAPKIT
DTAPKIT	17620	6-32 to 1/4-20 6-piece Drill Tap Set	✓		
DTAPKITM	12151	Metric, M3-M10 6-Piece Drill/Tap Set		✓	
LDTAPKIT	00909	8-32 to 1/4-20, 6-piece Long Drill/Tap Bit Kit with Quick-Change Adapter			✓

DTAP6-32	17611	6-32NC Drill/Tap Bit	✓		
DTAP8-32	17612	8-32NC Drill/Tap Bit	✓		
DTAP10-24	17613	10-24NC Drill/Tap Bit	✓		
DTAP10-32	17614	10-32NF Drill/Tap Bit	✓		
DTAP12-24	17615	12-24NC Drill/Tap Bit	✓		
DTAP1/4-20	17616	1/4-20NC Drill/Tap Bit	✓		
DTAP5/16-18	11627	5/16-18NC Drill/Tap Bit			
DTAP3/8-16	11628	3/8-16NC Drill/Tap Bit			
DTAPM3C	12160	M3 X .50 Drill/Tap Bit		✓	
DTAPM4C	12161	M4 X .70 Drill/Tap Bit		✓	
DTAPM5C	12162	M5 X .80 Drill/Tap Bit		✓	
DTAPM6C	12163	M6 X 1.00 Drill/Tap Bit		✓	
DTAPM8C	12164	M8 X 1.25 Drill/Tap Bit		✓	
DTAPM10C	12165	M10 X 1.50 Drill/Tap Bit		✓	
LDTAP8-32	00908	8-32NC Long Drill/Tap Bit			✓
LDTAP10-32	00907	10-32NF Long Drill/Tap Bit			✓
LDTAP1/4-20	00906	1/4-20NC Long Drill/Tap Bit			✓



*When compared to standard drill, tap, and countersink tools

+For best results, use Greenlee cutting oil with Drill/Tap bits. Always reverse drill rotation when backing bit out of hole. For material thicker than 1/4"; stop and reverse drill to clear chips mid-way through tapping process.