

Bandit Series

Page 1 of 2

Features

- One-piece die-cast aluminum housing, finned for more effective heat dissipation. Die-cast aluminum lens frame, hinged for easy re-lamping, secured with four stainless steel screws. Standard finish is Duraplex II Bronze Electrostatic Powder coat.
- Lens is a clear, tempered, shock and heat resistant glass, silicone-gasketed to lens frame for weather-tight seal.
- Semi-specular anodized aluminum reflector for maximum utilization of lamp lumens. Hinged reflector design permits easy access to ballast for wiring and maintenance.

Yoke Mount: Formed painted steel construction, with 180° of adjustability, includes 3' [91.44mm] SOW cable.


- Porcelain, 4 kV pulse rated, Mogul based lampholder with grip-type socket which prevents lamp loosening.
- EPA: Effective Projected Area = 1.7 ft² [0.16 m²]
- Comes with 3 year limited warranty.
- CSA Approved for Wet Locations



Available in 250W & 400W Metal Halide & High Pressure Sodium



Dimensions



Job Information

Type:

Job Name:

Cat. No.:

Lamp(s):

Notes:

Bandit Series

Page 2 of 2

Ordering information

Explanation of catalog number: Example: BTY400MAL-TW

BTY					-		
Series: BTY: Bandit Yoke Mount ¹	Lamp Wattage²: 250 = 250W 400 = 400W	Light Source: MA = Metal Halide LX = High Pressure Sodium	Lamp Included: L = Yes (not available For INC)	Options: FS = Fusing (120,277,347V Only) TLR = Twist Lock Photocontrol Receptacle	Voltage: T = Tri-Tap (120/277/347V)	Finish³: Blank = Bronze W = White B = Black G = Grey	

1 Supplied with 3' S0VW cable.

2 MA (250,400W); LX (250,400W)

3 For other housing finishes, consult factory for available colours & colour codes.

Job Information

Type:



© 2013 Koninklijke Philips Electronics N.V. All rights reserved.
Specifications are subject to change without notice.
www.philips.com/luminaires

SD0562 05/13

Philips Lighting Company
200 Franklin Square Drive
Somerset, NJ 08873
Phone: 855-486-2216

Philips Lighting Company
281 Hillmount Road
Markham ON, Canada L6C 2S3
Phone: 800-668-9008