

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Reflector Trim Frame-In Kit — See Individual Frame-In Kit Specification Sheets

	Incandescent			
	Frame-In Kit	Ceiling Type	Lamping	Height
1122 Matte White with Matte Black Step Baffle	1102P1	Non-IC	75W PAR30*	5 15/16"
	1103R	Non-IC Remodeler	85W BR30	5 15/16"
1122WH Matte White with White Step Baffle	1100IC	IC	75W PAR30*	7 5/16"
	1100AICM	AirSeal® IC	85W BR30	7 5/16"
	1100DICM	Deep IC		9 1/4"
	1100DAICM	Deep AirSeal® IC	75W PAR30*	9 1/4"
	1104ICX/N	AirSeal® IC	85W BR30	7 1/4"

*See Socket Extender Accessory or use Par 30L

Features

- Housing:** Hydroformed aluminum, .040" thick (18 ga.); matte white trim flange.
- Eyeball Housing:** Die-formed, one piece, aluminum, .040" thick; provides 358° horizontal rotation and 0° to 40° vertical; matte white finish.
- Step Baffle:** Die-cast aluminum with stepped conical surface for low brightness; precision-fitted into eyeball housing; matte black or white finish.
- Frame-In Kit:** (1102P1 standard frame shown). Other frames listed above and shown on the right. See Frame-In Kit specification sheets for more details.

Options & Accessories

- Retaining Clips:** **1955** - For installing in existing ceiling
- Medium-Based PAR30 Socket Extender:** **1968** - For use w/short neck PAR30 lamps in P1 housing

Labels

UL (Suitable for Damp Locations), I.B.E.W.

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	


Lightolier a Genlyte company www.lightolier.com
 631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710
 We reserve the right to change details of design, materials and finish.
 © 2011 Genlyte Group LLC • F0711



		Narrow				Medium														
		50W PAR30 NSP (T-H)		75W PAR30 NSP (T-H)		50W PAR30 NFL (T-H)		75W R30 SP	75W PAR30 NFL (T-H)											
DISTANCE 0' 1' 2' 3' 4' 5' 6'																				
	FOOTCANDLES (On Beam Center At 6')	181		291		49		43	83											
	BEAM SPREAD (To 50% Max. CP)	12'		12'		32'		26'	32'											
	MAX. CANDLEPOWER (Candelas)	6,500		10,500		1,750		1,540	3,000											
	RATED LIFE (Hours)	2,000		2,000		2,000		2,000	2,000											
0° AIMING ANGLE Illumination on Horizontal Plane 	D	FC	L	W	D	FC	L	W	D	FC	L	W	D	FC	L	W	D	FC	L	W
	6'	181	1.3'	1.3'	8'	164	1.7'	1.7'	4'	109	2.3'	2.3'	4'	96	1.8'	1.8'	6'	83	3.4'	3.4'
	8'	102	1.7'	1.7'	12'	73	2.5'	2.5'	6'	49	3.4'	3.4'	6'	43	2.8'	2.8'	8'	47	4.6'	4.6'
	10'	65	2.1'	2.1'	16'	41	3.4'	3.4'	8'	27	4.8'	4.8'	8'	24	3.7'	3.7'	10'	30	5.7'	5.7'
30° AIMING ANGLE Illumination on Horizontal Plane 	D	FC	L	W	D	FC	L	W	D	FC	L	W	D	FC	L	W	D	FC	L	W
	5'	169	1.4'	1.2'	7'	139	2.0'	1.7'	3'	126	2.4'	2.0'	3'	111	1.9'	1.6'	5'	78	3.9'	3.3'
	7'	86	2.0'	1.7'	10'	68	2.8'	2.4'	5'	45	3.9'	3.3'	5'	40	3.1'	2.7'	7'	40	5.5'	4.6'
	9'	52	2.5'	2.2'	13'	40	3.7'	3.2'	7'	23	5.5'	4.6'	7'	20	4.4'	3.7'	9'	24	7.1'	6.0'
30° AIMING ANGLE Illumination on Vertical Plane 	D	FC	L	W	D	FC	L	W	D	FC	L	W	D	FC	L	W	D	FC	L	W
	2'	203	1.7'	0.8'	3'	146	2.6'	1.3'	1'	219	3.0'	1.1'	1'	193	2.2'	0.9'	2'	94	6.1'	2.3'
	3'	90	2.6'	1.3'	4'	82	3.5'	1.7'	2'	55	6.1'	2.3'	2'	48	4.4'	1.8'	3'	42	9.1'	3.4'
	4'	51	3.5'	1.7'	5'	53	4.3'	2.1'	3'	24	9.1'	3.4'	3'	21	6.6'	2.8'	4'	23	12.2'	4.6'
5'	33	4.3'	2.1'	6'	36	5.2'	2.5'	4'	14	12.2'	4.6'	4'	12	8.8'	3.7'	5'	15	15.2'	5.7'	

		Wide														
		50W PAR30 FL (T-H)		75W R30 FL		75W PAR30 FL (T-H)		100W R30 FL								
DISTANCE 0' 1' 2' 3' 4' 5' 6'																
	FOOTCANDLES (On Beam Center At 6')	31		11		50		18								
	BEAM SPREAD (To 50% Max. CP)	42'		81'		42'		60'								
	MAX. CANDLEPOWER (Candelas)	1,100		400		1,800		680								
	RATED LIFE (Hours)	2,000		2,000		2,000		2,000								
0° AIMING ANGLE Illumination on Horizontal Plane 	D	FC	L	W	D	FC	L	W	D	FC	L	W	D	FC	L	W
	3'	122	2.3'	2.3'	2'	100	3.4'	3.4'	4'	113	3.1'	3.1'	2'	170	2.3'	2.3'
	5'	44	3.8'	3.8'	4'	25	5.8'	5.8'	6'	50	4.6'	4.6'	4'	43	4.6'	4.6'
	7'	22	5.4'	5.4'	6'	11	10.5'	10.5'	8'	28	6.1'	6.1'	6'	19	6.9'	6.9'
30° AIMING ANGLE Illumination on Horizontal Plane 	D	FC	L	W	D	FC	L	W	D	FC	L	W	D	FC	L	W
	3'	79	3.2'	2.7'	2'	65	6.0'	3.9'	3'	130	3.2'	2.7'	2'	110	3.5'	2.7'
	5'	29	5.4'	4.4'	4'	16	12.0'	7.9'	5'	47	5.4'	4.4'	4'	27	6.9'	5.3'
	7'	15	7.5'	6.2'	6'	7	18.1'	11.8'	7'	24	7.5'	6.2'	6'	12	10.4'	8.0'
30° AIMING ANGLE Illumination on Vertical Plane 	D	FC	L	W	D	FC	L	W	D	FC	L	W	D	FC	L	W
	1'	138	5.5'	1.5'	1'	50	†	1.3'	1'	255	5.5'	1.5'	1'	85	†	2.3'
	2'	34	11.0'	3.1'	2'	13	†	1.7'	2'	56	11.0'	3.1'	2'	21	†	4.6'
	3'	15	16.5'	4.6'	3'	6	†	2.1'	3'	25	16.5'	4.6'	3'	9	†	6.9'
4'	9	22.0'	6.1'	4'	3	†	2.5'	4'	14	22.0'	6.1'	4'	5	†	9.2'	

† Exceeds useable limits.
Data are based on bare lamp photometrics.
FC is initial footcandles at center of beam. L and W are to the point that the candlepower drops 50% of maximum



Job Information **Type:**

Lightolier a Genlyte company www.lightolier.com
631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710
We reserve the right to change details of design, materials and finish.
© 2011 Genlyte Group LLC • F0711

LIGHTOLIER®