


SÉRIE DX SERIES

DE PIÈCE / PART # : DX ___ _ YZ

SPÉCIFICATIONS ÉLECTRIQUES / ELECTRICAL SPECIFICATIONS



* 250VA@750VA
 ** 1000VA@3000VA

PHASE: 1

FREQ.: 50/60 Hz.
 ***60 Hz.


CLASSE ISOL. / INSUL. CLASS: *B(130°C)
 **H(180°C)

ELEV. TEMP. / TEMP. RISE: * < 80°C
 ** < 120°C

NIV. DE BRUIT / SOUND LEVEL: < 40 dB.

TENSION / YZ / VOLTAGE


A = 12 J = 347
 B = 24 K = 347/380
 C = 12/24 L = 347/380
 D = 16/32 M = 416
 E = 120 N = 208/416
 F = 208 O = 480***
 G = 240 P = 240/480
 H = 120/240 Q = 600***
 I = 277 S = _____
 U = 480/600***



VA	0250	0500	0750	1000	1500	2000	3000
A	5.12	5.12	5.12	5.12	7.50	7.50	7.50
B	5.85	5.85	5.85	5.85	7.25	7.25	7.25
C	10.4	10.4	10.4	10.4	11.9	11.9	11.9
D MTG	4.00	4.00	4.00	4.00	5.50	5.50	5.50
E MTG	9.75	9.75	9.75	9.75	11.2	11.2	11.2
F MTG	Ø 0.24						
LBS	20.0	21.9	23.4	23.4	44.5	51.7	56.5
KG	9.07	9.93	10.6	10.6	20.2	23.5	25.6

SPÉCIFICATIONS MÉCANIQUES / MECHANICAL SPECIFICATIONS: (dimensions = pouces/inches).

Toutes les dimensions sont approximatives. Spécifications peuvent changer sans préavis. All dimensions and weights are approximate. Specifications may change without notice.

						NUMÉRO DE MODÈLE: / MODEL NUMBER:		
						DX ___ _ YZ		
ZONE	REV	REVISION	DESCRIPTION	DATE	APPROVAL APPROB.	Dessiné par: / Drawn by: SS	DWG NO. / 71CUDXF0	REV / 02
DATE: MARCH/12/08						PAGE: 1 de 1		