

COMPACT MULTIPURPOSE BASEBOARD

SBB SERIES

A BREAKTHROUGH IN PERFORMANCE & DESIGN

Looking for the sleekest and newest baseboard ever to heat a living room, kitchen, bedroom or even an office, without taking up too much wall space? The compact multipurpose SBB baseboard fits the bill perfectly with three densities available. On top of being quick and easy to install, the SBB can be up to 30% shorter than conventional baseboards without sacrificing power and security.



UP TO 30% SHORTER THAN CONVENTIONAL BASEBOARDS

FREED UP PRECIOUS WALL SPACE

OPTIMAL PERFORMANCE AND SAFETY COMBINED WITH EASE OF INSTALLATION

OFFERED IN THREE DIFFERENT WATT DENSITIES

TO MEET THE NEEDS OF ANY PROJECT IN THE HOME AND OFFICE

IDEAL FOR:

KITCHEN, LIVING ROOM, BEDROOM, BASEMENT, OFFICE

COLOURS

- standard: white, soft white
- ORORA (optional): denim blue, midnight blue, turquoise, moss green, canary yellow, red, orange, anodized aluminum paint, gravel gray, charcoal, espresso, black (refer to [page 8 of the catalogue](#))

FINISH

epoxy-polyester powdercoat

MANUFACTURING

- 22-gauge steel cabinet and 18-gauge steel one-piece front able to support up to 110 kg (242 lb) in its center
- full-length thermal protection with automatic reset
- discreet air inlet and top air discharge to maximize air flow
- full-length wireway
- steel end caps with soft, rounded corners

ELEMENT

single tubular, stainless steel sheathed element with boxed aluminum fins for improved heat dissipation securely fastened at its center, floating in nylon sleeves at each end, eliminating expansion and contraction noises

CONTROL

- wall thermostat (not included) – the use of an electronic thermostat is strongly recommended
- built-in single or double pole mechanical thermostat installed in the left or right junction box (optional)
- built-in tamper-proof single or double pole mechanical thermostat installed in the left or right junction box (optional)
- low voltage relay kit installed in the right junction box only (optional)

INSTALLATION

- floor mounted
- wiring compartment at both ends of unit

ACCESSORIES

PRODUCT	DESCRIPTION	PRICE
SBBT1*	built-in single pole thermostat [120 V-600 V]	21.75
SBBT2*	built-in double pole thermostat [120 V-600 V]	25.75
SBBT1TP**	built-in tamper-proof single pole thermostat [120 V-600 V]	37.00
SBBT2TP**	built-in tamper-proof double pole thermostat [120 V-600 V]	37.00
SBBRE153*	built-in electronic low voltage relay [15 A @ 120 V-347 V]	45.50
SBBRE156*	built-in electronic low voltage relay [6 A @ 600 V]	77.00
SBBRE153T*	built-in electronic low voltage relay c/w transformer 24 V [15 A @ 208 V-347 V]	59.25
SBBRM240T*	electro. mecha. relay c/w transformer 24 V [6000 W @ 240 V and 5200 W @ 208 V]	73.25
SBBRM347T*	electro. mecha. relay c/w transformer 24 V [6000 W @ 347 V]	82.25
SBBRM347C*	electro. mecha. relay w/o transformer 24 V [6000 W @ 120-347 V]	60.75
SBBR841C1151*	built-in mechanical low voltage relay with transformer 24 V [6000 W @ 600 V]	115.00
SBBR841D1036*	built-in mechanical low voltage relay w/o transformer 24 V [6000 W @ 600 V]	100.00

Electronic relays can receive a PWM (pulsed width modulation) or digital (on/off) signal.

* Add W for white or BK for black (white unit supplied with a white knob and soft white or optional colored units supplied with a black knob)

* Factory installed * Factory installation is strongly recommended

PART OF THE SHC FAMILY OF PRODUCTS

NEED A CONVECTOR?
SEE PAGE 16




TECHNICAL SPECIFICATIONS

STANDARD DENSITY 350 W PER LINEAR FOOT *			MEDIUM DENSITY 275 W PER LINEAR FOOT *			LOW DENSITY 200 W PER LINEAR FOOT *			VOLTAGE	LENGTH	WEIGHT		
CODE	WATTS	PRICE	CODE	WATTS	PRICE	CODE	WATTS	PRICE	VOLTS	MM	IN	KG	LB
SBB0501	500	45.50	SBBM0401	400	51.00	SBBL0301	300	51.00	120	609	24	2.6	5.7
SBB0508	500	37.75	SBBM0408	400	42.25	SBBL0308	300	42.25	208	609	24	2.6	5.7
SBB0502	500/375	37.75	SBBM0402	400/300	42.25	SBBL0302	300/225	42.25	240/208	609	24	2.6	5.7
SBB0507	500/375/280	37.75	SBBM0407	400/300/225	42.25	---	---	---	277/240/208	609	24	2.6	5.7
SBB0503	500	45.50	---	---	---	---	---	---	347	609	24	2.6	5.7
SBB0751	750	52.50	SBBM0601	600	59.00	SBBL0451	450	59.00	120	762	30	3	6.7
SBB0758	750	43.00	SBBM0608	600	48.25	SBBL0458	450	48.25	208	762	30	3	6.7
SBB0752	750/560	43.00	SBBM0602	600/450	48.25	SBBL0452	450/340	48.25	240/208	762	30	3	6.7
SBB0757	750/560/420	43.00	SBBM0607	600/450/340	48.25	SBBL0457	450/340/255	48.25	277/240/208	762	30	3	6.7
SBB0753	750	52.50	SBBM0603	600	59.00	SBBL0453	450	59.00	347	762	30	3	6.7
SBB0755	750	52.50	---	---	---	---	---	---	480	762	30	3	6.7
SBB1001	1000	62.75	SBBM0801	800	70.25	SBBL0601	600	70.25	120	914	36	3.5	7.7
SBB1008	1000	50.50	SBBM0808	800	56.50	SBBL0608	600	56.50	208	914	36	3.5	7.7
SBB1002	1000/750	50.50	SBBM0802	800/600	56.50	SBBL0602	600/450	56.50	240/208	914	36	3.5	7.7
SBB1007	1000/750/560	50.50	SBBM0807	800/600/450	56.50	SBBL0607	600/450/340	56.50	277/240/208	914	36	3.5	7.7
SBB1003	1000	62.75	SBBM0803	800	70.25	SBBL0603	600	70.25	347	914	36	3.5	7.7
SBB1005	1000	62.75	SBBM0805	800	70.25	SBBL0605	600	70.25	480	914	36	3.5	7.7
SBB1006	1000	62.75	---	---	---	---	---	---	600	914	36	3.5	7.7
SBB1251	1250	74.00	SBBM1001	1000	83.00	SBBL0751	750	83.00	120	1066	42	4	8.7
SBB1258	1250	59.25	SBBM1008	1000	66.25	SBBL0758	750	66.25	208	1066	42	4	8.7
SBB1252	1250/940	59.25	SBBM1002	1000/750	66.25	SBBL0752	750/560	66.25	240/208	1066	42	4	8.7
SBB1257	1250/940/705	59.25	SBBM1007	1000/750/560	66.25	SBBL0757	750/560/420	66.25	277/240/208	1066	42	4	8.7
SBB1253	1250	74.00	SBBM1003	1000	83.00	SBBL0753	750	83.00	347	1066	42	4	8.7
SBB1255	1250	74.00	SBBM1005	1000	83.00	SBBL0755	750	83.00	480	1066	42	4	8.7
SBB1256	1250	74.00	SBBM1006	1000	83.00	---	---	---	600	1066	42	4	8.7
SBB1501	1500	81.50	SBBM1201	1200	91.25	SBBL0901	900	91.25	120	1219	48	4.4	9.7
SBB1508	1500	65.25	SBBM1208	1200	73.25	SBBL0908	900	73.25	208	1219	48	4.4	9.7
SBB1502	1500/1125	65.25	SBBM1202	1200/900	73.25	SBBL0902	900/675	73.25	240/208	1219	48	4.4	9.7
SBB1507	1500/1125/845	65.25	SBBM1207	1200/900/675	73.25	SBBL0907	900/675/510	73.25	277/240/208	1219	48	4.4	9.7
SBB1503	1500	81.50	SBBM1203	1200	91.25	SBBL0903	900	91.25	347	1219	48	4.4	9.7
SBB1505	1500	81.50	SBBM1205	1200	91.25	SBBL0905	900	91.25	480	1219	48	4.4	9.7
SBB1506	1500	81.50	SBBM1206	1200	91.25	SBBL0906	900	91.25	600	1219	48	4.4	9.7
---	---	---	SBBM1401	1400	110.00	SBBL1051	1050	110.00	120	1371	54	4.9	10.7
SBB1758	1750	76.50	SBBM1408	1400	85.50	SBBL1058	1050	85.50	208	1371	54	4.9	10.7
SBB1752	1750/1310	76.50	SBBM1402	1400/1050	85.50	SBBL1052	1050/790	85.50	240/208	1371	54	4.9	10.7
SBB1757	1750/1310/985	76.50	SBBM1407	1400/1050/790	85.50	SBBL1057	1050/790/590	85.50	277/240/208	1371	54	4.9	10.7
SBB1753	1750	97.75	SBBM1403	1400	110.00	SBBL1053	1050	110.00	347	1371	54	4.9	10.7
SBB1755	1750	97.75	SBBM1405	1400	110.00	SBBL1055	1050	110.00	480	1371	54	4.9	10.7
SBB1756	1750	97.75	SBBM1406	1400	110.00	SBBL1056	1050	110.00	600	1371	54	4.9	10.7
---	---	---	SBBM1601	1600	120.00	SBBL1201	1200	120.00	120	1524	60	5.3	11.7
SBB2008	2000	83.75	SBBM1608	1600	94.00	SBBL1208	1200	94.00	208	1524	60	5.3	11.7
SBB2002	2000/1500	83.75	SBBM1602	1600/1200	94.00	SBBL1202	1200/900	94.00	240/208	1524	60	5.3	11.7
SBB2007	2000/1500/1125	83.75	SBBM1607	1600/1200/900	94.00	SBBL1207	1200/900/675	94.00	277/240/208	1524	60	5.3	11.7
SBB2003	2000	108.00	SBBM1603	1600	120.00	SBBL1203	1200	120.00	347	1524	60	5.3	11.7
SBB2005	2000	108.00	SBBM1605	1600	120.00	SBBL1205	1200	120.00	480	1524	60	5.3	11.7
SBB2006	2000	108.00	SBBM1606	1600	120.00	SBBL1206	1200	120.00	600	1524	60	5.3	11.7
---	---	---	---	---	---	SBBL1351	1350	125.00	120	1676	66	5.8	12.7
SBB2258	2250	92.50	SBBM1808	1800	104.00	SBBL1358	1350	104.00	208	1676	66	5.8	12.7
SBB2252	2250/1690	92.50	SBBM1802	1800/1350	104.00	SBBL1352	1350/1010	104.00	240/208	1676	66	5.8	12.7
SBB2257	2250/1690/1265	92.50	SBBM1807	1800/1350/1010	104.00	SBBL1357	1350/1010/760	104.00	277/240/208	1676	66	5.8	12.7
SBB2253	2250	112.00	SBBM1803	1800	125.00	SBBL1353	1350	125.00	347	1676	66	5.8	12.7
SBB2255	2250	112.00	SBBM1805	1800	125.00	SBBL1355	1350	125.00	480	1676	66	5.8	12.7
SBB2256	2250	112.00	SBBM1806	1800	125.00	SBBL1356	1350	125.00	600	1676	66	5.8	12.7
---	---	---	---	---	---	SBBL1501	1500	136.00	120	1828	72	6.2	13.7
SBB2508	2500	101.00	SBBM2008	2000	114.00	SBBL1508	1500	114.00	208	1828	72	6.2	13.7
SBB2502	2500/1875	101.00	SBBM2002	2000/1500	114.00	SBBL1502	1500/1125	114.00	240/208	1828	72	6.2	13.7
SBB2507	2500/1875/1410	101.00	SBBM2007	2000/1500/1125	114.00	SBBL1507	1500/1125/845	114.00	277/240/208	1828	72	6.2	13.7
SBB2503	2500	121.00	SBBM2003	2000	136.00	SBBL1503	1500	136.00	347	1828	72	6.2	13.7
SBB2505	2500	121.00	SBBM2005	2000	136.00	SBBL1505	1500	136.00	480	1828	72	6.2	13.7
SBB2506	2500	121.00	SBBM2006	2000	136.00	SBBL1506	1500	136.00	600	1828	72	6.2	13.7

Add W for white or SW for soft white (see [page 8 of the catalogue](#) for optional colours and contact your *STELPRO representative for all other colours)
 Add HA for the high altitude version
 * Average densities shown.
 --- not available

TECHNICAL DRAWINGS



*STELPRO reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. Returns are not accepted for orders of products with optional colours.
 For all the latest models and updated prices, please refer to our website at www.stelpro.com.