

ETP™ 6000S Steel EMT Compression Couplings

NEC/CEC:
Listed for Ordinary Locations

Application

- To ground and secure EMT raceway sections together.

Features

- Concretetight.
- Raintight (wet locations) Canada.

Material/Finish

- Body and nut: steel.
- Steel/zinc plated

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-14895
- cUL Listed: E-14895, E14815
- CSA Certified: 009795
- NEMA: FB-1



6050S – 6400S

Trade Size (Inches)	Dimensions in Millimeters (Inches)			Weight per 100 kg (lb)	Catalog Number
	Body Length	Maximum Diameter			
1/2	35.1 (1.38)	21.3 (0.84)		8.6 (19.00)	6050S
3/4	38.1 (1.50)	35.1 (1.38)		11.3 (25.00)	6075S
1	42.2 (1.66)	33.3 (1.31)		17.7 (39.00)	6100S
1-1/4	63.5 (2.50)	42.9 (1.69)		39.9 (88.00)	6125S
1-1/2	63.5 (2.50)	49.3 (1.94)		47.2 (104.00)	6150S
2	63.5 (2.50)	60.5 (2.38)		67.6 (149.00)	6200S
2 - 1/2	108.0 (4.25)	79.5 (3.13)		108.9 (240.00)	6250S
3	114.3 (4.50)	95.3 (3.75)		158.8 (350.00)	6300S
3 - 1/2	120.7 (4.75)	108.0 (4.25)		215.5 (475.00)	6350S
4	127.0 (5.00)	120.7 (4.75)		272.2 (600.00)	6400S

ETP™ 6000US Steel EMT Compression Couplings

NEC/CEC:
Listed for Ordinary Locations

Application

- To ground and secure EMT raceway sections together.

Features

- Made in the U.S.A.
- Concretetight.
- Raintight (wet locations) Canada.

Material/Finish

- Body and nut: steel.
- Steel/zinc plated

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: (1/2 - 3) E14815
- CSA Standard: C22.2 No. 18.3
- cUL Listed: (1/2 - 3) E14815
- NEMA: FB-1



6050S — 6200US



6250US — 6400US

Trade Size (Inches)	Dimensions in Millimeters (Inches)			Catalog Number
	Body Length	Maximum Diameter		
1/2	34.0 (1.34)	0.97 (24.6)		6050US
3/4	34.0 (1.34)	31.0 (1.22)		6075US
1	35.8 (1.41)	38.1 (1.50)		6100US
1-1/4	44.5 (1.75)	48.5 (1.91)		6125US
1-1/2	47.8 (1.88)	54.9 (2.16)		6150US
2	54.1 (2.13)	68.3 (2.69)		6200US
2 - 1/2	139.7 (5.50)	104.9 (4.13)		6250US
3	139.7 (5.50)	119.1 (4.69)		6300US
3 - 1/2	143.0 (5.63)	135.6 (5.34)		6350US
4	146.1 (5.75)	149.4 (5.88)		6400US