

McGILL® Incandescent Utility Lights



Applications

- Ideal for food processing plants, barns, garages, warehouses, and workshops.
- Low cost, corrosion-resistant, enclosed utility lights, complete with base, wiring box, and globe, are convenient to use.

Features

- Fasten directly to walls, ceilings, or structural members — no separate outlet box required.
- Glass or plastic globes screw out for easy replacement of A-21 bulbs (not included) up to 150 Watts.
- High quality materials and sockets assure long, trouble-free service life.
- 3-1/2"/88.9 mm diameter; 9-1/2"/241.3 mm height
- Two 5/16"/7.9 mm diameter mounting holes on 4-3/8"/111.3 mm centers.
- Moisture-resistant construction with no exposed metal parts.
- Large compartment for easy wiring.
- Super strong, impact-resistant, thermoplastic mounting unit.
- For use up to 100 °F/38 °C ambient temperature.
- Accommodates up to 150 Watts max. domestic A-21 bulbs.
- For use with either 1/2"/12.7 mm or 3/4"/19.1 mm rigid non-metallic conduit.

Certifications and Compliances

- UL Listed: E8646
- UL Standard: 1598
- CSA Certified: LL56247 
- CSA Listed: C22.2 No. 250.0 



606 with 1435-6



653

McGILL Incandescent Utility Lights

	Wiring Compartment Cubic Inch/Cubic Decimeter	Supply Wire Rating °F/°C	Catalog Numbers	
			1/2"/12.7 mm Threaded Conduit Opening	3/4"/19.1 mm Threaded Conduit Opening
Utility light with glass globe				
For damp locations	15/0.25	257/125	600	601
For damp locations	15/0.25	221/105	C600 ^{CSA}	C601 ^{CSA}
For damp locations	12/0.20	140/60	603	604
For damp locations	12/0.20	140/60	C603 ^{CSA}	C604 ^{CSA}
Sealed unit for wet locations	12/0.20	140/60	605	606
Sealed unit for wet locations	12/0.20	140/60	C605 ^{CSA}	C606 ^{CSA}
Utility light with clear plastic globe ①				
For damp locations	15/0.25	257/125	640	641
For damp locations	15/0.25	221/105	C640 ^{CSA}	C641 ^{CSA}
For damp locations	12/0.20	140/60	643	644
For damp locations	12/0.20	140/60	C643 ^{CSA}	C644 ^{CSA}
Utility light with red plastic globe ①				
For damp locations	15/0.25	257/125	650	651
For damp locations	15/0.25	221/105	C650 ^{CSA}	C651 ^{CSA}
For damp locations	12/0.20	140/60	653	654
For damp locations	12/0.20	140/60	C653 ^{CSA}	C654 ^{CSA}
Accessories and Replacement Parts — Additional plastic globes see Protect-O-Globes				
				Catalog Number
Protective metal cage for glass globes only				1435-6
Base and socket only for 600, 640, and 650				610
Base and socket only for 601, 641, and 651				611
Base and socket only for 603, 643 and 653				5213-0623
Base and socket only for 604, 644 and 654				5213-0672
Base, socket, and seal assembly only for 605				5213-0637
Base, socket, and seal assembly only for 606				5213-0638
Socket only for 15 cubic inch/ 0.25 cubic decimeter wiring compartment				600-3
Socket only for 12 cubic inch/0.20 cubic decimeter wiring compartment				606-3
Glass globe only for 600, 601, 603, and 604 - 6-11/16"/296.9 mm long				0753
Glass globe only for 605 and 606 - 6-11/16"/296.9 mm long				0753-HR ②
Clear plastic globe only for 640, 641, 643 and 644 - 6-1/8"/6.1 mm long				649
Red plastic globe only for 650, 651, 653 and 654 - 6-1/8"/6.1 mm long				659
Green plastic globe only - 6-1/8"/6.1 mm long				669

① Plastic globes max. 75 Watt base-up mounting.

② Heat resistant globes required for wet locations.

^{CSA} CSA Certification only.