## Technical Information Bulletin

Date:	
In hands date of project:	
Project name/Number:	
Name of distributor:	
Client #:	
Name of end user:	

# Diameter ΜĎ

Dia.: 2 15/32 in. (63 mm)

MOL: 3 11/32 in. (85 mm)

DIMMER COMPATIBILITY LIST

SAL06P, SLC03P, AAL06

DVCL-153P, CTCL-153P, MACL-153P, AYCL-

253P, DVCL-253P, DVELV-300P, SELV-300P

HCL453P

IPL06, 6674

Legrand

Cooper

Leviton

Lutron

### ORDERING INFORMATION

Order code: 63951

Description: LED/P20/7W/27K/40/STD

UPC: 69549639515

Case quantity: 12

### PERFORMANCE DATA

PAR20 Shape: Base: E26 Wattage (W): Lamp voltage (VAC): 120 Colour temperature (K)\*\*: 2 700 40 000 Average life (L70 hours): Initial lumens (lm)\*: 509 Initial lumens per watt (lm/W): 73 CRI: 92 R9: 55 40 Beam angle (°): CBCP: 936 Power factor: 0.93

- 40 °C / - 40 °F to 40 °C / 104 °F Operating temperature range:

\*\*Typical colour temperature range: +/- 10 %

















\* This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

#### CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock do not use where directly exposed to water or weather.
- Not for use in totally enclosed luminaires.
- · Suitable for use in damp locations.
- Do not open no user serviceable parts inside.
  Added weight of the device may cause instability of a freestanding portable luminaire. Use in portable table lamps in which the distance from the bottom of the base to the top of the lamp holder does not exceed three (3) times the minimum base diameter.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- · Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com
- · Not recommended for use with timers.

Qty	Description	Price	
I accept the s	pecifications of the lamp configuration mentione	d above.	
Name:			
Company:			

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



Date:

Signature: