

UL Short Circuit Rating of Eaton Open Components for use in Industrial Control Panels

XT Frame Size	Component Type	Description	Catalog No.	FLA Adjustment Range	Label to be affixed next to device on panel	Max. 3 Ph. Horsepower Ratings				Max. Protective Device - Group Motor Applications					
						200V	230V	460V	575V	Short Circuit Rating -		Max. Fuse (A)		Max. Circuit Breaker (A)	
										Device	w/ XTPAXCL	Device	w/ XTPAXCL	Device	w/ XTPAXCL
B	Transformer Protective Device	Rotary Operated, 3 pole	XTPTP16BC1	0.10 - 0.16	Pub 51226	-	-	-	-	50kA	-	600	-	600	-
			XTPTP16BC1	0.16 - 0.25		-	-	-	-	50kA	-	600	-	600	-
			XTPTP40BC1	0.25 - 0.40		-	-	-	-	50kA	-	600	-	600	-
			XTPTP63BC1	0.40 - 0.63		-	-	-	-	50kA	-	600	-	600	-
			XTPT001BC1	0.63 - 1.0	Pub 51226	-	-	1/2	1/2	50kA	-	600	-	600	-
			XTPT1P6BC1	1.0 - 1.6		-	-	3/4	1	50kA	-	600	-	600	-
			XTPT2P5BC1	1.6 - 2.5		1/2	1/2	1	1.5	50kA	-	600	-	600	-
			XTPT0004BC1	2.5 - 4.0		1	1	2	3	50kA	-	600	-	600	-
			XTPT6P3BC1	4.0 - 6.3	Pub 51226	1.5	1.5	3	5	50kA	-	600	-	600	-
			XTPT010BC1	6.3 - 10		3	3	7.5	10	10kA	50kA	150	600	125	600
			XTPT012BC1	8 - 12		3	3	7.5	10	10kA	50kA	150	600	125	600
			XTPT016BC1	10 - 16	Pub 51226	3	5	10	10	10kA	50kA	150	600	125	600
			XTPT020BC1	16 - 20		5	5	10	15	10kA	18kA	150	600	125	600
			XTPT025BC1	20 - 25		5	7.5	15	20	10kA	18kA	150	600	125	600