

Technical Information Bulletin


Choice LED Panels



Date: _____ Name of distributor: _____
 In hands date of project: _____ Client #: _____
 Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 67157
Description: PAN2X4/100-277/50W/35K/CHOICE/STD
UPC: 69549671577
Case quantity: 1
DLC ID: PL3FZRX5UJRG



PHYSICAL DATA

Size in. (mm): 47.7" x 23.74" (1 212 x 603 mm)
Lens Type: Frosted Polystyrene
Frame Material: White Aluminum Alloy
Mounting: Recessed, suspended or surface


PERFORMANCE DATA

Watts (W): 50
Volts (VAC): 100-277
Colour temp. (K)¹: 3 500
Lumen output (lm)²: 5 194
Lumen per Watts (lm/W): 105
CRI: 83
Life L70 (h)³: 50 000
Beam angle (°) V:112.8 / H:113.3
THD (%): 120 V: 10.62 / 277 V:14.71
Power factor: 120 V: 0.99 / 277 V:0.92
Frequency (Hz): 60
Surge protection (Kv): 1 554 V
Operating temp. range: -20 to 40 °C (-4 to 104 °F)


¹ Typical colour temperature range: +/- 5 %
² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations

WIRING DIAGRAM

Single luminaire



Multiple luminaires



COMPATIBLE ACCESSORIES

Order code	Description	Type
64827	LPAN/ACC/2X4/SMK/STD	Surface mount kit
64829	LPAN/ACC/1X4_2X4/SUSPENSION/STD	Suspension cable
63491	DRYWALL KIT FOR 2X4 FRT/STD	Drywall kit

DESCRIPTION AND OTHER OPTIONS

PAN2X4		/	100-277		/	50W		/	35K		/	CHOICE		/	STD	
Series and size		Volts		Watts		Colour Temperature		Sub-brand		Brand						
PAN1X4	Panel 1 feet x 4 feet	100-277	100-277 V	40 W	35K	3 500 K	CHOICE	Choice	STD	STANDARD						
PAN2X2	Panel 2 feet x 2 feet			50 W	40K	4 000 K										
PAN2X4	Panel 2 feet x 4 feet				50K	5 000 K										

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
 Data is based upon tests performed in a controlled environment and representative of relative performance.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.
 August 2, 2019

Technical Information Bulletin


Choice LED Panels




ORDER CODE: 67157

TECHNICAL DRAWINGS AND DIMENSIONS


Length: 47.7" (1 212 mm)
 Width: 23.74" (603 mm)
 Depth with Driver: 1.77" (45 mm)
 Height for Driver: 1.38" (35 mm)
 Weight: 19.8lbs (9.0KG)



BEAM SPREAD*



CANDELA DISTRIBUTION*



COEFFICIENTS OF UTILIZATION (ZONAL CAVITY METHOD)*

Effective Floor Cavity Reflectance: 20%

RCC %:	80				70				50				30				10				0			
RW %:	70	50	30	0	70	50	30	0	50	30	20	0	50	30	20	0	50	30	20	0	50	30	20	0
RCR: 0	1.19	1.19	1.19	1.19	1.16	1.16	1.16	1.00	1.11	1.11	1.11	1.06	1.06	1.06	1.06	1.02	1.02	1.02	1.02	1.00	1.00	1.00	1.00	1.00
1	1.09	1.04	1.00	.96	1.06	1.02	.98	.84	.97	.94	.91	.88	.93	.91	.88	.86	.90	.88	.86	.84	.84	.84	.84	.84
2	.99	.90	.84	.78	.96	.89	.82	.71	.85	.80	.75	.73	.82	.77	.73	.72	.79	.75	.72	.70	.70	.70	.70	.70
3	.90	.79	.71	.65	.88	.78	.70	.60	.75	.68	.63	.62	.72	.66	.62	.62	.69	.65	.61	.59	.59	.59	.59	.59
4	.82	.70	.61	.55	.80	.69	.61	.52	.66	.59	.54	.53	.64	.58	.53	.53	.62	.57	.52	.50	.50	.50	.50	.50
5	.76	.63	.54	.47	.74	.62	.53	.45	.60	.52	.46	.46	.58	.51	.46	.46	.56	.50	.45	.43	.43	.43	.43	.43
6	.70	.57	.48	.41	.68	.56	.47	.40	.54	.46	.40	.40	.52	.45	.40	.40	.50	.44	.40	.38	.38	.38	.38	.38
7	.65	.51	.42	.36	.63	.50	.42	.35	.49	.41	.36	.36	.47	.41	.36	.36	.46	.40	.35	.33	.33	.33	.33	.33
8	.60	.47	.38	.32	.59	.46	.38	.31	.45	.37	.32	.32	.43	.37	.32	.32	.42	.36	.32	.30	.30	.30	.30	.30
9	.56	.43	.35	.29	.55	.42	.34	.28	.41	.34	.29	.29	.40	.33	.29	.29	.39	.33	.29	.27	.27	.27	.27	.27
10	.53	.40	.32	.26	.52	.39	.31	.26	.38	.31	.26	.26	.37	.31	.26	.26	.36	.30	.26	.24	.24	.24	.24	.24

*Complete IES files available on our website

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____