

Eaton XT IEC contactor

CE15GNS3AB

UPC:782113007878

Dimensions:

- **Height:** 4.27 IN
- **Length:** 4.22 IN
- **Width:** 2.56 IN

Weight:2.12 LB

Notes:No enclosure

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 37A
- **Coil Voltage:** 110-120 Vac, 50-60 Hz
- **Contact Configuration:** 1NO
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 3 hp
- **Mounting:** Side
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Relay:** No overload relay
- **Series:** Freedom
- **Type:** Contactor

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Motor Starters and Contactors - Low Voltage Catalog](#)
- [Eaton Specification Sheet - CE15GNS3AB](#)

Certifications:

- UL Listed



- IEC Rated
- CSA Certified

Product compliance:

- ISO 9000
- DIN VDE 0600

© 2016 Eaton. All rights reserved.