




Industrial Specification Grade Power Devices

2-Pole, 3-Wire Grounding
 NEMA 5-30, 30A 125V
 NEMA 6-30, 30A 250V
 NEMA 7-30, 30A 277V
 NEMA 5-50, 50A 125V
 NEMA 6-50, 50A 250V
 NEMA 7-50, 50A 277V

H-23 Straight Blade Plugs & Connectors



Industrial Specification Grade Power Plugs, Connectors and Flanged Inlets

FEATURES

- Neoprene gasket seals cord hole opening on AutoGrip™ Plug; prevents dust/moisture from entering wiring chamber.
- AutoGrip™ automatic cord grip clamps cord during assembly and reduces wiring time.
- Back-wired dead-front construction with easy wire clamp type terminals.
- Tapered cord grip cover eliminates cord snags.
- High strength thermoplastic plug resists breakage in high abuse locations.
- Angle plug provides four different cord positions.
- Terminals accept #12AWG - #4AWG conductors.

AutoGrip™ Plugs, Connectors and Flanged Inlets

Rating	A	V/AC	NEMA	Description	Cord Diameter	Color	Catalog No. Plug	Catalog No. Connector	Flanged Inlet
30	125	5-30	Straight		0.425-1.310" (10.8-33.3mm)	Gray	5717N	6716N	5717NFI
					Angle	0.560-1.310" (14.2-33.3mm)	Gray	5717AN	—
30	250	6-30	Straight		0.425-1.310" (10.8-33.3mm)	Gray	5701N	6700N	5701NFI
					Angle	0.560-1.310" (14.2-33.3mm)	Gray	5701AN	—
30	277	7-30	Straight		0.425-1.310" (10.8-33.3mm)	Gray	5703N	6795N	5703NFI
					Angle	0.560-1.310" (14.2-33.3mm)	Gray	5703AN	—
50	125	5-50	Straight		0.425-1.310" (10.8-33.3mm)	Gray	5712N	6711N	5712NFI
					Angle	0.560-1.310" (14.2-33.3mm)	Gray	5712AN	—
50	250	6-50	Straight		0.425-1.310" (10.8-33.3mm)	Gray	5710N	6709N	5710NFI
					Angle	0.560-1.310" (14.2-33.3mm)	Gray	5710AN	—
50	277	7-50	Straight		0.425-1.310" (10.8-33.3mm)	Gray	5705N	6796N	5705NFI
					Angle	0.560-1.310" (14.2-33.3mm)	Gray	5705AN	—

TESTING & CODE COMPLIANCE

• Listed to UL 498 Plugs & Inlets; UL verified to Fed. Spec. WC-596 (file no. E3663).
 • CSA certified to C22.2 no. 42 (file no. LR7087), except connectors.

MATERIAL CHARACTERISTICS

Plugs, Nylon and Polypropylene;
 Angle Plugs: Nylon and ABS. Connectors: Nylon, Polypropylene, Phenolic.

Environmental:
 Flammability per UL 94 requirements, Angle Plugs & Inlets: V2 rated.

Temperature Rating:
 -40°C to 95°C except Angle Plugs:
 -40°C to 85°C
 Inlets: -40°C to 75°C.

