

E-series - mission critical power when and where you need it

RhinoBox standard duty temporary power centers are designed to deliver safe and reliable temporary power in industrial and commercial job site conditions

Features & benefits

“Plug & power” E-series temporary power centers provide reliable power for construction sites, renovations, demolition, sporting events, entertainment venues, filmmaking, carnivals and more. Plug into the power of RhinoBox for all your temporary power needs.

Tool less and hinged metal door over circuit breaker panel provides damp location protection



Heavy duty safety yellow steel enclosure provides NEMA 3R weather resistance for long-lasting durability

Clearly marked safety and testing instructions are easy to read



Gasketed lift covers provide superior protection from the elements

Flip covers provide maximum weather resistance

50A locking inlet and receptacle for feed through applications

3/8" holes in legs ideal for caster, sled legs and attachment to fixed surfaces

Sturdy, heavy duty steel legs are reinforced to withstand abuse and provide long lasting performance

Unique interlocking legs provide sturdy and secure stacking for storage and transport

Available with manual or automatic GFCI reset configurations



RhinoBox temporary power centers with GFCI protection E-series

Product description

50A input
20A, 30A, 50A output
120/240 V/AC (max.)



RB300ME

Features

- Safely centralize and distribute temporary power on the job site
- Unique patented “stackable” design allows multiple RhinoBox units to lock together for safe transport and storage
- NEMA 3R enclosures designed with two devices per circuit
- Available with manual or automatic GFCI reset configurations
- Weatherproof receptacle covers protect from damage and weather
- Flip-up circuit breaker cover prevent accidental tripping


RhinoBox E-series

Rating A	V/AC	Distribution devices	Receptacle ratings	Protection		Catalog no.*	
				Overload	GFCI		
50	120/240 Max.	(6) WR duplex receptacles	20A, 125V	✓	✓	☐ RB300ME	•
		(1) Locking receptacle	30A, 250V	✓	—		
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		
50	120/240 Max.	(6) WR duplex receptacles	20A, 125V	✓	✓	☐ RB300ME-L5	•
		(1) Locking receptacle	30A, 125V	✓	—		
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		
50	120/240 Max.	(6) Single receptacles	20A, 125V	✓	✓	☐ RB301ME	•
		(1) Locking receptacle	30A, 250V	✓	—		
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		
50	120/240 Max.	(6) Locking receptacles	20A, 125V	✓	✓	☐ RB302ME	•
		(1) Locking receptacle	30A, 250V	✓	—		
		(1) Locking inlet	50A, 125/250V	—	—		
		(1) Locking outlet	50A, 125/250V	—	—		

*Automatic GFCI reset configurations are available. When ordering automatic RhinoBox replace “M” in Catalog no. with “A”.
Example: RB300AE = Automatic; RB300ME = Manual.



5-20R L5-20R L6-30R



Plug Non-NEMA 50A 125/250V CA Standard
Receptacle Non-NEMA 50A 125/250V CA Standard

Testing & code compliance: cETLus listed for outdoor use - NEMA 3R products. Complies with NEC® Articles 525 & 590 & OSHA Reg. 29CFR, Part 1926, Subpart K, 1926.404, GFCI requirements. Conforms to UL1640 and CSA C22.2, no. 14. **Material characteristics:** Enclosure: Cold-rolled 18 gauge steel. Legs: Cold-rolled 10 gauge steel.

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-30