

Wallbox Lighting Controls

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

5-Button Timers

Single-Pole, 1800W
Incandescent/Halogen, Magnetic Low
Voltage, Electronic Low Voltage, Fluorescent,
Compact Fluorescent, LED

5-Button Timers

FEATURES

- Automatically turns lights/fan OFF after preset time.
- 5 selectable preset group times.
- Programming modes for custom preset.
- Green LEDs indicate preset time selected and provides countdown.
- No neutral required.
- Replaces standard switch to save energy.
- Ideal for bathrooms, closets, laundry rooms and garages.
- Fits any decorator wallplate.
- Color change kits available.
- Horsepower rated for 1/4 HP motor loads.

ASPIRE 5-Button Timers



Description	Color	Default Time Settings	Catalog No.
5-Button Minute Timer with OFF Single-Pole, 15A, 120VAC; 1800W; Wire Leads	AW, DS, SG, WS	5/10/15/30/60 Minutes	<input type="checkbox"/> 9590 ___
5-Button Hour Timer with OFF Single-Pole, 15A, 120VAC; 1800W; Wire Leads	AW, DS, SG, WS	1/2/4/8/12 Hours	<input type="checkbox"/> 9591 ___

ACCELL 5-Button Timers



Description	Color	Default Time Settings	Catalog No.
5-Button Minute Timer with OFF Single-Pole, 15A, 120VAC; 1800W; Wire Leads	A, B, BK, GY, LA, V, W	5/10/15/30/60 Minutes	<input type="checkbox"/> PT18M -___
5-Button Hour Timer with OFF Single-Pole, 15A, 120VAC; 1800W; Wire Leads	A, B, BK, GY, LA, V, W	1/2/4/8/12 Hours	<input type="checkbox"/> PT18H -___

Color Ordering Information

For ordering, include Cat. No. followed by the color code:

ASPIRE: AW (Alpine White), DS (Desert Sand), LA (Light Almond), SG (Silver Granite), WS (White Satin)

ACCELL: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)


TESTING & CODE COMPLIANCE

- cULus Listed to UL60730, file no. E325082
- NOM Certified


MATERIAL CHARACTERISTICS

- Environmental: Flammability meets UL 94 requirements; V0 rated
- Temperature Rating: 0°C to 40°C (32°F to 104°F)


www.cooperwiringdevices.com




PT18M



PT18H



9590



9591

Wallbox Lighting Controls

Specification & Performance Data

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

5-Button Timers


Single-Pole, 1800W
Incandescent/Halogen, Magnetic Low Voltage, Electronic
Low Voltage, Fluorescent, Compact Fluorescent, LED

Application

Cooper Wiring Devices ACCELL and ASPIRE 5-Button Timers automatically turn lights and fans off after a preset time. These units are ideal for residential and light commercial applications and are compatible with Cooper Wiring Devices Decorator style devices and wallplates. These timers can offer energy savings in areas where lights or fans are often left on in areas like bathrooms, garages, closets, and laundry rooms. The timers are designed for Single-Pole installations up to 1800W or ¼ horsepower.

	Device Type	ASPIRE and ACCELL, 5-Button Timer
	Wiring Type	Wire Leads
	Testing & Code Compliance	<ul style="list-style-type: none">cULus Listed to UL60730, file no. E325082NOM Certified
Specifications: Environmental	Flammability	Meets UL 94 requirements; V0 rated
	Temperature Rating	0°C to 40°C (32°F to 104°F)
Specifications: Electrical	Rating	120V/AC 60 Hz
	Light Intensity Control	Full-range, continuously variable dimming
	Surge Protection	Meets ANSI/IEEE Std. C62.41-1980, tested to withstand voltage surges up to 6000V and current surges of up to 200A without damage
	Power-failure Memory	Returns to OFF state
	Lamp Ratings	1800W Incandescent, Halogen, CFL, Fluorescent, LED, MLV, ELV
Specifications: Mechanical	Wiring Types	Single-pole
	LED Indicators	Indicates time remaining
	Horsepower Rating	Up to 1/4 HP
	Voltage Ratings	Permanently marked on device
Materials:	Top Housing	Polycarbonate
	Bottom Housing	Polycarbonate
	Strap	Galvanized Steel
	Buttons	Polycarbonate
	Form Factor	Decorator
	Finish	Gloss

Single-Pole Wiring Diagram



Specifications subject to change without notice.