



# Flush Mount Telephone Jacks


## Flush Mount Telephone Jacks

### FEATURES

- Spring wire contacts with 50 micro-inches gold plating over nickel measure 0.018" (0.005mm) diameter to maximize contact life and reduce corrosion.
- For use in Category 3 RJ11, RJ14 and RJ25 applications.
- All telephone jacks with wallplates are box mounting.
- 100% computer-tested to assure consistent high quality and reliable performance.
- Terminals are color-coded for easy wiring.

COMMERCIAL  
RESIDENTIAL

## H-3 COMMUNICATIONS PREMISE WIRING PRODUCTS



### Telephone Jack with Wallplate – 4 Conductor – RJ11, RJ14 Applications

Description	Color	Catalog No.	
		Non-UL Version	UL Version
Type 625B4 Screw Terminals	Almond	—	3532-4A
	Ivory	2532-4V	3532-4V
	Light Almond	—	3532-4LA
	White	2532-4W	3532-4W

### Telephone Jack with Wallplate – 6 Conductor – RJ11, RJ14, RJ25 Applications

Description	Color	Catalog No.
Type 625B4 Screw Terminals	Almond	3532-6A
	Ivory	3532-6V
	Light Almond	3532-6LA
	White	3532-6W

### Telephone Jack with Mid-Size Wallplate – 4 Conductor – RJ11, RJ14 Applications

Description	Color	Catalog No.	
		Non-UL Version	UL Version
Type 625B4 Screw Terminals	Almond	—	3533-4A
	Ivory	2533-4V	3533-4V
	Light Almond	—	3533-4LA
	White	2533-4W	3533-4W

### Telephone Jack with Wallplate – 6 Conductor – RJ11, RJ14, RJ25 Applications

Description	Color	Catalog No.
Type 625B4 Screw Terminals	Almond	3533-6A
	Ivory	3533-6V
	Light Almond	3533-6LA
	White	3533-6W

### TESTING & CODE COMPLIANCE

- Meets UL requirements (file no. E134135).
- 3532 is CSA Certified (file no. 090192-0-0000).

### MATERIAL CHARACTERISTICS

Self-extinguishing  
high-impact  
thermoplastic  
meets UL 94, V0  
flame retardancy  
rating.