


## ORDERING INFORMATION

Order code: 62948  
 Description: LED/DL4/9W/30K/RETRO/E26/D/STD  
 UPC: 069549629486  
 Case quantity: 4



## PERFORMANCE DATA

Shape:	Downlight 4"
Wattage (W):	9
Lamp voltage (VAC):	120
Colour temperature (K)**:	3 000
Average life (L70 hours):	40 000
Initial lumens (lm)*:	550
Initial lumens per watt (lm/W):	61
CBCP:	-
CRI:	80
Beam angle:	120
Power factor:	≥ 0.9
Operating temperature range:	-20 °C/-4 °F to 40 °C/104 °F
Base:	E26

\*Initial lumens range: +/- 5 %

\*\*Typical colour temperature range: +/- 5 %



## COMPATIBLE DIMMER LIST

**LUTRON DIMMERS:** RRD-10ND, SZ-6ND, HW-RPM-4A-120, HxD-6ND, QSG-6P, LP-RPM-4A-120, PHPM-WBX, S-600PR-WH, DV-600PR-WH, TG-600PR-WH, AY600P, Q600P, GL600, CN-600PHW, DV-603PG, S-600, S-600P, LG-600P, D-600PH, TT-300NLH, TG-603PG, DV-600PR-WH.

**OTHER DIMMERS:** Ace 34050, 3027596.  
 Leviton IPL06-I02, 6633-PL, 6684, 6631, IPI06-1LX.  
 Legrand DrRD4W.

## CAUTIONS


- Turn power off before inspection, installation, or removal.
- Disconnect power at fuse or circuit breaker before installing or servicing.
- Risk of electric shock – do not use where directly exposed to water or weather.
- Suitable for use in damp locations – in covered ceilings.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60 Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers and recessed housings.
- Five year limited warranty.
- For housing compatibility list please see installation instructions or visit [www.standardpro.com](http://www.standardpro.com).
- For complete dimmer compatibility and warranty information visit [www.standardpro.com](http://www.standardpro.com).
- Operating temperature: -20°C/-4°F to 40°C/104°F.

NOTES: This device complies with Part 15 of the FCC rules and has been tested and found to comply with the limits for a Class B digital device. This product may cause interference with other devices. If interference occurs, change the location of the product. Any changes or modifications not expressly approved by the manufacturer could void the user's authority to operate the equipment. This RFLD device complies with Canadian ICES-003. LED lamps must be stored, operated under suitable environmental conditions and in accordance with, but not limited to, the latest National Electrical Code, cETLus, CSA and ANSI specifications.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

July 16, 2014

## PHOTOMETRY



Zone	Lumens	% Total
0-10	15.8	3.2%
10-20	45	9.30%
20-30	67.6	13.9%
30-40	81	16.7%
40-50	8.38	1.73%
50-60	76.3	15.7%
60-70	60.1	12.4%
70-80	38.5	7.9%
80-90	17.3	3.6%
<b>Total</b>	<b>485.3</b>	<b>100%</b>

Zone Lumen Summary

## HOUSING COMPATIBILITY LIST

Manufacturer	Model #
Halo	H99RTAT, H99R
All-pro	ET400R, EI400 ATSB, ET 400 ATSB, ET400R ATSB
Commercial electric	HBR2000R, H 00B, H3, H17, H1
Juno	TC1R, TC1, IC1
Lithonia	L3, L3R