S202-C2

Print View..
Print to Pdf..

## **General Information**

Extended Product Type: S202-C2

 Product ID:
 2CDS252001R0024

 EAN:
 4016779523387

 Catalog Description:
 Miniature Circuit Breaker - S200 - Number

of Poles 2 - Tripping characteristic C

Long Description: System pro M compact S200 miniature

circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for

overload protection and the

electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (B,C,D,K,Z), configurations (1P,1P+N,2P,3P,3P+N,4P), breaking capacities (up to 6 kA at 230/400 V AC) and rated currents (up to 63A). All MCBs of the product range S200 comply with IEC/EN 60898-1, IEC/EN 60947-2, UL1077 and CSA 22.2 No. 235, allowing the use for residential, commercial and industrial applications. Bottom-fitting auxiliary contact can be mounted on S200 to save 50% space.



## Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Miniature Circuit Breakers MCBs

Parts & Services » Drives » Medium Voltage AC Drives » General Purpose Drives » ACS1000

Parts & Services » Drives » Medium Voltage AC Drives » Special Purpose Drives » ACS5000 water cooled

## **Accessories Show accessory images**

## SparePartUsedOnList Show accessory images

# Ordering

**EAN:** 4016779523387

Minimum Order Quantity: 1 piece
Customs Tariff Number: 85362010

#### **Dimensions**

Product Net Width:35.0 mmProduct Net Depth:69.0 mmProduct Net Height:88.0 mmProduct Net Weight:0.250 kg

## **Container Information**

Package Level 1 Units:5 piecePackage Level 1 Width:92.0 mmPackage Level 1 Length:183.0 mmPackage Level 1 Height:80.0 mm

Package Level 1 Gross Weight: 1.300 kg
Package Level 1 EAN: 4016779608237

**Environmental** 

Ambient Air Temperature: Operation -25 ... +55 °C

Storage -40 ... +70 °C

Resistance to Shock acc. to IEC

60068-2-27:

25g / 2 shocks / 13 ms

Resistance to Vibrations acc. to IEC

60068-2-6:

5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In

Environmental Conditions: 28 cycles

with 55 °C / 90-96 % and 25 °C / 95-100 %

**RoHS Status:** Following EU Directive 2002/95/EC August 18, 2005 and amendment

**Technical** 

Standards: IEC/EN 60898-1

IEC/EN 60947-2

UL 1077

Number of Poles: 2
Tripping Characteristic: C
Rated Current (I<sub>p</sub>): 2.00 A

Rated Operational Voltage: acc. to IEC60898-1 400 V AC

acc. to IEC60947-2 440 V AC

Power Loss: 3.6 W

Per Pole 1.8 W

Rated Insulation Voltage (U<sub>i</sub>): acc. to IEC/EN 60664-1 440 V

Operational Voltage: Maximum (incl. tolerance) 125 V DC

Maximum (incl. tolerance) 440 V AC

Minimum 12 V AC / 12 V DC

Rated Frequency (f): 50 Hz

60 Hz

Rated Short-Circuit Capacity ( I<sub>cn</sub>

6 kA

):

Rated Ultimate Short-Circuit Breaking 10 kA

Capacity (I<sub>cu</sub>):

Rated Service Short-Circuit Breaking 7.5 kA

Capacity (I<sub>cs</sub>):

Energy Limiting Class: 3

Overvoltage Category: III

Pollution Degree: 3

Rated Impulse Withstand Voltage 4 kV

(U<sub>imp</sub>):

(6.2 kV @ sea level) kV

(5.0 kV @ 2000 m) kV

Dielectric Test Voltage:50 / 60 Hz, 1 min: 2 kVHousing Material:Insulation group II, RAL 7035Actuator Type:Insulation group II, black, sealable

Actuator Marking: 1 / O

Contact Position Indication: Red ON / Green OFF

Degree of Protection: IP20

Remarks: IP40 in enclosure with cover

Electrical Endurance:20000 AC cycleMechanical Endurance:20000 cycleTerminal Type:Screw Terminals

Screw Terminal Type: Failsafe Bi-directional Cylinder-lift Terminal

Connecting Capacity: Busbar 10 / 10 mm<sup>2</sup>

Flexible with Ferrule 0.75 ... 25 mm<sup>2</sup>

Flexible 0.75 ... 25 mm² Rigid 0.75 ... 35 mm² Stranded 0.75 ... 35 mm²

Tightening Torque:2.8 N⋅mRecommended Screw Driver:Pozidriv 2

Mounting on DIN Rail: TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715

Mounting Position: Any

**Technical UL/CSA** 

Maximum Operating Voltage UL/CSA: 480Y / 277 V AC
Connecting Capacity UL/CSA: Busbar 18 ... 8 AWG

Conductor 18 ... 4 AWG

**Tightening Torque UL/CSA:** 25 in·lb **Interrupting Rating acc. to UL1077:** 6 kA

**Certificates and Declarations (Document Number)** 

**Declaration of Conformity - CE**: 2CDK403001D0602 **RoHS Information**: 2CDK400003K0201

**Classifications** 

**eClass**: 7.0 27141901 **E-nummer**: 2100544

ETIM 4.0: EC000042 - Miniature circuit breaker (MCB)
ETIM 5.0: EC000042 - Miniature circuit breaker (MCB)

Object Classification Code: F

**UNSPSC**: 39121600