

XT IEC Bimetallic Overload Relay

XTOB012BC1

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Observe the maximum permissible fuse of the contactor with direct device mounting. Suitable for protection of EEx e-motors. EC prototype test certificate available upon request.

Warranties: No Data

Specifications:


- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 45 mm
- **Mounting:** Direct
- **Overload Range:** 9-12A
- **Trip Type:** 10A
- **Type:** XT IEC Bimetallic Overload Relay
- **Used With:** 9-15A contactor

Supporting documents:

- [C440 Electronic Overload Relay](#)
- [Eatons Volume 5-Motor Control and Protection](#)
- [XTOB_BC1 3D Inventor](#)
- [XTOB_BC1 AutoCAD 2D Footprint](#)
- [XTOB_BC1 3D Model Xchange](#)
- [XTOB_BC1 2D PDF](#)
- [XTOB_BC1 2D Drawing Xchange](#)
- [XTOB_BC1 AutoCAD 2D Footprint \(mm\)](#)
- [Global Data Sheet - XTOB012BC1](#)
- [Eaton Specification Sheet - XTOB012BC1](#)

Certifications:

- UL Listed
- CSA Certified
- IEC 60947



- EN 60947

Product compliance:

- RoHS Compliant
- CE Marked
- ATEX Compliant

© 2016 Eaton. All rights reserved.