


Dual Voltage 370/440V • Single MFD

370/440 Volt Oval						MFD	370/440 Volt Round					
Dimensions (Millimeters)			Dimensions (Inches)				OVAL	ROUND	Dimensions (Inches)		Dimensions (Millimeters)	
Width	Depth	Height	Width	Depth	Height	Di.			Height	Di.	Height	
51.5	31.5	60	2.03	1.24	2.36	36-5-370440	5	36-5R3744	1.65	2.37	42	60
51.5	31.5	60	2.03	1.24	2.36	36-7-370440	7.5	36-7R3744	1.65	2.37	42	60
51.5	31.5	80	2.03	1.24	3.15	36-10-370440	10	36-10R3744	1.65	2.78	42	70
51.5	31.5	80	2.03	1.24	3.15	36-12-370440	12.5	36-12R3744	1.65	2.78	42	70
51.5	31.5	80	2.03	1.24	3.15	36-15-370440	15	36-15R3744	1.65	3.15	42	80
71.0	45.0	80	2.80	1.77	3.15	36-17-370440	17.5	36-17R3744	1.65	3.15	42	80
71.0	45.0	80	2.80	1.77	3.15	36-20-370440	20	36-20R3744	1.78	3.15	45	80
71.0	45.0	80	2.80	1.77	3.15	36-25-370440	25	36-25R3744	1.78	3.54	45	90
71.0	45.0	90	2.80	1.77	3.55	36-30-370440	30	36-30R3744	2.00	3.94	50	100
71.0	45.0	90	2.80	1.77	3.55	36-35-370440	35	36-35R3744	2.00	3.94	50	100
71.0	45.0	90	2.80	1.77	3.55	36-40-370440	40	36-40R3744	2.00	4.33	50	110
71.0	45.0	110	2.80	1.77	4.33	36-45-370440	45	36-45R3744	2.00	4.33	50	110
71.0	45.0	110	2.80	1.77	4.33	36-50-370440	50	36-50R3744	2.00	4.33	50	110



OVAL



ROUND

Dual Voltage 370/440V • Dual MFD

370/440 Volt Oval						MFD	370/440 Volt Round					
Dimensions (Millimeters)			Dimensions (Inches)				OVAL	ROUND	Dimensions (Inches)		Dimensions (Millimeters)	
Width	Depth	Height	Width	Depth	Height	Di.			Height	Di.	Height	
71.0	45.0	80	2.80	1.77	3.15	36-25-5-3744	25/5	36-255R3744	1.97	3.54	50	90
71.0	45.0	100	2.80	1.77	3.94	36-30-5-3744	30/5	36-305R3744	1.97	4.16	50	105
71.0	45.0	100	2.80	1.77	3.94	36-35-5-3744	35/5	36-355R3744	2.17	4.33	55	110
71.0	45.0	110	2.80	1.77	4.33	36-40-5-3744	40/5	36-405R3744	2.36	4.72	60	120
71.0	45.0	110	2.80	1.77	4.33	36-45-5-3744	45/5	36-455R3744	2.36	4.72	60	120



SQUARE

Higher Voltage Capacitors Can Be Substituted For Lower Voltage Applications.

Dual Voltage 250-440V • Single MFD

250-440 Volt Square						MFD	
Dimensions (Millimeters)			Dimensions (Inches)				SQUARE
Width	Depth	Height	Width	Depth	Height		
37.0	18.0	28.0	1.46	0.71	1.10	36-2S440	2
37.0	18.0	28.0	1.46	0.71	1.10	36-3S440	3
37.0	22.0	34.0	1.46	0.87	1.34	36-4S440	4
37.0	22.0	34.0	1.46	0.87	1.34	36-5S440	5
47.0	26.0	38.0	1.85	1.02	1.50	36-7S440	7.5
47.0	26.0	38.0	1.85	1.02	1.50	36-8S440	8
58.0	30.0	44.0	2.28	1.18	1.73	36-10S440	10
58.0	30.0	44.0	2.28	1.18	1.73	36-12S440	12.5
58.0	30.0	44.0	2.28	1.18	1.73	36-15S440	15
58.0	39.0	50.0	2.28	1.54	1.97	36-20S440	20



RO TOM RUN CAPACITORS

- Heavy Duty, Compact Design
- UL & cUL Recognized
- Competitively Priced
- Built In Interrupter
- Largest Selection

NOTE:

CAPACITORS IN SERIES

- MFD rating decreases; Voltage increases.

$$\text{New MFD Rating} = \frac{\text{MFD}_1 \times \text{MFD}_2}{\text{MFD}_1 + \text{MFD}_2}$$

CAPACITORS IN PARALLEL

- MFD increases; Voltage rating stays constant.
- (ex. two 5 MFD 370 V capacitors wired in parallel is the equivalent of a 10 MFD 370 V Capacitor)

$$\text{New MFD Rating} = \text{MFD}_1 + \text{MFD}_2$$

- When connected in either series or parallel it is recommended that capacitors with the same MFD ratings be used.
- Higher voltages may be substituted for lower voltages in the same MFD rating.