

MQM Series MR16 LED lamps






FEATURES

- . 6, 12 and 24V with various wattages
- Fire-retardant thermoplastic
- 300° rotation
- CSA certified to C22.2 No.141-15

See warranty details at: www.tnb.ca/en/brands/lumacell

DIMENSIONS

Dimensions are approximate and subject to change.



TYPICAL SPECIFICATIONS

Lamp head and stem shall be injection molded, impact resistant, flame retardant thermoplastic and shall require no tool for aiming or adjustment. The lens shall be inverse concave design and fully adjustable for aisle or area distribution during installation without the need to energize the lamp. Visual identification of distribution shall be provided through position of adjustment pins.

Fixture shall be supplied with a canopy for installation on any four inch octagon box. Housing shall be designed to allow for lamp replacement if required.

The remote fixtures shall be certified to CSA 22.2 No.141-15.

The remote unit shall be the **Lumacell®** model: ____

WIRE GUARDS

	i e
460.0029-L	Wall ceiling Mount

REPLACEMENT LAMPS

MODEL	AC SPECS	DC SPECS	
580.0097-L	MR16 LED	6V-4W	
580.0122-L	MR16 LED	6V-5W	
580.0093-L	MR16 LED	12V-4W	
580.0098-L	MR16 LED	12V-5W	
580.0106-L	MR16 LED	12V-6W	
580.0104-L	MR16 LED	24V-4W	
580.0100-L	MR16 LED	24V-6W	

ORDERING INFORMATION

SERIES	LAMP TYPE	NUMBER OF HEADS	VOLTAGE/WATTAGE/LAMP TYPE	COLOURS
M= micro, PAR 18	QM= MR16 LED	1= single head 2= double head 3= triple head	LD1= MR16 LED, 6V-4W LD2= MR16 LED, 6V-5W LD7= MR16 LED, 12V-4W LD9= MR16 LED, 12V-5W LD10= MR16 LED, 12V-6W LD13= MR16 LED, 24V-4W LD14= MR16 LED, 24V-6W	Blank= factory white BK= black

EXAMPLE: MQMLD7

