

## Nylon Fish Tapes

436-5  
(12" Case)



- Co-extruded curl-resistant nylon fish tape fishes equally well in large and small conduit.
- High-impact nylon, one-piece handle for maximum durability, long life, and easy, comfortable use.
- Heavy-duty winder case.
- Nylon fish tape is intended for fishing only. Rope or line is recommended for pulling.

CAT. NO.	UPC NO.	DESCRIPTION
436-5	27396	50' × 3/16" (15.2 m × 4.8 mm) diameter Nylon Fish Tape in Winder Case
436-10	27397	100' × 3/16" (30.5 m × 4.8 mm) diameter Nylon Fish Tape in Winder Case
R436-5	36850	50' × 3/16" (15.2 m × 4.8 mm) diameter Nylon Fish Tape without Winder Case
R436-10	36849	100' × 3/16" (30.5 m × 4.8 mm) diameter Nylon Fish Tape without Winder Case
01664	01664	Replacement Tip NOTE: Requires Greenlee K05 or K09 series crimper or #6 hex crimp to install.
39790	39790	One-Piece Handle
39791	39791	12" (305 mm) diameter Replacement Case

### SPECIFICATIONS

<b>Capacity</b>	3/16" (4.8 mm) diameter – 250 lbs. (1.1 kN) maximum design strength	
<b>Weight</b>	436-5 – 2 lbs. (0.9 kg)	R436-5 – 1 lb. (0.5 kg)
	436-10 – 3 lbs. (1.4 kg)	R436-10 – 2 lbs. (0.9 kg)

## Flex-O-Twist® Flexible Steel Fish Tapes

539-50,  
539-100  
(12" Case)



- Made of wound, multi-strand 3/16" (4.8 mm) diameter steel cable for strength and flexibility.
- Flexible... slips through lateral and vertical bends in the same run.
- One-piece, high-impact nylon handle for maximum durability, long life, and easy, comfortable use.
- Heavy-duty winder case.

CAT. NO.	UPC NO.	DESCRIPTION
539-50	30162	50' × 3/16" (15.2 m × 4.8 mm) diameter Flexible Steel Fish Tape in Winder Case
539-100	34002	100' × 3/16" (30.5 m × 4.8 mm) diameter Flexible Steel Fish Tape in Winder Case
439-100	29518	100' × 3/16" (30.5 m × 4.8 mm) diameter Flexible Steel Fish Tape without Winder Case
39790	39790	One-Piece Handle
39791	39791	12" (305 mm) diameter Replacement Case

### SPECIFICATIONS

<b>Capacity</b>	3/16" (4.8 mm) tape width – 500 lbs. (2.2 kN) maximum design strength.	
<b>Weight</b>	539-50 – 6 lbs. (2.7 kg)	539-100 – 10 lbs. (4.5 kg)